

881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples



Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Features

- Bandpass SAW Filter with 25 MHz Bandwidth
- Surface Mount 3.0 x 3.0 x 1.3 mm package
- Single-Ended Input and Output
- Excellent selectivity with high out-of-band

Applications

- CDMA, WCDMA 850 and AMPS applications
- Wireless infrastructure
- Distributed Antenna Systems (DAS)
- Repeaters and PCS Applications

Product Image



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples



Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Electrical Specification

Parameters	Minimum	Typical	Maximum	Units	Notes
Center Frequency (fc)	-	881.5	-	MHz	
Insertion Loss	-	2.2	3.0	dB	869~894MHz
Amplitude Ripple	-	0.6	1.5	dB _{p-p}	869~894MHz
Attenuation	50	60	-	dB	D.C.~779 MHz
	42	47	-		779~849 MHz
	26	30			914~970 MHz
	50	58			970~1049 MHz
	45	55			1049~2000 MHz
VSWR	-	1.6	2.0	-	869~894MHz
DC Voltage	-	-	5	V	
Input Power	-	-	15	dBm	
Source Impedance (single ended) ¹	-	50	-	Ω	
Load Impedance (single ended) ¹	-	50	-	Ω	

Noes: (1) No Matching Network (Ref. Testing Environment Circuit as shown below)

Mechanical Specification

Parameters	Specifications
Dimension	3.0 x 3.0 x 1.3 mm
Mounting Type	SMD Mount

Environmental Specification

Parameters	Specifications
Operating Temperature Range	-30°C ~ +85°C
Storage Temperature Range	-40°C ~ +85°C
MSL level	N/A
ESD	N/A



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-15-23

ABRACON IS
ISO9001-2015
CERTIFIED

881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Product Dimensions



Unit : mm

Pin No.	Description
A,C,D,F	Ground
E	Input
B	Output

881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Measurement Circuit



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory




3.0 x 3.0 x 1.3 mm
RoHS Compliant

Frequency Characteristics

S21 narrow band



S21 wide band



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Group Delay Ripple



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples





Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

VSWR (S11 & S22)



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory




3.0 x 3.0 x 1.3 mm
RoHS Compliant

Smith Chart (S11 & S22)

Smith chart S11 (864~898MHz)



Smith chart S22 (864~898MHz)



881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples



Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process
Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2

Pb-Free Process
Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	200°C
Time (T_{smin} to T_{smax}) (t_s)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T_p)*	see Table 1	see Table 2
Time (t_p)** within 5°C of the specified classification temperature (T_C)	20 sec.	30 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as supplier minimum and a user maximum.

881.5 MHz SMD SAW Filter

ABSNS6A7-1CHM011M

Request Samples




Check Inventory



3.0 x 3.0 x 1.3 mm
RoHS Compliant

Packaging

Tape & Reel Dimension



Carrier Tape Specifications (mm)

E1	P0	F	P1	W	A0	B0	K0	Reel Qty
1.75 ± 0.1	4.0 ± 0.1	5.5 ± 0.10	8.0 ± 0.1	12.0 ± 0.3	3.4 ± 0.1	3.4 ± 0.1	1.4 ± 0.1	2,500

Reel Specifications (mm)

A	W ₁	N	C
330 ± 1.0	12.0 ± 1.0	62 ± 1.0	13 ± 0.5

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-15-23

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ABSNS6A7-1CHM011M](#)