

5G/4G External Whip Antenna



AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Features

- 698-960/1710-2690/3300-3800 MHz
- Includes 5G NR, CBRS, Private LTE Bands
- Support cellular 4G/LTE/3G bands
- Gain of 3 dBi
- Linear Polarization
- SMA Connector Mount

Applications

- 5G
- 4G/LTE
- IoT
- LTE radios
- Gateways & Routers
- Set-Top Boxes
- Security
- Smart Metering
- Vending Machines
- Smart Home

Electrical Specifications

Parameters	Min.	Typ.	Max.	Units	Notes
Operating Frequency Range	698		960	MHz	
	1710		2690		
	3300		3800		
VSWR			3.5		
Gain		3		dBi	
Impedance		50		Ω	
Polarization	Linear				

Mechanical Specification

Parameters	Description	Notes
Mounting Method	Connector	
Connector Type	SMA Male	

Environmental Specification

Parameters	Description
Operating Temperature	-40°C to +85°C
Vibration	10 ~ 55 Hz with 1.5 mm amplitude 2 hr



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-10-20

ABRACON IS
ISO9001-2015
CERTIFIED


5G/4G External Whip Antenna

AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Product Dimensions



Dimensions: mm




5G/4G External Whip Antenna

AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

VSWR



5G/4G External Whip Antenna




AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Radiation Pattern

2D Pattern
XY - Plane



5G/4G External Whip Antenna




AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Radiation Pattern

2D Pattern
XZ - Plane



5G/4G External Whip Antenna




AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Radiation Pattern

2D Pattern
YZ - Plane



5G/4G External Whip Antenna




AEACAC198013-S5GNR




198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

3D Pattern


698 MHz




824 MHz




960 MHz




1710 MHz



1990 MHz



2170 MHz



5G/4G External Whip Antenna




AEACAC198013-S5GNR




198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

3D Pattern


2690 MHz



3300 MHz



3800 MHz



Frequency	Efficiency	Gain (dBi)
698	0.65	2.94
824	0.61	3.04
960	0.58	2.9
1710	0.59	-0.4
1990	0.61	2.38
2170	0.62	2.47
2690	0.59	1.6
3300	0.58	0.19
3800	0.58	0.62

5G/4G External Whip Antenna



AEACAC198013-S5GNR



198.0 x 13.0 mm
RoHS/RoHS II Compliant
MSL = Not Applicable

Packaging

A carton holds 500 pcs of antenna. Each carton is 49.5 x 22 x 27 cm and weighs 13 kg.

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-10-20

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AEACAC198013-S5GNR](#)