

NFC Antenna



AFAR3026-SN



26.5 x 30 x 0.6 mm
RoHS/RoHS II Compliant
MSL = NA

Features

- NFC Antenna at 13.56 MHz
- Very thin, Low Profile structure
- Linear Polarization
- Easy integration using cable and IPEX connector

Applications

- IoT devices
- NFC payment readers
- Healthcare ID scanners
- Office ID
- Electronic wallets
- NFC data loggers transport
- Ticketing systems
- Electronic parking payments
- Industrial data collection
- Mobile Devices
- Access control

Electrical Specifications

Parameters	Min.	Typ.	Max.	Units
Operating Frequency		13.56		MHz
Inductance		47.356		nH
Return Loss	1.5			dB
Polarization	Linear			
Impedance	50			Ω

Environmental Characteristics

Parameters	Description
Operating Temperature	-40°C to +85°C

Mechanical Specifications

Parameters	Description	Notes
Cable type	Ø1.13 mm	Color: Gray
Cable length	100 ± 2.0 mm	
Connector	IPEX	
Mounting	Double-sided tape	Not included

NFC Antenna




AFAR3026-SN



26.5 x 30 x 0.6 mm
RoHS/RoHS II Compliant
MSL = NA

Product Dimensions



(Unit: mm)




AFAR3026-SN



26.5 x 30 x 0.6 mm
RoHS/RoHS II Compliant
MSL = NA

Measurement – Smith Chart



Packaging

Each carton is 330 x 280 x 254 mm and has 3600 pcs of antenna.

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AFAR3026-SN](#)