

Automotive Ferrite Chip Beads



AFBC-Q0603

Request Samples



Check Inventory



1.60 x 0.8 x 0.8 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- AEC-Q200 Qualified
- Operating Temperature: -55 ~ +150°C
- Wide range impedance
- Monolithic inorganic material construction
- Excellent heat resistance
- Current ratings up to 3A

Applications

- Electronic control Units (ECUs)
- Battery Management Systems (BMS)
- Powertrain system
- DC/AC Converters
- Industrial connectivity (IIoT)

Electrical Specifications

Part Number	Impedance	DC Resistance	Rated Current
Units	$\Omega \pm 25\%$	Ω Max.	mA Max.
Symbol	Z	R _{DC}	I _R
AFBC-Q0603-300	30	0.04	3000
AFBC-Q0603-800	80	0.04	3000
AFBC-Q0603-121	120	0.10	2000
AFBC-Q0603-151	150	0.10	2000
AFBC-Q0603-221	220	0.10	2000
AFBC-Q0603-301	300	0.2	1000
AFBC-Q0603-471	470	0.2	1000
AFBC-Q0603-601	600	0.2	1000

Test Conditions and Equipment

Impedance Test Frequency: 100MHz


I_R: Temperature Rise: 40°C Max. At Rated Current $\geq 1A$.

Operating Temperature: -55°C to +150°C (Including self-temperature rise)

Storage Temperature: <+40°C and RH 60% (Max).

AFBC-Q0603 is **RoHS Compliant and Pb free**

Automotive Ferrite Chip Beads



AFBC-Q0603

Request Samples




Check Inventory




1.60 x 0.8 x 0.8 mm
RoHS/RoHS II Compliant
MSL Level = 1

Electrical Specifications (Cont'd)


AFBC-Q0603-300




AFBC-Q0603-800




AFBC-Q0603-121




AFBC-Q0603-151




AFBC-Q0603-221




AFBC-Q0603-301




AFBC-Q0603-471



AFBC-Q0603-601



Automotive Ferrite Chip Beads



AFBC-Q0603

Request Samples



Check Inventory



1.60 x 0.8 x 0.8 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Number Identification

AFBC -Q0603 - -



Impedance Code

Please refer to the
Electrical Specification
table

Packaging

T: Tape and Reel
(4kpcs / reel)

Mechanical Specifications



L	W	T	a	H	I	J
1.60±0.15	0.80±0.15	0.80±0.15	0.30±0.20	0.95 Ref.	0.80 Ref.	0.85 Ref.

Dimension: mm

Automotive Ferrite Chip Beads



AFBC-Q0603

Request Samples




Check Inventory




1.60 x 0.8 x 0.8 mm
RoHS/RoHS II Compliant
MSL Level = 1

Materials



	Structure Description
1	Ferrite for Beads
2	Internal Terminal Electrode: Ag (100%)
3	Electro-plating: Ni (100%)
4	External Electro-plating: Sn (100%)

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ $150^{\circ}C \sim 200^{\circ}C$	60 ~ 180 sec.
2	Reflow	T_L $245^{\circ}C$	20 ~ 40 sec.
3	Peak heat	T_P $260^{\circ}C$	10 sec. MAX

Automotive Ferrite Chip Beads



AFBC-Q0603

Request Samples




Check Inventory




1.60 x 0.8 x 0.8 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

T= Tape and reel (4,000 pcs/reel)



Type	A	B	C	D
7"x8mm	9.0 ± 0.5	60.0 ± 2.0	13.5 ± 0.5	178.0 ± 2.0



Series	Bo	Ao	Ko	P
AFBC-Q0603	1.80 ± 0.05	0.96 ± 0.05	0.95 ± 0.05	4.00 ± 0.10

Dimension: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
 Phone: 512-371-6159 | Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISION: IR 08-10-22

ABRACON IS
 ISO9001-2015
 CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AFBC-Q0603-121-T](#) [AFBC-Q0603-151-T](#) [AFBC-Q0603-221-T](#) [AFBC-Q0603-300-T](#) [AFBC-Q0603-301-T](#) [AFBC-Q0603-471-T](#) [AFBC-Q0603-601-T](#) [AFBC-Q0603-800-T](#)