

High Q Ceramic Wirewound RF Inductor (AEC-Q200)



AISC-Q0402HQ Series

Request Samples



Check Inventory



1.27 x 0.76 x 0.61 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- PPAP ready and supported
- TS16949 certified production lines
- AEC-Q200 (grade 1) qualified
- Ceramic base with high SRF
- Excellent DCR and current carrying characteristics.
- Ultra-compact inductors
- Tight tolerance down to $\pm 2\%$

Applications

- Automotive applications
- Bluetooth, W-LAN, Broadband Network
- Impedance matching networks
- Filtering for high frequency communication circuits
- Video cameras, displays, and other electronic devices.

Electrical Specifications

Part Number	Inductance	Tolerance	Min. Quality Factor		L/Q Test Freq.	Max. DC Resistance	Max. Rated Current	Min. Self-resonant Frequency
Units	nH	-	Q		MHz	Ω	mA	GHz
Symbol	L	-	900MHz	1.7GHz	Freq.	DCR	Ir	S.R.F
AISC-Q0402HQ-1N0	1.0	C, D, J, K	46	75	250	0.030	2300	16.0
AISC-Q0402HQ-2N0	2.0	C, D, J, K	58	85	250	0.038	2100	15.2
AISC-Q0402HQ-2N2	2.2	C, D, J, K	60	86	250	0.038	2100	15.1
AISC-Q0402HQ-2N4	2.4	C, D, J, K	60	83	250	0.042	2000	14.0
AISC-Q0402HQ-2N7	2.7	C, D, J, K	62	85	250	0.075	1500	13.0
AISC-Q0402HQ-3N3	3.3	C, D, J, K	66	95	250	0.045	1700	12.8
AISC-Q0402HQ-3N6	3.6	C, D, J, K	65	94	250	0.045	1700	11.7
AISC-Q0402HQ-3N9	3.9	C, D, J, K	64	98	250	0.045	1700	9.50
AISC-Q0402HQ-4N3	4.3	D, J, K	63	90	250	0.50	1600	7.15
AISC-Q0402HQ-4N7	4.7	D, J, K	58	83	250	0.70	1500	6.85
AISC-Q0402HQ-5N1	5.1	G, J, K	54	76	250	0.115	1200	6.80
AISC-Q0402HQ-5N6	5.6	G, J, K	73	105	250	0.050	1600	6.50
AISC-Q0402HQ-6N2	6.2	G, J, K	73	100	250	0.055	1600	5.80
AISC-Q0402HQ-6N8	6.8	G, J, K	68	94	250	0.065	1500	5.80
AISC-Q0402HQ-7N5	7.5	G, J, K	60	82	250	0.090	1400	5.40
AISC-Q0402HQ-8N2	8.2	G, J, K	68	95	250	0.065	1500	5.40
AISC-Q0402HQ-8N7	8.7	G, J, K	68	95	250	0.065	1500	5.00
AISC-Q0402HQ-9N0	9.0	G, J, K	67	92	250	0.080	1400	5.00
AISC-Q0402HQ-9N5	9.5	G, J, K	64	90	250	0.090	1400	4.70
AISC-Q0402HQ-10N	10	G, J, K	62	90	250	0.100	1300	4.70
AISC-Q0402HQ-11N	11	G, J, K	68	98	250	0.065	1400	4.70
AISC-Q0402HQ-12N	12	G, J, K	66	100	250	0.100	1200	4.40
AISC-Q0402HQ-13N	13	G, J, K	622	82	250	0.150	870	4.20
AISC-Q0402HQ-15N	15	G, J, K	62	85	250	0.110	1100	3.90
AISC-Q0402HQ-16N	16	G, J, K	57	77	250	0.140	850	3.70



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
11/21/2023

ABRACON IS
ISO9001-2015
CERTIFIED

High Q Ceramic Wirewound RF Inductor (AEC-Q200)



AISC-Q0402HQ Series

Request Samples



Check Inventory



1.27 x 0.76 x 0.61 mm
RoHS/RoHS II Compliant
MSL Level = 1

Electrical Specifications (Cont'd)

Part Number	Inductance	Tolerance	Min. Quality Factor		L/Q Test Freq.	Max. DC Resistance	Max. Rated Current	Min. Self-resonant Frequency
Units	nH	-	Q		MHz	Ω	mA	GHz
Symbol	L	-	900MHz	1.7GHz	Freq.	DCR	Ir	S.R.F
AISC-Q0402HQ-18N	18	G, J, K	58	74	250	0.120	900	3.55
AISC-Q0402HQ-19N	19	G, J, K	61	88	250	0.145	850	3.50
AISC-Q0402HQ-20N	20	G, J, K	58	76	250	0.185	780	3.50
AISC-Q0402HQ-21N	21	G, J, K	48	62	250	0.460	450	1.70
AISC-Q0402HQ-22N	22	G, J, K	60	74	250	0.160	800	3.30
AISC-Q0402HQ-23N	23	G, J, K	60	77	250	0.160	800	3.30
AISC-Q0402HQ-24N	24	G, J, K	55	71	250	0.200	700	3.15
AISC-Q0402HQ-25N	25	G, J, K	57	73	250	0.250	600	3.15
AISC-Q0402HQ-26N	26	G, J, K	56	74	250	0.285	450	3.15
AISC-Q0402HQ-27N	27	G, J, K	62	86	250	0.320	450	3.20
AISC-Q0402HQ-30N	30	G, J, K	61	87	250	0.330	450	2.90
AISC-Q0402HQ-33N	33	G, J, K	61	80	250	0.330	490	2.80
AISC-Q0402HQ-36N	36	G, J, K	59	76	250	0.380	480	2.80
AISC-Q0402HQ-37N	37	G, J, K	57	72	250	0.460	470	2.70
AISC-Q0402HQ-39N	39	G, J, K	56	84	250	0.430	450	2.60
AISC-Q0402HQ-40N	40	G, J, K	56	75	250	0.430	450	2.60
AISC-Q0402HQ-43N	43	G, J, K	52	68	250	0.520	450	2.50
AISC-Q0402HQ-47N	47	G, J, K	48	62	250	0.580	420	2.40
AISC-Q0402HQ-51N	51	G, J, K	52	59	250	0.700	360	2.30

Test Conditions:

Inductance, Q: HP4286/E4982A

SRF: HP4287/E4982A

DCR: Micro-Ohm meter (Gom-801G)/E4982A

IDC: Applied the current to coils, the temperature of coil increases $\Delta T 15^{\circ}\text{C}$ ($T_a = 25^{\circ}\text{C}$).

Operating Temperature: -40°C to $+125^{\circ}\text{C}$

Components Storage Temperature: -40°C to $+125^{\circ}\text{C}$

Tape and Reel packaging Temperature: $15 \sim 28^{\circ}\text{C}$; $< 80\% \text{ RH}$

AISC-Q0402HQ is AEC-Q200 Qualified

AISC-Q0402HQ Series is **RoHS Compliant and Pb free**



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
11/21/2023

ABRACON IS
ISO9001-2015
CERTIFIED

High Q Ceramic Wirewound RF Inductor (AEC-Q200)



AISC-Q0402HQ Series

Request Samples




Check Inventory




1.27 x 0.76 x 0.61 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Number Identification



Mechanical Dimensions



A	B	C	D	E	F	G	H	I	J
1.27 max	0.76 max	0.61 max	0.15 max	0.51	0.23	0.56	0.66	0.5	0.46

Dimensions: mm



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
11/21/2023

ABRACON IS
ISO9001-2015
CERTIFIED

1.27 x 0.76 x 0.61 mm
RoHS/RoHS II Compliant
MSL Level = 1

Zone	Description	Temperature	Times
1	Preheat	$T_{\text{SMIN}} \sim T_{\text{SMAX}}$ $150^{\circ}\text{C} \sim 180^{\circ}\text{C}$	90 ~ 120 sec.
2	Reflow	T_{L} 220°C	40 ~ 60 sec.
3	Peak heat	T_{P} $260^{\circ}\text{C} \pm 5^{\circ}\text{C}$	10 sec. MAX



REVISION Initial Release :
11/21/2023

ABRACON IS
ISO9001-2015
CERTIFIED

High Q Ceramic Wirewound RF Inductor (AEC-Q200)



AISC-Q0402HQ Series

Request Samples




Check Inventory




1.27 x 0.76 x 0.61 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

T: Tape & Reel: 4,000 pcs/reel



A	B	H	F	P	P0	P1	W
0.81	1.23	0.73	3.50	2.0	4.0	2.0	8.0



Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
11/21/2023

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AISC-Q0402HQ-13NJ-T](#) [AISC-Q0402HQ-26NG-T](#) [AISC-Q0402HQ-8N2G-T](#) [AISC-Q0402HQ-37NG-T](#) [AISC-Q0402HQ-20NK-T](#) [AISC-Q0402HQ-21NJ-T](#) [AISC-Q0402HQ-33NJ-T](#) [AISC-Q0402HQ-4N3D-T](#) [AISC-Q0402HQ-26NK-T](#) [AISC-Q0402HQ-11NG-T](#) [AISC-Q0402HQ-12NG-T](#) [AISC-Q0402HQ-11NJ-T](#) [AISC-Q0402HQ-47NJ-T](#) [AISC-Q0402HQ-40NK-T](#) [AISC-Q0402HQ-9N5J-T](#) [AISC-Q0402HQ-4N7J-T](#) [AISC-Q0402HQ-3N3K-T](#) [AISC-Q0402HQ-5N6J-T](#) [AISC-Q0402HQ-8N7K-T](#) [AISC-Q0402HQ-36NG-T](#) [AISC-Q0402HQ-24NG-T](#) [AISC-Q0402HQ-6N2J-T](#) [AISC-Q0402HQ-11NK-T](#) [AISC-Q0402HQ-26NJ-T](#) [AISC-Q0402HQ-33NG-T](#) [AISC-Q0402HQ-27NG-T](#) [AISC-Q0402HQ-3N6D-T](#) [AISC-Q0402HQ-19NJ-T](#) [AISC-Q0402HQ-5N1K-T](#) [AISC-Q0402HQ-5N6G-T](#) [AISC-Q0402HQ-2N2J-T](#) [AISC-Q0402HQ-24NJ-T](#) [AISC-Q0402HQ-3N6K-T](#) [AISC-Q0402HQ-19NG-T](#) [AISC-Q0402HQ-30NG-T](#) [AISC-Q0402HQ-18NG-T](#) [AISC-Q0402HQ-3N3C-T](#) [AISC-Q0402HQ-6N2G-T](#) [AISC-Q0402HQ-6N8G-T](#) [AISC-Q0402HQ-6N2K-T](#) [AISC-Q0402HQ-36NJ-T](#) [AISC-Q0402HQ-27NK-T](#) [AISC-Q0402HQ-21NK-T](#) [AISC-Q0402HQ-9N5G-T](#) [AISC-Q0402HQ-33NK-T](#) [AISC-Q0402HQ-2N0C-T](#) [AISC-Q0402HQ-20NG-T](#) [AISC-Q0402HQ-40NJ-T](#) [AISC-Q0402HQ-36NK-T](#) [AISC-Q0402HQ-23NJ-T](#) [AISC-Q0402HQ-5N1J-T](#) [AISC-Q0402HQ-9N0K-T](#) [AISC-Q0402HQ-4N7K-T](#) [AISC-Q0402HQ-12NK-T](#) [AISC-Q0402HQ-18NJ-T](#) [AISC-Q0402HQ-30NK-T](#) [AISC-Q0402HQ-51NJ-T](#) [AISC-Q0402HQ-39NG-T](#) [AISC-Q0402HQ-15NG-T](#) [AISC-Q0402HQ-2N7D-T](#) [AISC-Q0402HQ-25NJ-T](#) [AISC-Q0402HQ-2N4J-T](#) [AISC-Q0402HQ-16NG-T](#) [AISC-Q0402HQ-25NK-T](#) [AISC-Q0402HQ-23NK-T](#) [AISC-Q0402HQ-3N9J-T](#) [AISC-Q0402HQ-25NG-T](#) [AISC-Q0402HQ-15NJ-T](#) [AISC-Q0402HQ-2N7J-T](#) [AISC-Q0402HQ-5N1G-T](#) [AISC-Q0402HQ-39NK-T](#) [AISC-Q0402HQ-16NK-T](#) [AISC-Q0402HQ-10NJ-T](#) [AISC-Q0402HQ-2N4C-T](#) [AISC-Q0402HQ-3N9D-T](#) [AISC-Q0402HQ-7N5K-T](#) [AISC-Q0402HQ-16NJ-T](#) [AISC-Q0402HQ-30NJ-T](#) [AISC-Q0402HQ-9N5K-T](#) [AISC-Q0402HQ-21NG-T](#) [AISC-Q0402HQ-24NK-T](#) [AISC-Q0402HQ-43NG-T](#) [AISC-Q0402HQ-3N3D-T](#) [AISC-Q0402HQ-7N5J-T](#) [AISC-Q0402HQ-12NJ-T](#) [AISC-Q0402HQ-27NJ-T](#) [AISC-Q0402HQ-40NG-T](#) [AISC-Q0402HQ-2N4D-T](#) [AISC-Q0402HQ-1N0K-T](#) [AISC-Q0402HQ-3N9K-T](#) [AISC-Q0402HQ-47NK-T](#) [AISC-Q0402HQ-37NK-T](#) [AISC-Q0402HQ-19NK-T](#) [AISC-Q0402HQ-2N4K-T](#) [AISC-Q0402HQ-47NG-T](#) [AISC-Q0402HQ-51NG-T](#) [AISC-Q0402HQ-51NK-T](#) [AISC-Q0402HQ-43NJ-T](#) [AISC-Q0402HQ-10NG-T](#) [AISC-Q0402HQ-22NJ-T](#)