Unshielded Radial Power Inductor



AIUR-15 Series

Request Samples



Check Inventory (>)



20.0 x \$\phi 18.0mm **RoHS/RoHS II Compliant** MSL Level = N/A

Features

- Ferrite Core
- High Reliability

Applications

- **Switching Power Supplies**
- **Noise Filtering**
- DC to DC Converters
- **Electronic Household Appliances**
- **Buzzers and Alarm Systems**
- Television and Audio Equipment

Electrical Specifications

Part Number AIUR-15- Inductance Code	Inductance	Tolerance	DCR (Max)	I _{RATED} (Max)	Marking
Units	μH	%	Ω	A	
Symbol	L	M, K	DCR	I_{DC}	
AIUR-15-220	22	M	0.030	5.7	220M
AIUR-15-270	27	M	0.033	5.0	270M
AIUR-15-330	33	K	0.038	4.8	330K
AIUR-15-390	39	K	0.038	4.5	390K
AIUR-15-470	47	K	0.044	4.2	470K
AIUR-15-560	56	K	0.048	4.0	560K
AIUR-15-680	68	K	0.055	3.8	680K
AIUR-15-820	82	K	0.066	3.5	820K
AIUR-15-101	100	K	0.082	3.2	101K
AIUR-15-121	120	K	0.098	3.0	121K
AIUR-15-151	150	K	0.110	2.7	151K
AIUR-15-181	180	K	0.130	2.5	181K
AIUR-15-221	220	K	0.160	2.3	221K
AIUR-15-271	270	K	0.190	2.0	271K
AIUR-15-331	330	K	0.260	1.8	331K
AIUR-15-390	390	K	0.290	1.7	390K
AIUR-15-471	470	K	0.330	1.5	471K
AIUR-15-561	560	K	0.410	1.4	561K
AIUR-15-681	680	K	0.460	1.3	681K
AIUR-15-821	820	K	0.630	1.1	821K
AIUR-15-102	1000	K	0.710	1.0	102K

Test Conditions

Test frequency: 1KHz, 0.25V

 I_{RATED} : The DC current at which L drops 10% typical from its initial value or $\Delta T \le 40^{\circ}$ C,

whichever is lower.

Operating Temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (including self-heating)

Storage Temperature: -40°C ~ +125°C



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

ABRACON IS ISO9001-2015 CERTIFIED

REVISION: F 12-15-21

Unshielded Radial Power Inductor



AIUR-15 Series

Request Samples (>)




Check Inventory (>)




20.0 x \$\phi 18.0mm **RoHS/RoHS II Compliant** MSL Level = N/A

Part Number Identification



Mechanical Dimensions



A	В	С	D	Е	F	G
18 Max	20.5 Max	10 Min	3.0 Min	1.0	10	5.5 Max

Dimension: mm

Packaging:

90 pcs/tray

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



REVISION: F 12-15-21

ABRACON IS ISO9001-2015 CERTIFIED