

Is Now Part of



# **ON Semiconductor**®

# To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="https://www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="https://www.onsemi.com">Fairchild\_questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.

October 2013

TS-6P



## DFB2005 - DFB20100 Glass-Passivated Bridge Rectifiers

#### Features

- UL Certificate: # E258596
- Glass-Passivated Junction
- Ideal for Printed Circuit Board
- Reliable Low-Cost Construction
- Plastic Material has Underwriters Laboratory Flammability Classification 94V-0
- Surge Overload Rating to 250 A Peak
- High Case Dielectric Strength: 2000 V<sub>RMS</sub>
- Isolated Voltage from Case to Lead: > 2500 V

#### **Ordering Informations**

Part Number	Marking	Package	Packing Method
DFB2005	DFB2005		
DFB2010	DFB2010		
DFB2020	DFB2020		
DFB2040	DFB2040	TS-6P 4L	Rail
DFB2060	DFB2060		
DFB2080	DFB2080		
DFB20100	DFB20100	]	

1

DFB2005 - DFB20100 — Glass-Passivated Bridge Rectifiers

### Absolute Maximum Ratings<sup>(1)</sup>

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}C$  unless otherwise noted.

		Value							
Symbol	Parameter	DFB	DFB	DFB	DFB	DFB	DFB	DFB	Units
		2005	2010	2020	2040	2060	2080	20100	
V <sub>RRM</sub>	Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
V <sub>RMS</sub>	Maximum RMS Voltage	35	70	140	280	420	560	700	V
V <sub>DC</sub>	Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
I <sub>(AV)</sub>	Maximum Average Forward Rectified Current	20			А				
I <sub>FSM</sub>	Peak Forward Surge Current (8.3 ms Single Half-wave)	2		250			А		
$R_{ extsf{ heta}JC}$	Typical Thermal Resistance <sup>(2)</sup>			4.75			°C/W		
TJ	Operating Temperature Range	-55 to +150			°C				
T <sub>STG</sub>	Storage Temperature Range	-55 to +150			°C				

Notes:

1. Single-phase, half-wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.

2. Device mounted on 4 inch x 5 inch x 0.25 inch Al-plate heat sink.

## **Electrical Characteristics**

Values are at  $T_A = 25^{\circ}C$  unless otherwise specified.

Symbol	Parameter	Test condition	Value	Unit	
V <sub>F</sub>	Maximum	10 A	1.0	V	
	Instantaneous Forward Voltage	20 A	1.1		
I <sub>R</sub>	Maximum DC Reverse Current at Rated DC Blocking Voltage	T <sub>A</sub> = 25°C	10	ıιΔ	
		T <sub>A</sub> = 125°C	500	μι	
l <sup>2</sup> t	Rating for Fusing (t < 8.3 ms)	259	A <sup>2</sup> s		
CJ	Typical Junction Capacitance per l	140	pF		

Note:

3. Measured at 1 MHz and applied reverse bias of 4.0 V DC.





NOTES:

- A. THIS PACKAGE DOES NOT CONFORM TO

- A. THIS PACKAGE DOES NOT CONFORM TO ANY STANDARDS.
  B. ALL DIMENSIONS ARE IN MILLIMETERS.
  C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
  D. DRAWING FILE NAME: TS6P04AREV2



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

DFB2060 DFB2080 DFB2005 DFB2010 DFB20100 DFB2020 DFB2040