AMDLA7030S MOLDED INDUCTOR

Request Samples 🕥

Check Inventory



- **FEATURES**
- Shielded construction
- Soft saturation
- High opertating temperature up to 155°C
- Designed for switching frequencies between 100KHz-2MHz




ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE (uH)	TOLERANCE (%)	IRMS	ISAT	DC RESISTANCE (mΩ)	
	(uH)	(70)	(A)	(A)	TYP	MAX
AMDLA7030S-R15NT	0.15	30	25.0	36.0	1.7	2.1
AMDLA7030S-R22MT	0.22	20	21.0	32.0	2.0	2.5
AMDLA7030S-R33MT	0.33	20	20.0	22.0	2.8	3.4
AMDLA7030S-R36MT	0.36	20	18.0	21.0	3.3	3.9
AMDLA7030S-R47MT	0.47	20	16.0	18.0	3.4	4.0
AMDLA7030S-R56MT	0.56	20	15.0	16.0	3.9	4.5
AMDLA7030S-R68MT	0.68	20	14.5	15.0	4.7	5.3
AMDLA7030S-R82MT	0.82	20	13.0	14.0	5.4	6.0
AMDLA7030S-1R0MT	1	20	11.0	13.5	5.7	7.4
AMDLA7030S-1R2MT	1.2	20	9.5	12.5	7.7	9.5
AMDLA7030S-1R5MT	1.5	20	9.0	12.0	10.2	12.1
AMDLA7030S-2R2MT	2.2	20	7.5	9.0	13.5	15.0
AMDLA7030S-2R7MT	2.7	20	7.0	8.8	17.3	20.0
AMDLA7030S-3R3MT	3.3	20	6.0	8.5	19.0	22.0
AMDLA7030S-4R7MT	4.7	20	5.0	5.5	28.0	33.0
AMDLA7030S-5R6MT	5.6	20	5.0	5.2	39.0	42.0
AMDLA7030S-6R8MT	6.8	20	4.2	5.0	43.0	50.0
AMDLA7030S-8R2MT	8.2	20	4.0	4.7	54.0	60.0
AMDLA7030S-100MT	10	20	3.5	4.5	62.0	68.0
AMDLA7030S-150MT	15	20	2.5	4.0	110	140
AMDLA7030S-220MT	22	20	2.0	2.5	150	190
AMDLA7030S-330MT	33	20	1.8	2.0	215	258

* Please refer to Part Identification section

Test Conditions

Inductance: 100 kHz, 1 V, 0 Adc Humidity Range: 85 \pm 2% RH Temperature Rise Current: Current measured at Δ T of 40°C Saturation Current: Current measured at Δ L of 30%




GENERAL SPECIFICATIONS

Operating Temperature: -55°C to +155°C with (40°C rise) Irms current. Maximum Part Temperature: +155°C Components Storage Temperature: -55°C to +155°C Tape and Reel Packaging Temperature: -55°C to +80°C MSL: Level 1

MATERIALS


Core:	Metal Alloy
Wire:	Copper
Terminal:	Tin Plating
lnk:	Black

PRODUCT DIMENSIONS





RECOMMENDED REFLOW PROFILE




ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	T _{smin} ~ T _{smax} 150°C ~ 200°C	60 ~ 180 sec.
2	Reflow	Т _L 217°С	60 ~ 150 sec.
3	Peak Heat	т _Р 260°С	10 sec. MAX






PACKAGING

Tape and Reel:1,000Units per Carton:8,000T&R per Carton:8Weight per Carton:11.0kgWeight per Piece:0.7gCarton Dimensions:410 x 325 x 415mm



ТҮРЕ	А	В	С	D
13" x 16 mm	16.4 +2/-0	100 ± 2.0	13.5 ± 0.5	330



B	A ₀	κ _o	Р	VV	F	ļ	U
7.7 ± 0.1	7.0 ± 0.1	3.3 ± 0.1	12.0 ± 0.1	16.0 ± 0.3	7.5 ± 0.1	0.35 ± 0.05	1.5 ± 0.1

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.



Headquarters: 5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

AMDLA7030S-100MT	AMDLA7030S-1R0MT	AMDLA7030S-1R5MT	AMDLA7030S-2R2MT	AMDLA7030S-150MT
AMDLA7030S-1R2MT	AMDLA7030S-220MT	AMDLA7030S-2R7MT	AMDLA7030S-330MT	AMDLA7030S-3R3MT
AMDLA7030S-R33MT	AMDLA7030S-R36MT	AMDLA7030S-R47MT	AMDLA7030S-R56MT	AMDLA7030S-R68MT
AMDLA7030S-R82MT	AMDLA7030S-4R7MT	AMDLA7030S-5R6MT	AMDLA7030S-6R8MT	AMDLA7030S-8R2MT
AMDLA7030S-R15NT	AMDLA7030S-R22MT			