

APXG6016GH

Request Samples



Check Inventory



Ø60.0 x 16.7 mm

RoHS Compliant

MSL Level = N/A


Features

- Multiband Active GNSS
 - GPS : L1/L2/L5
 - GLONASS : G1/G2/G3
 - Galileo : E1/E5a/E5b/E6
 - BeiDou : B1/B2/B3
 - QZSS : L1/L2/L5/L6
 - SBAS : L1/L5
 - IRNSS : L5
 - L-band
- Active GNSS patch with LNA max gain of 36±2 dB
- RHCP polarization
- Small size of Ø60.0 x 16.7 mm
- Light weight
- Fully customizable RF cable and connector options

Applications

- GPS/GLONASS/Galileo/BeiDou applications
- IoT
- M2M
- Remote technology monitoring
- Geofencing
- Surveying and mapping systems
- Logistics
- UAV applications

Product Image



High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples




Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

GNSS Frequency Bands Covered

GPS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
	■	■	■	
GLONASS	G1 1598.06-1609.31MHz	G2 1242.93-1251.68MHz	G3 1202.025MHz	
	■	■	■	
Galileo	E1 1575.42MHz	E5a 1176.45MHz	E5b 1201.5MHz	E6 1278.75MHz
	■	■	■	■
BeiDou	B1 1561MHz	B2 1207.14MHz	B3 1268.52MHz	
	■	■	■	
QZSS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	L6 1278.75MHz
	■	■	■	■
IRNSS/NAVIC			L5 1176.45MHz	
			■	
SBAS	L1/E1/B1 1575.42MHz		L5/B2a/E5a 1176.45MHz	
	■		■	



Frequency allocation: GNSS systems, upper L bands and lower L bands



5101 Hidden Creek Ln Spicewood TX 78669
 Phone: 512-371-6159 | Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-06-23

ABRACON IS
 ISO9001-2015
 CERTIFIED

High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples



Check Inventory




Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Electrical Specification

Parameters	Typ.	Units	Note
Antenna			
Frequency	GPS: L1/L2/L5 GLONASS: G1/G2/G3 Galileo: E1/E5a/E5b/E6 Beidou: B1/B2/B3 QZSS: L1/L2/L5/L6 IRNSS/NAVIC: L5 SBAS: L1/E1/B1 L5/B2a/E5a L band correction service	-	
VSWR	≤ 2	-	
Polarization	RHCP	-	(Right Hand Circular Polarization)
Nominal Impedance	50	Ω	
Peak Gain	4.8	dBic	1565–1585 MHz (L1)
	5.0		1212-1242MHz (L2)
	-2.8		1166-1186MHz (L5)
Differential Propagation Delay	≤ 5	ns	
Axial Ratio	≤ 3	dB	
LNA			
Noise Figure	≤ 2	dB	
Gain	36 ± 2	dB	
Passband Ripple	± 2	dB	
Nominal Impedance	50	Ω	
VSWR	≤ 2.0	-	Max
Operating Voltage	+3.3 to 12	V	
Current Consumption	≤ 55	mA	

* With Diameter 120 mm GND Plane

High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples



Check Inventory



Ø60.0 x 16.7 mm

RoHS Compliant

MSL Level = N/A


Mechanical Specifications

Parameter	Specification
Antenna Dimension	Ø60.0 x 16.7 mm
Mounting Type	4x M2.5 Through hole screws
RF Connector	MMCX (M)

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +85°C
RoHS Compliance	Yes
ESD Sensitive	Yes
Pb free	Yes
MSL	N/A
Relative Humidity	Up to 95%

High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples



Check Inventory



Ø60.0 x 16.7 mm

RoHS Compliant

MSL Level = N/A

Ordering Information

Part Number	Description	Connector Option
APXG6016GH	High Precision GNSS Active Patch Antenna with MMCX (M) connector with 120mm cable length	MMCX (M)



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-06-23

ABRACON IS
ISO9001-2015
CERTIFIED

High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples




Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Product Dimensions



TOP VIEW

SIDE VIEW

BOTTOM VIEW

Unit: mm

Unspecified tolerance: ± 0.3 mm



APXG6016GH

Request Samples






Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Reflection Characteristics – Return Loss & VSWR





APXG6016GH

Request Samples




Check Inventory




Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A


Radiation Characteristics

Passive Peak Gain



LNA Gain





APXG6016GH

Request Samples




Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Radiation Characteristics –Efficiency





APXG6016GH

Request Samples







Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Radiation Characteristics – 3D & 2D Pattern

1575MHz (L1 Band)



High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples








Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

1227MHz (L2 Band)



High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples





Check Inventory




Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A


1176MHz (L5 Band)




XY plane



XZ plane



YZ plane



High Precision GNSS Active Patch Antenna



APXG6016GH

Request Samples



Check Inventory



Ø60.0 x 16.7 mm
RoHS Compliant
MSL Level = N/A

Packaging

60 pcs per carton

Dimension of the carton: 455 x 330 x 220 mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-06-23

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[APXG6016GH-0060S](#)