

Wireless Charging Coil Assembly

AWCCA-48R32 Series



RoHS / RoHS II Compliant



48.5 x 32.5mm

Moisture Sensitivity Level (MSL) – MSL = 1

FEATURES:

- Wireless Charging Receiver single Coil (11.1 μ H)
- Outline Dimensions: 38.5mm x 32.5mm x 1.0mm
- For Rx applications
- High permeability shielding to protect sensitive electronics
- Durable construction
- RoHS / RoHS II Compliant & Pb free.

APPLICATIONS:

- Batteries and Battery Chargers
- Consumer Electronics
- Smart Watches
- Digital Cameras and Camcorders
- Wireless Charging Stations
- Mobile Phones & Charging Accessories
- Power Supplies
- Power Tool Manufacturers

STANDARD SPECIFICATIONS

Maximum Ratings

Item	Value
Operating Temperature Range (including self-temp rise)	T= -40°C ~ 85°C
Storage Temperature (Packaging)	<40°C 60%RH (Max.)

Electrical Characteristics

Part Number	Inductance	Q-Factor	Current Rating (rms)	DC Resistance
AWCCA-48R32H11-C01-B	10.5 μ H $\pm$ 10%	23 min.	2.6A Typ.	160m Ω $\pm$ 20%
Test Condition	100KHz / 1V			

Test Conditions

A) If any doubt on the results, measurements/tests should be made within the following limits: Ambient Temperature: 20 $\pm$ 2°C, RH: 65% $\pm$ 5%

B) Irms: Base on temperature rise by 40°C Typ.

PART IDENTIFICATION:

AWCCA-48R32

H11

-

C

01

-

B

Height

H11 = 1.5mm max

Feature

C = Coil

Design Code

01

Packaging

B: Box



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-05-21

ABRACON IS
ISO9001-2015
CERTIFIED

Wireless Charging Coil Assembly

AWCCA-48R32 Series




RoHS / RoHS II Compliant



48.5 x 32.5mm

OUTLINE DIMENSIONS:



Dimensions: mm

A	B	C	D	E	F	G	H	J
32.0±0.5	28.0±1.5	12.0±1.0	48.0±0.5	37.0±1.5	21.0±1.0	50.0±2.0	10.0±2	1.5 Max

Winding Specifications

Number of Coils	Wire	Number of Turns	Inductance
1	φ0.30 x 2	13	10.5μH ±10%

Product Customization

Products can be customized according to the Wireless Charging Coil Standards or to customer requirements. Please refer to the following table for the feature ranges, and contact ABRACON or authorized distributor / agent for further details.

Inductance Range [μH]	DC Resistance Range [mΩ]	Dimension Range [mm]	Thickness range [mm]
1 ~ 100	10 ~ 1000	10 ~ 200	0.4 ~ 10

Manual Soldering: 350°C Max, 3secs

Storage condition

- Recommended storage conditions: -40°C~85°C, 70%RH (Max.)
- Recommended storage conditions (with packaging): <40°C, 60%RH

Operation Conditions

- Use condition limit: T=-40°C ~ +85°C, (including self-temperature rise).

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-05-21

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AWCCA48R32H11C01B](#) [AWCCA-48R32H11-C01-B](#)