

Features


- Tolerances down to ± 10 PPM
- Stabilities down to ± 10 PPM

STANDARD SPECIFICATIONS

PARAMETERS	MAX (Unless otherwise noted)
Frequency Range	12.000 ~ 80.000 MHz
Frequency Tolerance @ 25°C	(See options below)
Frequency Stability, ref 25°C	(See options below)
Temperature Range	
Operating (T_{OPR})	(See options below)
Storage (T_{STG})	-55°C ~ +125°C
Shunt Capacitance (C_o)	3 pF
Load Capacitance (C_L)	(See options below)
Drive Level	100 μ W
Aging per year (@ 25°C)	± 5 PPM
Maximum Soldering Temp / Time	260°C / 10 Seconds
Moisture Sensitivity Level (MSL) per J-STD-033	1
Termination Finish	Au over Ni
Seal Method	Seam
Lead (Pb) Free	Yes
RoHS Compliant	Yes

Frequency Range (MHz)	Operating Mode	Max ESR Ω
12.000 ~ 13.999999	Fundamental	200
14.000 ~ 15.999999	Fundamental	150
16.000 ~ 19.999999	Fundamental	90
20.000 ~ 23.999999	Fundamental	70
24.000 ~ 24.999999	Fundamental	60
25.000 ~ 44.999999	Fundamental	50
45.000 ~ 80.000	Fundamental	40

DIMENSIONS / MECHANICAL SPECIFICATIONS



Note: Dimensional drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, etc. may vary.

AVAILABLE OPERATING TEMPERATURES AND STABILITIES*

Operating Temperature	± 10 PPM	± 15 PPM	± 20 PPM	± 25 PPM	± 30 PPM	± 50 PPM	± 100 PPM
0°C ~ +70°C	O	O	O	O	O	O	N/A
-10°C ~ +60°C	O	O	O	O	O	O	N/A
-10°C ~ +70°C	O	O	O	O	O	O	N/A
-20°C ~ +70°C	O	O	O	O	O	O	N/A
-30°C ~ +85°C	X	O	O	O	O	O	N/A
-40°C ~ +85°C	X	O	O	O	O	O	N/A
-40°C ~ +105°C	X	X	X	X	X	O	O
-40°C ~ +125°C	X	X	X	X	X	O	O
-55°C ~ +125°C	X	X	X	X	X	O	O

Key: O = Available, X = Not Available, N/A = Not applicable *Does not imply a stocked part.

FC2BS


(Former FX252BS)

2.5mm x 2.0mm

SMD Crystal



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.55	4.0	4.0	3.5	8.0	0.65	-T3 = 3,000 -T2 = 2,000 -T1 = 1,000	2.0	ø13	ø21	ø60	ø180	9.0	2.0



Available Options & Part Identification for SMD Crystal C2BS ¹							
Sample PN: FC2BSCCDM24.0-T3							
F	C2BS	C	C	D	M	24.0	-T3
Fox	Model Number	Tolerance	Stability	Load Capacitance²	Operating Temperature	Frequency (MHz)	Values Added Options
		B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	A = ±100 PPM B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	D = 8pF W = 9pF E = 10pF G = 12pF L = 18pF M = 20pF	C = 0 to +70°C D = -10 to +60°C E = -10 to +70°C F = -20 to +70°C K = -30 to +85°C M = -40 to +85°C P = -40 to +105°C I = -40 to +125°C T = -55 to +125°C		Blank = Bulk T1 = 1,000 pcs T2 = 2,000 pcs T3 = 3,000 pcs

¹ Not all frequency, tolerance, stability, load, and operating temperature combinations may be available.

² Listed load capacitances represent the most commonly used. Other load capacitances are available. Contact us for assistance

Reliability Test Conditions
Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[FC2BSBBEM13.4916-1-T1](#) [FC2BSCCGM12.0-T3](#)