

REGULATORY COMPLIANCE

 Lead Free COMPLIANT	 EU RoHS 2011/65 + 2015/863 COMPLIANT	 China RoHS COMPLIANT	 REACH SVHC COMPLIANT	 DRC CONFLICT FREE
--	--	--	---	--


ITEM DESCRIPTION

Quartz Crystal Clock Oscillators XO (SPXO) LVCMOS (CMOS) 3.3Vdc 4 Pad 2.0mm x 2.5mm Ceramic Surface Mount (SMD)


ELECTRICAL SPECIFICATIONS

Nominal Frequency	1MHz to 50.625MHz
Frequency Tolerance/Stability	Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration ±100ppm Maximum ±20ppm Maximum ±25ppm Maximum ±50ppm Maximum
Operating Temperature Range	-10°C to +70°C -40°C to +85°C
Supply Voltage	3.3Vdc ±10%
Input Current	6mA Maximum over Nominal Frequency of 1MHz to 19.999999MHz 7mA Maximum over Nominal Frequency of 20MHz to 39.999999MHz 8mA Maximum over Nominal Frequency of 40MHz to 50.625MHz
Output Voltage Logic High (V_{OH})	I _{OH} = -4mA 90% of V _{DD} Minimum
Output Voltage Logic Low (V_{OL})	I _{OL} = +4mA 10% of V _{DD} Maximum
Rise/Fall Time	Measured at 20% to 80% of waveform 10nSec Maximum
Duty Cycle	Measured at 50% of waveform 50 ±10(%) 50 ±5(%)
Load Drive Capability	15pF Maximum
Output Logic Type	CMOS
Pin 1 Connection	Tri-State (High Impedance)
Tri-State Input Voltage (V_{IH} and V_{IL})	90% of V _{DD} Minimum or No Connect to Enable Output, 10% of V _{DD} Maximum to Disable Output (High Impedance)
Standby Current	Disabled Output: High Impedance 10µA Maximum
RMS Phase Jitter	12kHz to 20MHz offset frequency 1pSec Maximum
Start Up Time	10mSec Maximum
Storage Temperature Range	-55°C to +125°C


PART NUMBERING GUIDE



MECHANICAL DIMENSIONS



SUGGESTED SOLDER PAD LAYOUT




PIN	CONNECTION
1	Tri-State
2	Case/Ground
3	Output
4	Supply Voltage


All Tolerances are ± 0.1

All Dimensions in Millimeters

OUTPUT WAVEFORM & TIMING DIAGRAM



TEST CIRCUIT FOR CMOS OUTPUT




Note 1: An external 0.01µF ceramic bypass capacitor in parallel with a 0.1µF high frequency capacitor close (less than 2mm) to the Package ground and supply voltage pin is required.


Note 2: A low input capacitance (<12pF), 10X Attenuation Factor, High Impedance (>10Mohms), and High bandwidth (>300MHz) Passive probe is recommended.

Note 3: Capacitance value (C_L) includes sum of all probe and fixture capacitance.

Compliant to EIA-481



RECOMMENDED SOLDER REFLOW METHOD




HIGH TEMPERATURE INFRARED/CONVECTION

Ts MAX to TL (Ramp-up Rate)	3°C/Second Maximum
Preheat	
- Temperature Minimum (Ts MIN)	150°C
- Temperature Typical (Ts TYP)	175°C
- Temperature Maximum (Ts MAX)	200°C
- Time (ts)	60 - 180 Seconds
Ramp-up Rate (TL to TP)	3°C/Second Maximum
Time Maintained Above:	
- Temperature (TL)	217°C
- Time (tL)	60 - 150 Seconds
Peak Temperature (TP)	260°C Maximum for 10 Seconds Maximum
Target Peak Temperature (TP Target)	250°C +0/-5°C
Time within 5°C of actual peak (tp)	20 - 40 Seconds
Ramp-down Rate	6°C/Second Maximum
Time 25°C to Peak Temperature (t)	8 Minutes Maximum
Moisture Sensitivity Level	Level 1
Additional Notes	Temperatures shown are applied to body of device.

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

RECOMMENDED SOLDER REFLOW METHOD



LOW TEMPERATURE INFRARED/CONVECTION

T _s MAX to T _L (Ramp-up Rate)	5°C/Second Maximum
Preheat	
- Temperature Minimum (T _s MIN)	N/A
- Temperature Typical (T _s TYP)	150°C
- Temperature Maximum (T _s MAX)	N/A
- Time (t _s)	60 - 120 Seconds
Ramp-up Rate (T _L to T _P)	5°C/Second Maximum
Time Maintained Above:	
- Temperature (T _L)	150°C
- Time (t _L)	200 Seconds Maximum
Peak Temperature (T _P)	240°C Maximum
Target Peak Temperature (T _P Target)	240°C Maximum 2 Times / 230°C Maximum 1 Time
Time within 5°C of actual peak (t _p)	10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time
Ramp-down Rate	5°C/Second Maximum
Time 25°C to Peak Temperature (t)	N/A
Moisture Sensitivity Level	Level 1
Additional Notes	Temperatures shown are applied to body of device.

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[EC5600TTS-32.000M TR](#) [EC5620ETTTTS-14.31818M TR](#) [EC5600ETTTTS-4.000M TR](#) [EC5620ETTTTS-29.4912M TR](#)
[EC5620TS-3.6864M TR](#) [EC5600ETTS-7.3728M TR](#) [EC5625TTS-16.000M TR](#) [EC5625TTS-14.7456M TR](#)
[EC5620TTS-8.000M TR](#) [EC5620TTS-14.7456M TR](#) [EC5625ETTTTS-8.000M TR](#) [EC5620TTS-18.432M TR](#)
[EC5625ETTS-30.000M TR](#) [EC5600ETTS-8.000M TR](#) [EC5625TS-11.0592M TR](#) [EC5600TTS-14.31818M TR](#)
[EC5625ETTTTS-11.0592M TR](#) [EC5600ETTS-33.000M TR](#) [EC5645TTS-14.7456M TR](#) [EC5625TTS-1.8432M TR](#)
[EC5645TTS-12.352M TR](#) [EC5620ETTS-24.576M TR](#) [EC5600ETTTTS-16.384M TR](#) [EC5625TS-40.000M TR](#)
[EC5625ETTS-11.0592M TR](#) [EC5625TS-12.352M TR](#) [EC5645ETTS-12.352M TR](#) [EC5625TS-48.000M TR](#) [EC5645TS-](#)
[7.3728M TR](#) [EC5625ETTS-4.000M TR](#) [EC5600ETTS-12.352M TR](#) [EC5620TTS-12.288M TR](#) [EC5645ETTS-30.000M](#)
[TR](#) [EC5600ETTS-32.000M TR](#) [EC5600ETTTTS-24.000M TR](#) [EC5645TS-14.7456M TR](#) [EC5620TS-16.384M TR](#)
[EC5620TS-8.000M TR](#) [EC5620ETTTTS-50.000M TR](#) [EC5625TTS-12.000M TR](#) [EC5600TTS-20.000M TR](#) [EC5625TTS-](#)
[18.432M TR](#) [EC5620TS-7.3728M TR](#) [EC5645ETTS-32.000M TR](#) [EC5645TS-11.0592M TR](#) [EC5645ETTS-20.000M](#)
[TR](#) [EC5625TTS-8.000M TR](#) [EC5600TTS-27.000M TR](#) [EC5620TS-11.0592M TR](#) [EC5645TS-1.8432M TR](#)
[EC5600TS-29.4912M TR](#) [EC5645ETTTTS-14.7456M TR](#) [EC5645TS-32.000M TR](#) [EC5625TS-24.000M TR](#)
[EC5625TTS-10.000M TR](#) [EC5620TTS-4.000M TR](#) [EC5600TTS-12.352M TR](#) [EC5645TTS-50.000M TR](#) [EC5625ETTS-](#)
[1.8432M TR](#) [EC5645TS-20.000M TR](#) [EC5625ETTTTS-29.4912M TR](#) [EC5600ETTTTS-24.576M TR](#) [EC5600TS-27.000M](#)
[TR](#) [EC5600ETTTTS-8.000M TR](#) [EC5620ETTTTS-33.000M TR](#) [EC5625ETTS-24.576M TR](#) [EC5620ETTTTS-3.6864M TR](#)
[EC5625ETTTTS-32.000M TR](#) [EC5620ETTS-33.000M TR](#) [EC5620ETTTTS-10.000M TR](#) [EC5625ETTTTS-48.000M TR](#)
[EC5620TS-14.7456M TR](#) [EC5620TTS-12.000M TR](#) [EC5620TTS-10.000M TR](#) [EC5620ETTTTS-11.0592M TR](#)
[EC5620ETTTTS-16.000M TR](#) [EC5620TTS-7.3728M TR](#) [EC5625ETTS-3.6864M TR](#) [EC5645ETTTTS-24.000M TR](#)
[EC5600TTS-8.000M TR](#) [EC5620ETTS-7.3728M TR](#) [EC5620ETTS-8.000M TR](#) [EC5600TTS-24.576M TR](#)
[EC5600TTS-25.000M TR](#) [EC5620ETTS-12.000M TR](#) [EC5645TTS-4.000M TR](#) [EC5600TTS-1.8432M TR](#)
[EC5645ETTS-8.000M TR](#) [EC5620ETTTTS-40.000M TR](#) [EC5600ETTS-16.384M TR](#) [EC5620TS-25.000M TR](#)
[EC5600ETTS-40.000M TR](#) [EC5620ETTS-27.000M TR](#) [EC5620ETTS-16.384M TR](#) [EC5645TTS-8.000M TR](#)
[EC5620TTS-25.000M TR](#) [EC5645ETTS-50.000M TR](#) [EC5625ETTS-16.000M TR](#) [EC5645ETTTTS-7.3728M TR](#)
[EC5625TTS-4.000M TR](#)