

Features

- AEC-Q200 Qualified
- IATF-16949 Certified
- Temperature Ranges from -40°C to +125°C
- Supply Voltages: 1.8V, 2.5V, 3.3V

1.8V ELECTRICAL CHARACTERISTICS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (F ₀)	1.000 ~ 50.000 MHz
Temperature Range	
Storage (T _{STG})	-55°C ~ +150°C
Supply Voltage (V _{DD})	1.8V±5%
Input Current (I _{DD})	
1.000 ~ 9.999999 MHz	5 mA
10.000 ~ 31.999999 MHz	6 mA
32.000 ~ 50.000 MHz	15 mA
Standby Current (I _{ST})	
T _a = -40 ~ +85°C	10µA
T _a = -40 ~ +105°C/125°C	20µA
Output Symmetry (50% V _{DD})	40 % ~ 60 %
Rise/Fall Time (10%~90%V _{DD} Levels) (T _R /T _F)	5 nS
Output Voltage (V _{OL})	10 % V _{DD}
(V _{OH})	90 % V _{DD} Min
Output Load (HCMOS)	15 pF
Start-up Time (T _S)	10 mS
Output Disable Time ¹	100 nS
Output Enable Time ¹	10 mS

ENABLE / DISABLE FUNCTION	
Pin1	Output (pin 3)
OPEN ¹	Active
'1' Level V _{IH} ≥ 70%V _{DD}	Active
'0' Level V _{IL} ≤ 30%V _{DD}	High Z

Available Options by Stability & Operating Temp for 1.8V		
Frequency Stability	Operating Temperature (°C)	Frequency Range (MHz)
±100PPM ²	-40 ~ +85	1.000 ~ 50.000
±100PPM ²	-40 ~ +105	1.000 ~ 50.000
±100PPM ²	-40 ~ +125	1.000 ~ 50.000
±50PPM ²	-40 ~ +85	1.000 ~ 50.000
±50PPM ²	-40 ~ +105	1.000 ~ 50.000
±50PPM ²	-40 ~ +125	1.000 ~ 50.000
±25PPM ³	-40 ~ +85	1.000 ~ 50.000

¹ An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

² Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, one-year aging, shock, and vibration.

³ Inclusive of 25°C tolerance and operating temperature range.

2.5V ELECTRICAL CHARACTERISTICS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (F_0)	32.768 kHz
Temperature Range	
Storage (T_{STG})	-55°C ~ +125°C
Supply Voltage (V_{DD})	2.5V±10%
Input Current (I_{DD})	
1.000 ~ 9.999999 MHz	6 mA
10.000 ~ 31.999999 MHz	8 mA
32.000 ~ 75.000 MHz	20 mA
Standby Current (I_{ST})	
$T_a = -40 \sim +85^\circ\text{C}$	10µA
$T_a = -40 \sim +105^\circ\text{C}/125^\circ\text{C}$	20µA
Output Symmetry (50% V_{DD})	40 % ~ 60 % ⁴
Rise/Fall Time (10%~90% V_{DD} Levels) (T_R/T_F)	
1.000 ~ 49.999999 MHz	5 nS
50.000 ~ 75.000 MHz	4 nS
Output Voltage (V_{OL})	10 % V_{DD}
(V_{OH})	90 % V_{DD} Min
Output Load (HCMOS)	15 pF
Start-up Time (T_S)	10 mS
Output Disable Time ¹	100 nS
Output Enable Time ¹	10 mS

ENABLE / DISABLE FUNCTION	
Pin1	Output (pin 3)
OPEN ¹	Active
'1' Level $V_{IH} \geq 70\%V_{DD}$	Active
'0' Level $V_{IL} \leq 30\%V_{DD}$	High Z

Available Options by Stability & Operating Temp for 2.5V		
Frequency Stability	Operating Temperature (°C)	Frequency Range (MHz)
±100PPM ²	-40 ~ +85	1.000 ~ 75.000
±100PPM ²	-40 ~ +105	1.000 ~ 75.000
±100PPM ²	-40 ~ +125	1.000 ~ 75.000
±50PPM ²	-40 ~ +85	1.000 ~ 75.000
±50PPM ²	-40 ~ +105	1.000 ~ 75.000
±50PPM ²	-40 ~ +125	1.000 ~ 75.000
±25PPM ³	-40 ~ +85	1.000 ~ 75.000

¹ An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

² Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, one-year aging, shock, and vibration.

³ Inclusive of 25°C tolerance and operating temperature range.

⁴ 45/55 Symmetry available on an inquiry basis

3.3V ELECTRICAL CHARACTERISTICS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (F_0)	1.000 ~ 135.000 MHz
Temperature Range Storage (T_{STG})	-55°C ~ +150°C
Supply Voltage (V_{DD})	3.3V±10%
Input Current (I_{DD})	
1.000 ~ 19.999999 MHz	7 mA
20.000 ~ 31.999999 MHz	12 mA
32.000 ~ 49.999999 MHz	20 mA
50.000 ~ 79.999999 MHz	25 mA
80.000 ~ 99.999999 MHz	30 mA
100.000 ~ 135.000 MHz	40 mA
Standby Current (I_{ST})	
$T_a = -40 \sim +85^\circ\text{C}$	10µA
$T_a = -40 \sim +105^\circ\text{C}/125^\circ\text{C}$	20µA
Output Symmetry (50% V_{DD})	40 % ~ 60 % ⁴
Rise/Fall Time (10%~90% V_{DD} Levels) (T_R/T_F)	
1.000 ~ 49.999999 MHz	10 nS
50.000 ~ 79.999999 MHz	8 nS
80.000 ~ 99.999999 MHz	5 nS
100.000 ~ 135.000 MHz	4 nS
Output Voltage (V_{OL})	10 % V_{DD}
(V_{OH})	90 % V_{DD} Min
Output Load (HCMOS)	15 pF
Start-up Time (T_S)	10 mS
Output Disable Time ¹	100 nS
Output Enable Time ¹	10 mS

ENABLE / DISABLE FUNCTION	
Pin1	Output (pin 3)
OPEN ¹	Active
'1' Level $V_{IH} \geq 70\%V_{DD}$	Active
'0' Level $V_{IL} \leq 30\%V_{DD}$	High Z


Available Options by Stability & Operating Temp for 3.3V		
Frequency Stability	Operating Temperature (°C)	Frequency Range (MHz)
±100PPM ²	-40 ~ +85	1.000 ~ 135.000
±100PPM ²	-40 ~ +105	1.000 ~ 135.000
±100PPM ²	-40 ~ +125	1.000 ~ 135.000
±50PPM ²	-40 ~ +85	1.000 ~ 135.000
±50PPM ²	-40 ~ +105	1.000 ~ 135.000
±50PPM ²	-40 ~ +125	1.000 ~ 135.000
±25PPM ³	-40 ~ +85	1.000 ~ 135.000

¹ An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

² Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, one-year aging, shock, and vibration.

³ Inclusive of 25°C tolerance and operating temperature range.

⁴ 45/55 Symmetry available on an inquiry basis



STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Maximum Soldering Temp / Time	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL)	N/A
Termination Finish	Au (0.3~1μm) over Ni (1.27~8.89μm)
Seal Method	Seam
Lead (Pb) Free	Yes
ROHS Compliant	Yes, no exemptions
ROHS/REACH Compliant (latest version)	Yes


FO5HA

(Former FA510, FA530, FA540)

5mm x 3.2mm
HCMOS SMD Oscillator



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.55	4.0	8.0	5.5	12.0	1.5	-T1 = 1,000	2.0	ø13	ø21	ø62	ø180	13.5	2.0



Available Options & Part Identification*

Sample PN: **FO5HACBM25.0**

F	O5HA	C	B	M	25.0	-T1
Fox	Model Number	Voltage C = 3.3V±10% H = 2.5V±5% K = 1.8V±5%	Stability A = ±100 PPM B = ±50 PPM D = ±25 PPM	Operating Temperature M = -40 to +85°C P = -40 to +105°C I = -40 to +125°C	Frequency (MHz)	Values Added Options Blank = Bulk T1 = 1,000 pcs

*Not all frequencies in the frequency range, or every combination of stability, temp range, and voltage available

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[FO5HACAI16.0-T1](#) [FO5HACBI16.0-T1](#) [FO5HACBI12.0-T1](#) [FO5HACBI50.0-T1](#) [FO5HACBP50.0-T1](#)
[FO5HACDM25.0-T1](#) [FO5HACDM25.0-BULK](#) [FO5HACBI16.384-T1](#)