

# CERAMIC SMD CRYSTAL

**ABM8**

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive-MSL = N/A: Not Applicable



**RoHS**  
Compliant



3.2 x 2.5 x 0.8mm

## FEATURES:

- Seam sealed package assures high reliability
- Tight tolerance and stability available
- Suitable for RoHS reflow

## APPLICATIONS:

- High density applications
- Modems, communication and test equipment
- PCMCIA, Wireless applications


## STANDARD SPECIFICATIONS:

| Parameters                                                          | Minimum                                                                              | Typical | Maximum  | Units | Notes                                                              |
|---------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------|----------|-------|--------------------------------------------------------------------|
| Frequency Range                                                     | 8.000                                                                                |         | 125.000* | MHz   | Contact Abracon for available F<10MHz                              |
| Operation Mode                                                      | Fundamental                                                                          |         |          |       | 8MHz - 54MHz                                                       |
|                                                                     | 3rd Overtone<br>(Standard Frequencies: 64, 66, 66.6666, 75, 80, 98.304, 100, 125MHz) |         |          |       | 64MHz - 125MHz<br>Please contact Abracon for available frequencies |
| Operating Temperature                                               | -10                                                                                  |         | +60      | °C    | Standard<br>(see options if other than STD)                        |
| Storage Temperature                                                 | -55                                                                                  |         | +125     | °C    |                                                                    |
| Frequency Tolerance @+25°C                                          | -50                                                                                  |         | +50      | ppm   | Standard<br>(see options if other than STD)                        |
| Frequency Stability over the Operating Temperature ( ref. to +25°C) | -50                                                                                  |         | +50      | ppm   | Standard<br>(see options if other than STD)                        |
| Equivalent series resistance (R1)                                   | See table 1 below                                                                    |         |          | Ω     |                                                                    |
| Shunt capacitance (C0)                                              |                                                                                      |         | 3.0      | pF    |                                                                    |
| Load capacitance (CL)                                               |                                                                                      | 18.0    |          | pF    | Standard (See options if other than STD)                           |
| Drive Level                                                         |                                                                                      | 10      | 100      | μW    |                                                                    |
| Aging                                                               | -2                                                                                   |         | +2       | ppm   | @25°C±3°C<br>First year                                            |
| Insulation Resistance                                               | 500                                                                                  |         |          | MΩ    | @ 100Vdc ± 15V                                                     |

TABLE 1- Standard ESR

| Frequency (MHz)        | ESR(Ω)<br>max | Frequency (MHz)           | ESR(Ω)<br>max |
|------------------------|---------------|---------------------------|---------------|
| 8.000-9.999 (Fund)     | 400           | 30.000 - 39.999 (Fund)    | 40            |
| 10.000 -11.999 (Fund)  | 200           | 40.000 - 54.000 (Fund)    | 35            |
| 12.000 -15.999 (Fund)  | 120           | 64.000 - 80.000 (3rd OT)  | 120           |
| 16.000 -19.999 (Fund)  | 70            | 98.304 - 125.000 (3rd OT) | 80            |
| 20.000 - 29.999 (Fund) | 50            |                           |               |

## OPTIONS AND PART IDENTIFICATION: (Left blank if standard)



# CERAMIC SMD CRYSTAL

ABM8



RoHS  
Compliant



3.2 x 2.5 x 0.8mm

## OUTLINE DRAWING:





Table 2


| Height (mm) |             |
|-------------|-------------|
| ABM8        | 0.80 max    |
| ABM81       | 0.65+/-0.05 |
| ABM82       | 0.60+/-0.10 |

**Note:** Due to material availability, the chamfer could be located on pin #1, 3, or 4. Be advised that the chamfer location has no impact on the electrical performance of the device.

Dimensions: mm


## TAPE & REEL:

- Option "-T" : Tape and reel (1,000pcs/reel) : ABM8, ABM82  
Tape and reel (3,000pcs/reel) : ABM81
- Option "-T2" : Tape and reel (250pcspcs/reel) : ABM8
- Option "-T3" : Tape and reel (3,000pcs/reel) : ABM8, ABM82 only



Dimensions: mm

## REFLOW PROFILE:



| Zone | Description | Temperature                                            | Time          |
|------|-------------|--------------------------------------------------------|---------------|
| 1    | Preheat     | T <sub>SMIN</sub> ~ T <sub>SMAX</sub><br>150°C ~ 180°C | 60 ~ 120 sec. |
| 2    | Reflow      | T <sub>L</sub><br>230°C                                | 30 ~ 40 sec.  |
| 3    | Peak heat   | T <sub>P</sub><br>260°C ± 5°C                          | 10 sec. MAX   |

**ATTENTION:** Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## [ABRACON:](#)

[ABM8-18.432MHZ-B2-T](#) [ABM8-25.000MHZ-B2-T](#) [ABM8-28.63636MHZ-B2-T](#) [ABM8-33.000MHZ-B2-T](#) [ABM8-24.000MHZ-B2-T](#) [ABM8-44.000MHZ-B2-T](#) [ABM8-24.576MHZ-B2-T](#) [ABM8-16.000MHZ-B2-T](#) [ABM8-22.1184MHZ-B2-T](#) [ABM8-27.000MHZ-B2-T](#) [ABM8-29.4912MHZ-B2-T](#) [ABM8-48.000MHZ-B2-T](#) [ABM8-40.000MHZ-B2-T](#) [ABM8-30.000MHZ-B2-T](#) [ABM8-20.000MHZ-B2-T](#) [ABM8-28.375MHZ-B2-T](#) [ABM8-16.3676MHZ-10-1-U-T](#) [ABM8-16.800MHZ-10-1-U-T](#) [ABM8-19.200MHZ-10-1-U-T](#) [ABM8-24.5535MHZ-10-1-U-T](#) [ABM8-26.000MHZ-10-1-U-T](#) [ABM8-13.000MHZ-10-1-U-T](#) [ABM8-14.7456MHZ-10-1-U-T](#) [ABM8-16.000MHZ-10-1-U-T](#) [ABM8-16.384MHZ-10-1-U-T](#) [ABM8-20.000MHZ-10-1-U-T](#) [ABM8-24.576MHZ-10-1-U-T](#) [ABM8-27.000MHZ-10-1-U-T](#) [ABM8-30.000MHZ-10-1-U-T](#) [ABM8-36.000MHZ-10-1-U-T](#) [ABM8-40.000MHZ-10-1-U-T](#) [ABM8-27.0000MHZ-10-B1-U-T](#) [ABM8-14.31818MHZ-B2-T](#) [ABM8-16.384MHZ-B2-T](#) [ABM8-13.000MHZ-B2-T](#) [ABM8-32.000MHZ-B2-T](#) [ABM8-12.000MHZ-B2-T](#) [ABM8-156-20.000MHZ-T](#) [ABM8-32.000MHZ-10-1-U](#) [ABM81-25.000MHz-10-B1U-T3](#) [ABM81-27.120MHz-10-B1U-T3](#) [ABM81-14.31818MHz-B4Y-T3](#) [ABM81-30.000MHz-10-D1U-T3](#) [ABM81-36.000MHz-B4Y-T3](#) [ABM81-25.000MHz-B4Y-T3](#) [ABM81-32.000MHz-10-B1U-T3](#) [ABM81-16.000MHz-10-B1U-T3](#) [ABM81-24.000MHz-10-B1U-T3](#) [ABM81-48.000MHz-B4Y-T3](#) [ABM81-16.934MHz-B4Y-T3](#) [ABM81-26.000MHz-B4Y-T3](#) [ABM81-24.000MHz-B4Y-T3](#) [ABM81-40.000MHz-B4Y-T3](#) [ABM81-20.000MHz-B4Y-T3](#) [ABM81-38.400MHz-B4Y-T3](#) [ABM81-30.000MHz-B4Y-T3](#) [ABM81-12.000MHz-10-B1U-T3](#) [ABM81-24.576MHz-B4Y-T3](#) [ABM81-27.000MHz-B4Y-T3](#) [ABM81-19.200MHz-B4Y-T3](#) [ABM81-32.000MHz-B4Y-T3](#) [ABM81-16.000MHz-B4Y-T3](#) [ABM8-12.000-B2-T3](#) [ABM8-13.000-B2-T3](#) [ABM8-18.432-B2-T3](#) [ABM8-16.000-B2-T3](#) [ABM8-28.63636-B2-T3](#) [ABM8-32.000-B2-T3](#) [ABM8-44.000-B2-T3](#) [ABM8-30.000-B2-T3](#) [ABM8-12.288-B2-T3](#) [ABM8-14.31818-B2-T3](#) [ABM8-20.000-B2-T3](#) [ABM8-24.000-R60-D-1-W-T3](#) [ABM8-25.000-B2-T3](#) [ABM8-27.000-B2-T3](#) [ABM8-48.000-B2-T3](#) [ABM8-22.1184-B2-T3](#) [ABM8-19.200-B2-T3](#) [ABM8-29.4912-B2-T3](#) [ABM8-24.576-B2-T3](#) [ABM8-16.384-B2-T3](#) [ABM8-40.000-B2-T3](#) [ABM8-33.000-B2-T3](#) [ABM8-24.000-B2-T3](#) [ABM8-28.375-B2-T3](#) [ABM8-166-114.285MHZ-T2](#) [ABM8-24.000MHZ-R60-D-1-W-T](#) [ABM8-24.000MHZ-B2-T3](#) [ABM8-28.63636MHZ-B2-T3](#) [ABM8-32.000MHZ-B2-T3](#) [ABM8-37.500MHZ-12-1-U-T](#) [ABM8-18.080MHZ-10-R60-E-1-U-T](#) [ABM8-12.288MHZ-B2-T](#) [ABM8-19.200MHZ-B2-T](#) [ABM8-24.000MHZ-D2-T](#) [ABM8-25.000MHZ-D2Y-T](#) [ABM8-25.000MHZ-10-D1G-T](#) [ABM8-14.31818MHZ-D2Y-T](#) [ABM8-16.000MHZ-7-1-U-T](#)