

FEATURES

- 2.0mm Height Max
- Internal Trim
- Clipped Sine Output
- Tape and Reel (1,000 pcs. STD)



OPTIONS

- 5.0V
- 3.0V


ELECTRICAL CHARACTERISTICS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (F ₀)	9.600 ~ 50.000 MHz
Temperature Range	
Operating (T _{OPR})	-30°C ~ +75°C
Storage (T _{STG})	-35°C ~ +80°C
Initial Frequency Tolerance (@25°C)	
V _C = 1.5V (V _{DD} = 3.0V)	±0.5PPM
V _C = 2.5V (V _{DD} = 5.0V)	
Supply Voltage (V _{DD})	5.0V ± 5%
	3.0V ± 5%
Input Current (I _{DD})	
9.600 ~ 21.999MHz	2.0mA
21.999+ ~ 27.999 MHz	3.0mA
27.999+ ~ 39.999 MHz	4.0mA
39.999+ ~ 50.000 MHz	5.0mA
Frequency Stability	
Over Temperature Range	±2.5PPM
Over Supply Voltage Change (V _{DD} ± 5%)	
9.600 ~ 21.999 MHz	±0.3PPM
21.999+ ~ 27.999 MHz	±0.5PPM
27.999+ ~ 50.000 MHz	±1.0PPM
Over Load Change (10KΩ ± 10% // 10pF ± 10%)	±0.3PPM
Output Waveform (Clipped Sine)	
Peak to Peak Level (V _{p-p})	
5.0V Version: 9.600 ~ 15.999 MHz	1.0V Min
5.0V Version: 16.000 ~ 50.000 MHz	0.8V Min
3.0V Version: 9.600 ~ 15.999 MHz	0.8V Min
3.0V Version: 16.000 ~ 50.000 MHz	0.7V Min
Output Load	10KΩ // 10pF ±10%
Frequency Adjustment (Internal Trimmer)	±3.0PPM Min
Voltage Control Option (VCTCXO) ¹	±5.0PPM Min
(V _C =1.5±1.0V, V _{DD} = 3.0V)	
(V _C =2.5±1.0V, V _{DD} = 5.0V)	
Aging per year	1.0PPM

¹ For proper operation, a control voltage (V_C) must be applied to pin 1 on VCTCXOs
All specifications subject to change without notice.

DIMENSIONS / MECHANICAL SPECIFICATIONS



Recommended Solder Pad Layout



Pin Connection


#1 V _c	#3 Output
#2 GND	#4 V _{DD}

FT9CV

(Former FOX801AELF/ FOX801BELF Series)

11.4mm x 9.6mm
Clipped Sine, VCTCXO **FOX**

TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
Ø1.5	4.0	12.0	11.5	24.0	2.7	1,000	2.0	Ø13	Ø21	Ø80	Ø330	25.5	1.6



Available Options & Part Identification for VCTCXO Model T9CV¹

Sample PN: **FT9CVDPH25.0-T1**

F	T9CV	D	P	H	25.0	-T1
Fox	Model Number T9CV = VCTCXO	Voltage D = +3V±5% P = +5V±5%	Stability P = ±2.5 PPM	Operating Temperature H = -30 to +75°C	Frequency (MHz)	Values Added Options Blank = Bulk T1 = 1,000 pcs

Note 1: Not all frequencies in the frequency range, or every combination of stability, temp range, and voltage available

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[FOX801BELF-192](#) [FOX801BELF-144](#) [FOX801BELF-160](#) [FOX801BELF-100](#) [FOX801BELF-1280](#) [FOX801BELF-12.288](#) [FOX801BELF-200](#)