


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/18/06	R. Hazelwood
B	REVISED PER ECO 5825	11/4/08	J. Kordik
C	REVISED PER ECO 6098	5/17/10	J. Kordik



WIRE CONNECTION

P1		P2
2	BLUE	3
3	GREEN	5
5	ORANGE	2

NOTES: UNLESS OTHERWISE SPECIFIED

TEST REQUEST:

1. OPEN SHORT 100%
2. CT ≤ 1 OHM IS ≥ 2M OHM.

1. THIS CABLE ASSY TO BE MANUFACTURED IN COMPLIANCE WITH EU DIRECTIVE "ROHS 2002/95/EC".
2. BAG AND TAG PER MANUFACTURING REQUIREMENTS.

ITEM LIST	
①	DB 9P FEMALE CONNECTOR SHELL: FRONT NICKEL, BACK TIN INSULATOR COLOR: BLACK
②	CABLE: CAT-5 UTP 24 OR 26 AWG COLOR: BLACK
③	RJ11 6P4C PLATED GOLD 3U
④	SCREW: #4-40 UNC PD40-175TNP COLOR: BLACK
⑤	DB9 CONNECTOR OVERMOLDED WITH PVC, 65P. PE COATING.
⑥	SCREW OVERMOLDED WITH PVC, 30P, COLOR: BLACK.

TOLERANCES		THIRD ANGLE PROJECTION		APPLIED MOTION PRODUCTS, INC.	
DECIMALS: MM (INCH)					
X.XXX = ± (.005)					
X.XX = ±0.13 (.010)		APPROVALS	DATE	PROGRAMMING CABLE	
X.X = ±0.25 (.020)		DRAWN <i>R. Hazelwood</i> CHECKED	5/18/06		
ANGLES:		APPROVED		B	DWG NO. 3004-189
MACH. = ±.5°				C	REV C
CHAM. = ±5°				SCALE: NONE SHEET 1 OF 1	
COMPUTER DATA BASE DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Applied Motion:](#)

[3004-189](#)