

SPECIFICATIONS:	
STEPS PER REVOLUTION: 200	ROTOR INERTIA: 38.0 G-CM ² (0.20 OZ-IN ²) REF
STEP ANGLE: 1.8°	DETENT TORQUE: 122.3 G-CM (1.69 OZ-IN) MIN
STEP TO STEP ACCURACY: ±.09 DEGREES [1], [2]	INSULATION CLASS: B
POSITIONAL ACCURACY: ±.09 DEGREES [1], [3]	BEARINGS: ABEC 3, DOUBLE SHIELDED
HYSTERESIS: - %	WEIGHT: 210 G (7.3 OZ) APPROXIMATE
SHAFT RUNOUT: 0.03 T.I.R.	TEMP. RISE: 80 °C MAX. [8]
RADIAL PLAY: 0.02 MAX W/A .5KG RADIAL LOAD	OPERATING TEMP. RANGE: -20 TO +50 °C
END PLAY: 0.08 MAX W/A 0.5KG AXIAL LOAD	STORAGE TEMP. RANGE: -30 TO +70 °C
	RELATIVE HUMIDITY RANGE: 15 TO 85 %

[7]						
SPECIFICATION CONNECTION	NUMBER OF PHASE	RESISTANCE PER PHASE OHM ±10%	INDUCTANCE PER PHASE mH ±20%	RATED CURRENT Amp	RATED VOLTAGE V	HOLDING TORQUE N.m Min [1]
BI-POLAR SERIES	2	8.4	10.0	0.67	5.6	0.22
BI-POLAR PARALLEL	2	2.1	2.5	1.34	2.8	0.22
UNI-POLAR	4	4.2	2.5	0.95	4.0	0.16

HT17-268

REVISIONS				
ECO NO.	REV	DESCRIPTION	DATE	APPROVED
5976	A	INITIAL RELEASE	8/28/09	J.KORDIK
5995	B	PERPENDICULARITY CORRECTED	9/28/09	J.KORDIK
6090	C	STANDARDIZE ENCODER HOLES	3/29/10	J.KORDIK
7247	D	ADD UL TO LABEL	1/26/16	J.KORDIK
7446	E	REVISE NOTE 10	6/6/16	J.KORDIK
8209	F	CLEAN-UP	4/29/19	J.KORDIK
8277	G	REMOVE ENCODER HOLES	7/3/19	J.KORDIK

NOTES, UNLESS OTHERWISE SPECIFIED:


- [1] MEASUREMENTS MADE AT RATED CURRENT IN EACH PHASE.
- [2] BETWEEN ANY TWO ADJACENT STEP POSITIONS.
- [3] MAXIMUM ERROR IN 360°.
4. HIPOT 500 VAC, 60 Hz FOR ONE MINUTE.
5. LEADS: 8, 26 AWG, 7 STRAND MIN., UL AND CSA APPROVED, UL 1430 OR UL 3265.
6. INSULATION RESISTANCE: 100 MEGOHMS MIN AT 500 VDC.
- [7] AS MEASURED USING AN A.C. INDUCTANCE BRIDGE, AT 1KHz.
- [8] AS MEASURED BY THE CHANGE IN RESISTANCE METHOD, WITH RATED VOLTAGE APPLIED TO 2 PHASES; WITH MOTOR AT REST.
- [9] SHAFT OPTION: IF DOUBLE SHAFT REQUIRED ADD "D" TO END OF PART NUMBER, DOUBLE SHAFT REQUIRES ADDED HOLES FOR ENCODER OPTION.
10. THIS MOTOR IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
- [11] MOTOR LABEL TO INCLUDE "ROHS" COMPLIANT, 'MADE IN (COUNTRY OF ORIGIN)' AND DATE CODE.

DRIVE SEQUENCE MODEL
BI-POLAR FULL STEP


STEP	ORANGE & BLK/WHT	BLACK & ORG/WHT	RED & YEL/WHT	YELLOW & RED/WHT	
1	+	-	+	-	↓ CW ↑ CCW
2	-	+	+	-	
3	-	+	-	+	
4	+	-	-	+	

CW(CLOCKWISE) AND CCW(COUNTER-CLOCKWISE) ROTATION
WHEN SEEN FROM THE FLANGE SIDE OF THE MOTOR

WIRING DIAGRAM





LABEL DETAIL



CONTRACT NO. -				
APPROVALS	DATE	STEP MOTOR OUTLINE		
DRAWN R.JONEZ	8/19/09			
CHECKED		B COMPUTER DATA BASE DRAWING DWG NO. HT17-268 REV G		
APPROVED				
APPROVED		SCALE: NONE		SHEET 1 OF 2

MOTOR DRAWING



TOLERANCES		THIRD ANGLE PROJECTION		 APPLIED MOTION PRODUCTS, INC.	
DECIMALS: MM (INCH) X.XXX= ±0.013 (.005) X.XX = ±0.25 (.01) X.X = ±2.5 (0.1) ANGLES: MACH. = ±.5° CHAM. = ±5°					
APPROVALS		DATE		STEP MOTOR OUTLINE	
DRAWN <i>R. JONEZ</i>		8/19/09			
CHECKED				B	REV G
COMPUTER DATA BASE DRAWING		APPROVED		DWG NO. HT17-268	
				SCALE: NONE	
				SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Applied Motion:](#)

[HT17-268D](#)