



## RF Power GaN Transistor

This 59 W RF power GaN transistor is designed for cellular base station applications covering the frequency range of 2110 to 2170 MHz.

This part is characterized and performance is guaranteed for applications operating in the 2110 to 2170 MHz band. There is no guarantee of performance when this part is used in applications designed outside of these frequencies.

### 2100 MHz

- Typical Single-Carrier W-CDMA Performance:  $V_{DD} = 48$  Vdc,  $I_{DQ} = 500$  mA,  $P_{out} = 59$  W Avg., Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF.


| Frequency | $G_{ps}$<br>(dB) | $\eta_D$<br>(%) | Output PAR<br>(dB) | ACPR<br>(dBc) |
|-----------|------------------|-----------------|--------------------|---------------|
| 2110 MHz  | 18.0             | 37.0            | 7.0                | -33.3         |
| 2140 MHz  | 18.0             | 36.9            | 7.0                | -33.3         |
| 2170 MHz  | 18.1             | 37.0            | 6.9                | -32.3         |

### Features


- High terminal impedances for optimal broadband performance
- Designed for digital predistortion error correction systems
- Optimized for Doherty applications

**A3G20S350-01S**

**2110–2170 MHz, 59 W Avg., 48 V  
AIRFAST RF POWER GaN  
TRANSISTOR**



**NI-400S-2SA**



**Figure 1. Pin Connections**

**Table 1. Maximum Ratings**

| Rating                                                  | Symbol     | Value       | Unit             |
|---------------------------------------------------------|------------|-------------|------------------|
| Drain-Source Voltage                                    | $V_{DS}$   | 125         | Vdc              |
| Gate-Source Voltage                                     | $V_{GS}$   | –8, 0       | Vdc              |
| Operating Voltage                                       | $V_{DD}$   | 0 to +55    | Vdc              |
| Maximum Forward Gate Current @ $T_C = 25^\circ\text{C}$ | $I_{GMAX}$ | 24          | mA               |
| Storage Temperature Range                               | $T_{stg}$  | –65 to +150 | $^\circ\text{C}$ |
| Case Operating Temperature Range                        | $T_C$      | –55 to +150 | $^\circ\text{C}$ |
| Operating Active Die Surface Temperature Range          | $T_J$      | –55 to +225 | $^\circ\text{C}$ |
| Maximum Channel Temperature <sup>(1)</sup>              | $T_{CH}$   | 275         | $^\circ\text{C}$ |

**Table 2. Thermal Characteristics**

| Characteristic                                                                                                                        | Symbol                 | Value               | Unit               |
|---------------------------------------------------------------------------------------------------------------------------------------|------------------------|---------------------|--------------------|
| Thermal Resistance by Infrared Measurement, Active Die Surface-to-Case<br>Case Temperature $83^\circ\text{C}$ , $P_D = 89.8\text{ W}$ | $R_{\theta JC}$ (IR)   | 0.64 <sup>(2)</sup> | $^\circ\text{C/W}$ |
| Thermal Resistance by Finite Element Analysis, Channel-to-Case<br>Case Temperature $83^\circ\text{C}$ , $P_D = 89.8\text{ W}$         | $R_{\theta CHC}$ (FEA) | 1.01 <sup>(3)</sup> | $^\circ\text{C/W}$ |

**Table 3. ESD Protection Characteristics**

| Test Methodology                      | Class |
|---------------------------------------|-------|
| Human Body Model (per JS-001-2017)    | 1B    |
| Charge Device Model (per JS-002-2014) | C3    |

**Table 4. Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|----------------|--------|-----|-----|-----|------|
|----------------|--------|-----|-----|-----|------|

**Off Characteristics**

|                                                                                     |             |   |   |      |      |
|-------------------------------------------------------------------------------------|-------------|---|---|------|------|
| Off-State Drain Leakage<br>( $V_{DS} = 150\text{ Vdc}$ , $V_{GS} = -8\text{ Vdc}$ ) | $I_{D(BR)}$ | — | — | 35.0 | mAdc |
|-------------------------------------------------------------------------------------|-------------|---|---|------|------|

**On Characteristics**

|                                                                                                               |              |      |      |      |      |
|---------------------------------------------------------------------------------------------------------------|--------------|------|------|------|------|
| Gate Threshold Voltage<br>( $V_{DS} = 10\text{ Vdc}$ , $I_D = 10\text{ mAdc}$ )                               | $V_{GS(th)}$ | –3.8 | –3.0 | –2.3 | Vdc  |
| Gate Quiescent Voltage<br>( $V_{DD} = 48\text{ Vdc}$ , $I_D = 500\text{ mAdc}$ , Measured in Functional Test) | $V_{GS(Q)}$  | –3.7 | –2.9 | –2.3 | Vdc  |
| Gate-Source Leakage Current<br>( $V_{DS} = 150\text{ Vdc}$ , $V_{GS} = -8\text{ Vdc}$ )                       | $I_{GSS}$    | –9.9 | —    | —    | mAdc |

1. Reliability tests were conducted at  $225^\circ\text{C}$ . Operations with  $T_{CH}$  at  $275^\circ\text{C}$  will reduce median time to failure.

2. Refer to AN1955, *Thermal Measurement Methodology of RF Power Amplifiers*. Go to <http://www.nxp.com/RF> and search for AN1955.

3.  $R_{\theta CHC}$  (FEA) must be used for purposes related to reliability and limitations on maximum channel temperature. MTTF may be estimated by the expression  $MTTF\text{ (hours)} = 10^{[A + B/(T + 273)]}$ , where  $T$  is the channel temperature in degrees Celsius,  $A = -10.3$  and  $B = 8263$ .

(continued)

**Table 4. Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise noted) (continued)

| Characteristic                                                                                                                                                                                                                                                                                                                                                                                                            | Symbol   | Min  | Typ   | Max   | Unit |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------|-------|-------|------|
| <b>Functional Tests</b> <sup>(1)</sup> (In NXP Production Test Fixture, 50 ohm system) $V_{DD} = 48\text{ Vdc}$ , $I_{DQ} = 500\text{ mA}$ , $P_{out} = 59\text{ W Avg.}$ , $f = 2170\text{ MHz}$ , Single-Carrier W-CDMA, IQ Magnitude Clipping, Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF. ACPR measured in 3.84 MHz Channel Bandwidth @ $\pm 5\text{ MHz}$ Offset. [See note on correct biasing sequence.] |          |      |       |       |      |
| Power Gain                                                                                                                                                                                                                                                                                                                                                                                                                | $G_{ps}$ | 17.0 | 18.1  | 19.5  | dB   |
| Drain Efficiency                                                                                                                                                                                                                                                                                                                                                                                                          | $\eta_D$ | 34.8 | 37.0  | —     | %    |
| $P_{out}$ @ 3 dB Compression Point, CW                                                                                                                                                                                                                                                                                                                                                                                    | P3dB     | 54.2 | 54.7  | —     | dBm  |
| Adjacent Channel Power Ratio                                                                                                                                                                                                                                                                                                                                                                                              | ACPR     | —    | -32.3 | -30.3 | dBc  |

**Wideband Ruggedness** (In NXP Production Test Fixture, 50 ohm system)  $I_{DQ} = 500\text{ mA}$ ,  $f = 2140\text{ MHz}$ , Additive White Gaussian Noise (AWGN) with 10 dB PAR

|                                                                                                                           |                       |
|---------------------------------------------------------------------------------------------------------------------------|-----------------------|
| ISBW of 400 MHz at 55 Vdc, 191 W Avg. Modulated Output Power (3 dB Input Overdrive from 11 W Avg. Modulated Output Power) | No Device Degradation |
|---------------------------------------------------------------------------------------------------------------------------|-----------------------|

**Typical Performance** (In NXP Production Test Fixture, 50 ohm system)  $V_{DD} = 48\text{ Vdc}$ ,  $I_{DQ} = 500\text{ mA}$ , 2110–2170 MHz Bandwidth

|                                                                                                    |                    |   |       |   |       |
|----------------------------------------------------------------------------------------------------|--------------------|---|-------|---|-------|
| $P_{out}$ @ 3 dB Compression Point <sup>(2)</sup>                                                  | P3dB               | — | 410   | — | W     |
| AM/PM<br>(Maximum value measured at the P3dB compression point across the 2110–2170 MHz bandwidth) | $\Phi$             | — | -15   | — | °     |
| VBW Resonance Point<br>(IMD Third Order Intermodulation Inflection Point)                          | VBW <sub>res</sub> | — | 70    | — | MHz   |
| Gain Flatness in 60 MHz Bandwidth @ $P_{out} = 59\text{ W Avg.}$                                   | $G_F$              | — | 0.2   | — | dB    |
| Gain Variation over Temperature<br>(-40°C to +85°C)                                                | $\Delta G$         | — | 0.018 | — | dB/°C |
| Output Power Variation over Temperature<br>(-40°C to +85°C)                                        | $\Delta P_{1dB}$   | — | 0.001 | — | dB/°C |

**Table 5. Ordering Information**

| Device          | Tape and Reel Information                             | Package     |
|-----------------|-------------------------------------------------------|-------------|
| A3G20S350-01SR3 | R3 Suffix = 250 Units, 32 mm Tape Width, 13-inch Reel | NI-400S-2SA |


- Part internally input matched.
- P3dB =  $P_{avg} + 7.0\text{ dB}$  where  $P_{avg}$  is the average output power measured using an unclipped W-CDMA single-carrier input signal where output PAR is compressed to 7.0 dB @ 0.01% probability on CCDF.

**NOTE: Correct Biasing Sequence for GaN Depletion Mode Transistors****Turning the device ON**

- Set  $V_{GS}$  to the pinch-off voltage, typically -5 V.
- Turn on  $V_{DS}$  to nominal supply voltage (+48 V).
- Increase  $V_{GS}$  until  $I_{DS}$  current is attained.
- Apply RF input power to desired level.

**Turning the device OFF**

- Turn RF power off.
- Reduce  $V_{GS}$  down to the pinch-off voltage, typically -5 V.
- Adjust drain voltage  $V_{DS}$  to 0 V. Allow adequate time for drain voltage to reduce to 0 V from external drain capacitors.
- Turn off  $V_{GS}$ .





aaa-038560

**Figure 2. A3G20S350-01S Production Test Circuit Component Layout**

**Table 6. A3G20S350-01S Production Test Circuit Component Designations and Values**

| Part                 | Description                                 | Part Number         | Manufacturer |
|----------------------|---------------------------------------------|---------------------|--------------|
| C1                   | 10 pF Chip Capacitor                        | 100B100JT500XT      | ATC          |
| C2, C5, C8, C11, C13 | 9.1 pF Chip Capacitor                       | 600F9R1BT250XT      | ATC          |
| C3, C6, C7, C14      | 10 $\mu$ F Chip Capacitor                   | C5750X7S2A106M230KB | TDK          |
| C4                   | 1.6 pF Chip Capacitor                       | 600F1R6BT250XT      | ATC          |
| C9                   | 0.6 pF Chip Capacitor                       | 600F0R6BT250XT      | ATC          |
| C10                  | 0.8 pF Chip Capacitor                       | 600F0R8BT250XT      | ATC          |
| C12                  | 0.3 pF Chip Capacitor                       | 600F0R3BT250XT      | ATC          |
| C15                  | 220 $\mu$ F, 100 V Electrolytic Capacitor   | MCGPR100V227M16X26  | Multicomp    |
| R1, R2               | 15 $\Omega$ , 1/4 W Chip Resistor           | CRCW120615R0FKEA    | Vishay       |
| PCB                  | Rogers RO4350B, 0.020", $\epsilon_r = 3.66$ | D134491             | MTL          |

# PACKAGE INFORMATION



|                                                   |                                 |                            |
|---------------------------------------------------|---------------------------------|----------------------------|
| © NXP SEMICONDUCTORS N. V.<br>ALL RIGHTS RESERVED | MECHANICAL OUTLINE              | PRINT VERSION NOT TO SCALE |
| TITLE:<br><br>NI-400S-2SA                         | DOCUMENT NO: 98ASA01061D REV: 0 |                            |
|                                                   | STANDARD: NON-JEDEC             |                            |
|                                                   | SOT1828-3                       | 05 MAR 2018                |

NOTES:

1. CONTROLLING DIMENSION: INCH

2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

3. DIMENSION H IS MEASURED .030 INCH (0.762 MM) AWAY FROM THE FLANGE TO CLEAR THE EPOXY FLOW OUT REGION PARALLEL TO DATUM B.

4. INPUT & OUTPUT LEADS (PIN 1 & 2) MAY HAVE SMALL FEATURES SUCH AS SQUARE HOLES OR NOTCHES FOR MANUFACTURING CONVENIENCE.

| BB                                               | INCH  |       | MILLIMETER         |       | DIM                                                                | INCH                       |     | MILLIMETER |     |
|--------------------------------------------------|-------|-------|--------------------|-------|--------------------------------------------------------------------|----------------------------|-----|------------|-----|
|                                                  | MIN   | MAX   | MIN                | MAX   |                                                                    | MIN                        | MAX | MIN        | MAX |
| AA                                               | .395  | .405  | 10.03              | 10.29 | aaa                                                                | .005                       |     | 0.13       |     |
| DIM                                              | .382  | .388  | 9.70               | 9.86  | bbb                                                                | .010                       |     | 0.25       |     |
| CC                                               | .125  | .163  | 3.18               | 4.14  | ccc                                                                | .015                       |     | 0.38       |     |
| D                                                | .275  | .285  | 6.98               | 7.24  |                                                                    |                            |     |            |     |
| E                                                | .031  | .041  | 0.79               | 1.04  |                                                                    |                            |     |            |     |
| F                                                | .004  | .006  | 0.10               | 0.15  |                                                                    |                            |     |            |     |
| H                                                | .057  | .067  | 1.45               | 1.70  |                                                                    |                            |     |            |     |
| K                                                | .0995 | .1295 | 2.53               | 3.29  |                                                                    |                            |     |            |     |
| M                                                | .395  | .405  | 10.03              | 10.29 |                                                                    |                            |     |            |     |
| N                                                | .385  | .395  | 9.78               | 10.03 |                                                                    |                            |     |            |     |
| R                                                | .355  | .365  | 9.02               | 9.27  |                                                                    |                            |     |            |     |
| S                                                | .365  | .375  | 9.27               | 9.53  |                                                                    |                            |     |            |     |
| © NXP SEMICONDUCTORS N.V.<br>ALL RIGHTS RESERVED |       |       | MECHANICAL OUTLINE |       |                                                                    | PRINT VERSION NOT TO SCALE |     |            |     |
| TITLE:<br><br>NI-400S-2SA                        |       |       |                    |       | DOCUMENT NO: 98ASA01061D                      REV: 0               |                            |     |            |     |
|                                                  |       |       |                    |       | STANDARD: NON-JEDEC                                                |                            |     |            |     |
|                                                  |       |       |                    |       | SOT1828-3                                              05 MAR 2018 |                            |     |            |     |

## PRODUCT DOCUMENTATION, SOFTWARE AND TOOLS

Refer to the following resources to aid your design process.

### Application Notes

- AN1908: Solder Reflow Attach Method for High Power RF Devices in Air Cavity Packages
- AN1955: Thermal Measurement Methodology of RF Power Amplifiers

### Software

- .s2p File

### Development Tools

- Printed Circuit Boards

## REVISION HISTORY

The following table summarizes revisions to this document.

| Revision | Date      | Description                                                                     |
|----------|-----------|---------------------------------------------------------------------------------|
| 0        | Aug. 2020 | <ul style="list-style-type: none"><li>• Initial release of data sheet</li></ul> |

### ***How to Reach Us:***

**Home Page:**  
nxp.com

**Web Support:**  
nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: [nxp.com/SalesTermsandConditions](http://nxp.com/SalesTermsandConditions).

NXP, the NXP logo and Airfast are trademarks of NXP B.V. All other product or service names are the property of their respective owners.

© 2020 NXP B.V.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NXP:

[A3G20S350-01SR3](#)