## AP101 100W TO-247 High Power Resistors FIRCUL

- 100 watts at 25°C case temperature heat sink mounted
- TO-247 style power package
- Single screw mounting to heat sink
- Moulded case for protection
- Electrically isolated case
- Non-Inductive design
- RoHS Compliant



#### **Characteristics**

Tolerance (Code):  $\pm 1\%$  (F),  $\pm 5\%$  (J),  $\pm 10\%$  (K)

Operating temperature: -65°C to +175°C

Temperature coefficient: ± 50ppm/°C to ± 300ppm/°C (re to ohmic values), referenced to 25°C, ΔR taken at +105°C

Operating voltage: 700V max

Dielectric strength: 1800Vac 60 seconds, ΔR±0.15%

Insulation resistance: 10G min Maximum torque: 0.9 Nm

Free air: 25°C, rated at 3.5W

Load Life ΔR±1.0%, Rated power, 2,000 hours
Solderability 90% min. coverage, 245±5°C for 3 seconds

Momentary Overload  $\Delta R \pm 0.5\%$ , 1.5 times rated power and V (dc)  $\leq$  1.5 VMax. for 5 seconds

Moisture resistance  $\Delta R \pm 0.5\%$ , -10°C - +65°C, RH>90%, cycle 240 hours

Thermal Shock  $\Delta R \pm 0.5\%$ , -65°C - 150°C, 100 cycles

Terminal Strength  $\Delta R \pm 0.2\%$ , (Pull Test) 2.4N Vibration, High Frequency  $\Delta R \pm 0.4\%$ , 20g peak

## **Ordering Procedure**


<u>Standard Resistor:</u> Series, Resistance Value, Tolerance Code, TCR

eg: AP101 10K J 50ppm

#### **Electrical Specifications**

	Value Range	Tolerance Pref. Value Range	TCR (ppm/°C)
	R05 - 1R	± 1% (F)	Not specified
	> 1R - 3R	E12, E24, E96	± 300ppm/°C
	> 3R - 10R	± 5% (J)	± 100ppm/°C, ± 200ppm/°C
	> 10R - 100K	E12, E24	± 50ppm/°C, ± 100ppm/°C, ± 200ppm/°C
		± 10% (K)	
		E12	

## **Derating Curve**



The case temperature is to be used for the definition of the applied power limit

The case temperature measurement must be made with a thermocouple contacting
the centre of the component mounted on the designed heat sink

Thermal grease should be applied properly

ARCOL UK Limited,

Threemilestone Ind. Estate,

Truro, Cornwall, TR4 9LG, UK.

T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com


www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. Arcol operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask Arcol.

Page 1 of 2 201118

# AP101 100W TO-247 High Power Resistors



ARCOL UK Limited, Threemilestone Ind. Estate, Truro, Cornwall, TR4 9LG, UK. T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. Arcol operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask Arcol.

Page 2 of 2 201118

#### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Ohmite:

AP101 82R J 100PPM AP101 5K J 100PPM AP101 56R F 50PPM AP101 3R9 J 100PPM AP101 68R J 100PPM AP101 2K2 F 50PPM AP101 150R J 100PPM AP101 8R2 J 100PPM AP101 390R F 50PPM AP101 680R F 50PPM AP101 1K J 100PPM AP101 3K3 F 50PPM AP101 100R F 50PPM AP101 2K7 F 50PPM AP101 33R F 50PPM AP101 470R F 50PPM AP101 220R F 50PPM AP101 390R J 100PPM AP101 27R J 100PPM AP101 100R J 100PPM AP101 25R F 50PPM AP101 2R7 F AP101 R07 J AP101 820R F 50PPM AP101 10R J 100PPM AP101 3R3 J 100PPM AP101 560R J 100PPM AP101 33R J 100PPM AP101 15R J 100PPM AP101 560R F 50PPM AP101 1K5 F 50PPM AP101 8K2 F 50PPM AP101 8R2 F 50PPM AP101 1R2 F AP101 5R J 100PPM AP101 68R F 50PPM AP101 39R F 50PPM AP101 R08 J AP101 270R F 50PPM AP101 680R J 100PPM AP101 1K2 J 100PPM AP101 180R F 50PPM AP101 4R7 F 100PPM AP101 6R8 F 50PPM AP101 56R J 100PPM AP101 27R F 50PPM AP101 1K F 50PPM AP101 330R F 50PPM AP101 4R7 J 100PPM AP101 5K F 50PPM AP101 R3 J AP101 2R5 J AP101 10R F 50PPM AP101 12R F 50PPM AP101 270R J 100PPM AP101 4K7 F 50PPM AP101 47R J 100PPM AP101 39R J 100PPM AP101 470R J 100PPM AP101 5R F 50PPM AP101 R8 J AP101 50R J 100PPM AP101 5R6 J 100PPM AP101 12R J 100PPM AP101 120R F 50PPM AP101 10K J 100PPM AP101 5R6 F 50PPM AP101 5K6 J 100PPM AP101 180R J 100PPM AP101 1K2 F 50PPM AP101 50R F 50PPM AP101 22R F 50PPM AP101 47R F 50PPM AP101 18R F 50PPM AP101 5K6 F 50PPM AP101 2R2 F AP101 6K8 F 50PPM AP101 150R F 50PPM AP101 3K9 F 50PPM AP101 1R8 F AP101 82R F 50PPM AP101 2R5 F AP101 R4 J AP101 820R J 100PPM AP101 R6 J AP101 R06 J AP101 2K7 J 100PPM AP101 2K2 J 100PPM AP101 2K5 J 100PPM AP101 25R J 100PPM AP101 220R J 100PPM AP101 10K F 50PPM AP101 22R J 100PPM AP101 3K3 J 100PPM AP101 1K5 J 100PPM AP101 8K2 J 100PPM AP101 3K9 J 100PPM AP101 330R J 100PPM AP101 1K8 F 50PPM AP101 6K8 J 100PPM