



This tool kit provides everything you need to measure power and provide a stable light source for fiber optic cable testing. This kit includes:

- The FPM-55 Fiber Optic Power Meter for measuring wavelengths from 800-1650 nm, with a mere 0.01 dB resolution
 - Measures 6 preset calibrated wavelengths with high precision to determine absolute or relative power
 - Stores up to 1,000 data entries which can be downloaded via USB
 - Includes FC/SC adapters for APC/PC/UPC connectors and an LC adapter for PC/UPC connectors only
- The FLS-55 Fiber Optic Light Source for providing a stable light source at 850/1300 nm for multimode or 1310/1550 nm wavelengths singlemode fiber measurements
 - Has four different modulation outputs (CW, 270 Hz, 1 kHz, 2 kHz) at 1310 nm and 1550 nm wavelengths
 - Includes FC, SC, and LC adapters to directly connect to UPC/PC FC, SC, and LC fiber connectors
- A FREE BAG! The H-22 Rugged Carrying Case with Straps (\$35 value)!
- Nylon Carry Case (FPM-55)
- Storage Pouch (FLS-55)
- With both the FPM-55 and FLS-55
 - Instruction Manuals
 - (3) AA Batteries each (required for operation)
 - (2) Cleaning Swabs each
 - FC Adapter, LC Adapter, and SC Adapters

SPECIFICATIONS	
DIMENSIONS	11.13" x 9.13" x 6.63" (28.3 cm x 23.2 cm x 16.8 cm)
UPC #	810053352083



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[FPL-5555](#)