



The Jonard Tools FC-600 precision fiber cleaver is designed to provide a precise, one step cleave to prepare fiber to be fusion spliced. This fiber cleaver features the following:

- One step design automatically cleaves the fiber, rotates the blade, and collects fiber scraps
- Provides a cleave with a cutting angle of less than 0.5° for optimal fiber preparation for fusion splicing
- Blade automatically rotates after each cleave, and can be used for 52,000 cleaves before needing to be replaced
- Lightweight and rugged design for long term durability
- Holds 250 μ m and 900 μ m fiber and comes with built in fiber trash can
- Scaled holder for accurate cleave lengths from 5 to 20 mm (0.20" to 0.79")
- Ideal for fiber technicians, fiber splicers, and anyone that needs to cleave a fiber optic cable prior to performing a fusion splice

SPECIFICATIONS	
CLEAVE LENGTH	5 mm-20 mm (Single Fiber 0.25 mm Coating), 12 mm-20 mm (Single Fiber 0.9 mm Coating)
CLEAVE ANGLE	Less than 0.5°
BLADE LIFE	52,000 cleaves
PRODUCT MAIN COLOR	Black
DIMENSIONS	4.72" x 4.02" x 2.76" (12 cm x 10.2 cm x 7 cm)
WEIGHT	1.05 lb (476.7 g)
UPC #	810053351413



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[FC-600](#)