

SA-9-E-115 - Fume Absorber, ESD Safe 115V - Data Sheet

Smoke Absorber / Fume Absorber - ESD safe. The SA-9-E-115 model Fume Absorber features a static-dissipative housing. This SA Series Smoke Absorber features an Aerodynamic hood design which effectively draws irritating soldering fumes away from the work area. Carbon-impregnated filters trap a limited portion of the flux fumes. Compact size, low profile and adjustable stand allows convenient placement 6" to 8" (152 to 203mm) from work area.

Specifications

- Input Voltage: 115v / 60Hz
- Max Air Volume: 105 to 126 CFM
- Noise Level: 45-50 dB (A)
- Motor HP: 15-17 Watt
- Motor RPM: 3000
- Activated Carbon Wt.: 12g



Specifications	
Includes	3 Filters
Activated Carbon Weight	12 grams
Maximum Air Volume	105 to 126 CFM
Noise Level	45-50 dB (A)
Voltage	115V (60Hz)
Features	Static-dissipative housing. Aerodynamic Hood. Compact Size.
Material	ESD Safe Housing
Dimensions	8-1/2" (H) x 8-1/4" (W) x 4" (D)
Weight	3.603 lbs
UPC No.	811490010215

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[SA-9-E-115](#)