


G5Q-EL/-EL2/-EL3

PCB Power Relay

A Miniature Power Relay with high performance

- IEC/EN 60335-1 conformed.
- Coil insulation system: class F (UL1446)
- [Type G5Q-EL]
 - Higher performance compare with G5Q standard type.
 - Minimum 100,000 operations durability at 10 A (250 VAC) switching.
- [Type G5Q-EL2]
 - High inrush capacity performance (Inrush current 40 A).
 - UL508 TV3 conformed.
- [Type G5Q-EL3]
 - Ideal for motor switching 3 A with high inrush 30 A
 - IEC/EN 60079-15 conformed.



Model Number Legend

G5Q-□□□-□□□
 1 2 3 4 5 6

1. Number of Pole

1 : 1-pole

2. Contact Form

A : SPST-NO (1a)

3. Enclosure rating

None : Flux protection
 (-EL type only)

4 : Fully sealed
 (-EL2, -EL3)

4. Classification

EL : For Resistive load

EL2 : For Inrush load

EL3 : For Motor load

5. Market Code

HA : Home Appliance according
 to IEC/EN60335-1

6. Case Vent Hole

None : No vent hole

VH : Vent hole (-EL type only)

Application Examples

- Home appliances
- Building automation
- Lighting control
- Output of control system
- FA I/O module

G5Q-EL/-EL2/-EL3

Ordering Information

Classification	Contact form	Enclosure rating	Model	Rated coil voltage	Minimum packing unit
-EL type (For Resistive load)	SPST-NO (1a)	Flux protection (Vent hole type)	G5Q-1A-EL-HA-VH	5 VDC 12 VDC 24 VDC	100 pcs/tray
-EL2 type (For Inrush load)	SPST-NO (1a)	Sealed	G5Q-1A4-EL2-HA	5 VDC 12 VDC 24 VDC	
-EL3 type (For Motor load)	SPST-NO (1a)	Sealed	G5Q-1A4-EL3-HA	5 VDC 12 VDC 24 VDC	

Note 1. When ordering, add the rated coil voltage to the model number.

Example: G5Q-1A4-EL2-HA DC12

Rated coil voltage

Note 2. Contact your OMRON sales representative for tube packing models.

Ratings

Coil

Rated voltage	Rated current (mA)	Coil resistance (Ω)	Must operate voltage (V)	Must release voltage (V)	Max. voltage (V)	Power consumption (mW)
			% of rated voltage			
5 VDC	80.0	63	75% max.	5% min.	190% (at 23°C)	Approx. 400
12 VDC	33.3	360				
24 VDC	16.7	1440				

Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

Note 2. The operating characteristics are measured at a coil temperature of 23°C.

Note 3. The "Max. voltage" is the maximum voltage that can be applied to the relay coil.

Note 4. 5 VDC of coil rated voltage is available only for -EL3

●Contacts

Item	Load	-EL type (For Resistive load)	-EL2 type (For Inrush load)	-EL3 type (For Motor load)
		SPST-NO (1a)		
		Flux protection	Sealed	Sealed
Contact type	Single			
Contact material	Ag-Alloy (Cd free)			
Rated load	Resistive load: 10 A at 250 VAC		Capacitive load: Inrush 40 A (100 μs) / 1 A break at 250 VAC	Motor load: Inrush 30 A (0.5 s) / 3 A break cosφ=0.5 at 250 VAC
Rated carry current	10 A			
Max. rated voltage	277 VAC			
Max. rated current	10 A AC			


■Characteristics

Item		Classification	-EL type (For Resistive load)	-EL2 type (For Inrush load)	-EL3 type (For Motor load)
Contact resistance *1			100 mΩ max.		
Operate time			10 ms max.		
Release time			5 ms max.		
Insulation resistance *2			1,000 MΩ min. (at 500 VDC)		
Dielectric strength	Between coil and contacts		4,000 VAC, 50/60 Hz for 1 min		
	Between contacts of the same polarity		1,000 VAC, 50/60 Hz for 1 min		
Impulse withstand voltage	Between coil and contacts		8 kV (1.2 x 50 μs)		
Vibration resistance	Destruction		10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)		
	Malfunction		10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)		
Shock resistance	Destruction		1,000 m/s ²		
	Malfunction		100 m/s ²		
Durability	Mechanical		10,000,000 operations (18,000 operations per hour)		
	Electrical		Resistive load 100,000 operations at 23°C (operation: ON for 1 sec. OFF for 9 sec.)	Capacitive load 100,000 operations at 23°C (operation: ON for 1 sec. OFF for 3 sec.)	Motor load 300,000 operations at 23°C (operation: ON for 1 sec. OFF for 1 sec.)
Failure rate (P level) (reference *3)			10 mA at 5 VDC		
Ambient operating temperature			-40°C to 85°C (with no icing or condensation)		
Ambient operating humidity			5% to 85%		
Weight			Approx. 6.5 g		


Note. Values in the above table are the initial values at 23°C.
*1. The contact resistance is possible with 1 A applied at 5 VDC using a fall-of-potential method.
*2. Testing conditions: The insulation resistance was measured with a 500 VDC megohmmeter at the same locations as the electric strength was measured.
*3. This value was measured at switching frequency of 120 operation/min.

■Engineering Data

●Maximum Switching Capacity (AC)




●Ambient Temperature VS. Maximum Coil Voltage



Note. The Maximum coil voltage refers to the maximum value in a varying of operating power voltage, not a continuous voltage.

●Shock Malfunction



Actual Load Life (Reference Values)

G5Q-1A4-EL2-HA

120 VAC Capacitive load

Inrush: 56 A (0-P), Break: 0.2 A (rms)

200,000 operations min. (Ambient temperature: 23°C)

G5Q-1A4-EL3-HA

250 VAC Inductive load

Inrush: 30 A (0-P)/ 0.5 s, Break: 1.7 A (rms)

500,000 operations min. (Ambient temperature: 30°C)


Dimensions

(Unit: mm)


G5Q-1A-EL-HA-VH

G5Q-1A4-EL2-HA

G5Q-1A4-EL3-HA



Terminal Arrangement/
Internal Connections
(Bottom View)



(No coil polarity)

Approved Standards

UL Recognized: (File No. E41515)

CSA Certified: (File No. LR31928)

Model	Coil ratings	Contact ratings	Number of test operations
G5Q-1A-EL-HA-VH	5, 12, 24 VDC	10 A 250 VAC Resistive 40°C	6,000
G5Q-1A4-EL2-HA	5, 12, 24 VDC	5 A 250 VAC Resistive 85°C	6,000
		TV-3 40°C	25,000
		1 A 120 VAC 30 A Inrush-max. 1 msec 85°C	25,000
G5Q-1A4-EL3-HA	5, 12, 24 VDC	10 A 250 VAC Resistive 40°C	50,000
		1/2HP 250 VAC 40°C	50,000
		1/6HP 125 VAC 40°C	50,000

EN/IEC, VDE (Certified/No.40009467)

Model	Coil ratings	Contact ratings	Number of test operations
G5Q-1A-EL-HA-VH	5, 12, 24 VDC	10 A 250 VAC ($\cos\phi=1$) 105°C	10,000
G5Q-1A4-EL2-HA	5, 12, 24 VDC	5 A 250 VAC ($\cos\phi=1$) 85°C	10,000
		Peak inrush 30 A / Break 1 A 230 VAC 85°C	25,000
G5Q-1A4-EL3-HA	5, 12, 24 VDC	3 A 250 VAC ($\cos\phi=0.4$) 85°C	50,000

Creepage distance	6.4 mm min.
Clearance distance	5.5 mm min.
Insulation material group	IIIa
Type of insulation coil-contact circuit open contact circuit	Reinforced Micro disconnection
Rated Insulation voltage	250 V
Pollution degree	2
Rated voltage system	250 V
Over voltage category	III
Category of protection according to IEC 61810-1	RT II (Flux protection) / RT III (Sealed)
Glow wire according to IEC 60335-1 ed.5	GWT 750°C min. (IEC 60695-2-11) / GWFI 850°C min. (IEC 60695-2-12)
Tracking resistance according to IEC 60112	PTI 250 V min. (housing parts)
Flammability class according to UL94	V-0
Coil Insulation system	F Class (UL 1446)

Precautions

●Please refer to "PCB Relays Common Precautions" for correct use.



G
5
Q
-
E
L
/
-
E
L
2
/
-
E
L
3

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact	
Americas https://components.omron.com/us	Europe https://components.omron.com/eu
Asia-Pacific https://components.omron.com/ap	China https://components.omron.com.cn
Korea https://components.omron.com/kr	Japan https://components.omron.com/jp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Omron:](#)

[G5Q-1A4-EL3-HA DC12](#)