CS-series CompoNet Master Units CS1W-CRM21

CS-series CompoNet Master Units Increase the Range of Applicability of Sensors and Actuators.

• The CS-series CompoNet Master Unit manages the CompoNet network, controls communications between the PLC and Slave Units, and handles I/O data and message data.




CS1W-CRM21

Features

- Setup is simple. Make the master's mode settings and set the baud rate, and you're ready to go.
- Control up to 2,560 points and 384 nodes with one Master Unit.
- Intuitive memory mapping with separate areas for Word Slave Units and Bit Slave Units.
- Seven-segment display helps with startup and enables prompt detection of problems.
- Collect information from Slave Units using message communications, or use message communications to set parameters.
- Inherits the ease of use of the CompoBus/S.
- Flexible I/O allocations with software setting function.

System Configuration



Communication Specifications


Item	Specification			
Communications protocol	CompoNet Network protocol			
Types of communications	Remote I/O communications (programless, constant sharing of data with Slave Units) and message communications (explicit message communications as required with Slave Units and FINS message communications as required with PLCs)			
Baud rate	4 Mbits/s *1, 3 Mbits/s, 1.5 Mbits/s, 93.75 kbits/s			
Modulation	Base-band			
Coding	Manchester code			
Error control	Manchester code rules, CRC			
Communications media	The following media can be used. *2 Round cable I (JIS C 3306, 2-conductor 0.75 mm ²) Round cable II (JIS C3306 4-conductor 0.75 mm ²) Flat Cable I (DCA4-4F10 Standard Flat Cable) Flat Cable II (DCA5-4F10 Sheathed Flat Cable)			
Communications distance and wiring	Refer to Cable Types, Baud Rates, and Maximum Distances on page 3.			
Connectable Master Units	CompoNet Master Units			
Connectable Slave Units	CompoNet Slave Units			
Maximum I/O capacity	Word Slave Units: 1,024 inputs and 1,024 outputs (2,048 I/O points total) Bit Slave Units: 256 inputs and 256 outputs (512 I/O points total)			
Maximum number of nodes	Word Slave Units: 64 input nodes and 64 output nodes Bit Slave Units: 128 input nodes and 128 output nodes Repeater Units: 64 nodes			
Bits allocated per node address	Word Slave Units: 16 bits Bit Slave Units: 2 bits			
Maximum number of nodes per trunk line or sub-trunk line	32 nodes (including Repeater Units)			
Applicable node addresses	Word Slave Units: IN0 to IN63 and OUT0 to OUT63 Bit Slave Units: IN0 to IN127 and OUT0 to OUT127 Repeater Units: 0 to 63			
Repeater Unit application conditions	Up to 64 Repeater Units can be connected per network. When Repeater Units are connected in series from the Master Unit, up to 2 extra segment layers can be created (i.e., up to 2 Repeater Units are allowed between a Slave Unit and the Master Unit).			
Signal lines	Two lines: BDH (communications data high) and BDL (communications data low)			
Power lines	Two lines: BS+ and BS– (power for communications and internal Slave Unit circuits) • Power is supplied from the Master Unit or Repeater Units.			
Communications power supply	24 VDC ±10%			
Connection forms	Flat Cable at baud rate of 93.75 kbits/s: No restrictions Other cables or baud rates: Trunk line and branch lines			
	Connections for Slave Units and Repeater Units: T-branch or multidrop connections			
Remote I/O communications	 Automatic startup when power is turned ON *3 or manual startup using the Remote I/O Communications Start Switch in I/O Communications Manual Start Mode. In Registered Slave Unit Participation Standby Mode, communications is not started until all registered Slave Units are participating in the network. In Communications Error Communications Stop Mode, communications stop when a communications error occurs. 			
I/O communications manual startup mode	I/O Communications Manual Startup Mode can be set from the CX-Integrater so that remote I/O communications are not started when the power is turned ON. Remote I/O communications will not start until the Remote I/O Communications Start Switch is turned ON in memory.			
Communications error communications stop mode	All remote I/O communications are stopped if a communications error occurs in any Slave Unit. *4			
Communications error input data zero clear mode	All input data will be cleared to zeros in any Slave Unit in which a communications error occurs.			
Duplicated Slave address check If the same address is set for two different Slave Units or the same memory is allocated to two nodes, the Slave Unit that joins communications last will cause a duplicated address error and with the network. The Duplicated Address Error Flag will turn ON.				
Registration table The Slave Units that can participate for each node address are registered in a table s registered Slave Units can participate. If a different Slave Unit attempts to join the ner Registration Table Verification Error Flag will turn ON. The Registration Table is generated automatically or manually edited from Support Software.				

	Item	Specification
Slave Unit status	Without registration table	 Participation Flag and Communications Error Flag for each Slave Unit Participation Flag: Turns ON and remains ON if the Slave Unit joins the network even one time after system power is turned ON. Communications Error Flag: Turns ON if the Slave Unit cannot communicate with the Master Unit for any reason after the Slave Unit has joined the network (i.e., if the Participation Flag is ON). (Turns OFF when the error is removed.) Duplicated Address Error Flags and Alarm Flags
	With registration table	 Participation Flags and Communications Error Flags for each node address for all Slave Units registered in the Registration Table Registration Table Verification Error Flags All Registered Slave Units Participating Flag

- Note: 1. Drop-line connections are not supported with a baud rate of 4 Mbits/s, so Slaves with prewired cables (Bit Slaves) cannot be used.
 Round cable, Flat Cable, and Flat Cable II are all different types of cable. To use more than one type of cable at a time, Repeater Units must be used to separate them on trunk lines and sub-trunk lines.
 - 3. When power is turned ON to the PLC and the Slave Unit communications power is turned ON. Communications are not started in the following cases:
 - 4. Communications will not stop for verification errors for registration tables or duplicated address settings.
 - 5. This error will also occur if a Slave Unit leaves the network and then a different type of Slave Unit joins the network.
 - 6. The Registered Slave Unit Participation Monitoring Time can be set (verification error check timing).
 - Registered Slave Unit Participation Standby Mode can be set. (Remote I/O communications will not start until all registered Slave Units are participating.)

Cable Types, Baud Rates, and Maximum Distances

This section provides specifications on the maximum cable length and maximum number of nodes for each type of cable. Do not exceed these specifications.



Restrictions (at Baud Rate of 4 Mbits/s (No Branch Lines))

Cable type	Maximum length per segment (maximum length with Repeater Units)	Branch line length	Total branch line length per segment	Branch location restrictions	Maximum number of Slave Units per segment *2
Round cable I	30 m (90 m)	0 m *1	0 m *1	-	32 nodes
Flat Cable I and Flat Cable II Round Cable II	30 m (90 m)	90 m) 0 m *1 0 m *1 –		-	32 nodes

***1.** T-branches cannot be connected (only multidrop connections are possible).

***2.** Number of nodes including Repeater Units

Restrictions (at Baud Rate of 3 Mbits/s)

Cable type	Maximum length per segment (maximum length with Repeater Units)	Branch line length	Total branch line length per segment	Branch location restrictions	Maximum number of nodes per branch *1	Sub-branch line length	Total sub- branch line length per segment	Maximum number of Slave Units per segment *2
Round cable I	30 m (90 m)	0.5 m	8 m	3 branches/m	1 node	0 m	0 m	32 nodes
Flat Cable I and Flat Cable II Round Cable II	30 m (90 m)	0.5 m	8 m	3 branches/m	1 node	0 m	0 m	32 nodes

*1. The maximum number of nodes per branch is the maximum number of Slave Units or Repeater Units that can be connected to one branch line using multidrop or T-branch connections (sub-branches).

***2.** Number of nodes including Repeater Units

Restrictions (at Baud Rate of 1.5 Mbits/s)

	Cable type	Maximum length per segment (maximum length with Repeater Units)	Branch line length	Total branch line length per segment	Branch location restrictions	Maximum number of nodes per branch *1	Sub-branch line length	Total sub- branch line length per segment	Maximum number of Slave Units per segment *2
Round	Without branches	100 m (300 m)	0 m *3	0 m *3	-	-	-	-	32 nodes
cable I	With branches	30 m (90 m)	2.5 m	25 m	3 branches/m	3 nodes	0 m	0 m	32 nodes
Flat Cab Round C	le I and Flat Cable II Cable II	30 m (90 m)	2.5 m	25 m	3 branches/m	3 nodes	0.1 m *4	2 m *4	32 nodes

***1.** The maximum number of nodes per branch is the maximum number of Slave Units or Repeater Units that can be connected to one branch line using multidrop or T-branch connections (sub-branches).

*2. Number of nodes including Repeater Units

*3. T-branches cannot be connected (only multidrop connections are possible).

***4.** T-branch connections from sub-branch lines.

Restrictions (at Baud Rate of 93.75 kbits/s)

Cable type	Maximum length per segment (maximum length with Repeater Units)	Branch line length	Total branch line length per segment	Branch location restrictions	Maximum number of nodes per branch *1	Sub-branch line length	Total sub- branch line length per segment	Maximum number of Slave Units per segment *2
Round cable I	500 m (1500 m)	6 m	120 m	3 branches/m	1 node	-	-	32 nodes
Flat Cable I and Flat Cable II Round Cable II	No restrictions to a total length per segment of 200 m					32 nodes		

***1.** The maximum number of nodes per branch is the maximum number of Slave Units or Repeater Units that can be connected to one branch line using multidrop or T-branch connections (sub-branches).

*2. Number of nodes including Repeater Units

Ordering Information

International Standards

• The standards are abbreviated as follows: U: UL, U1: UL(Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, and CE: EC Directives.

• Contact your OMRON representative for further details and applicable conditions for these standards.

Nama	A	Speci	fications	Number of unit	Power consumption (A)		Model	Standards
Name	Appearance	Type of communications	Maximum number of I/O points per Master Unit	numbers allocated	5-V system	26-V system	Model Standa	Standards
CS1 Special I/O Unit		Remote I/O communications Message communications	Word Slave Units: 1,024 inputs and 1,024 outputs (2,048 I/O points total) Bit Slave Units: 256 inputs and 256 outputs (512 I/O points total)	1, 2, 4, or 8	0.4	_	CS1W-CRM21	CE, U, U1, L, N

	Specifications				
Product name		Number of licenses	Media	Model	Standards
CX-One FA Integrated Tool Package Ver. 4.⊡	The CX-One is a package that integrates the Support Software for OMRON PLCs and components. CX-One runs on the following OS. Note: Windows XP (Service Pack 3 or higher, 32-bit version) / Windows Vista (32-bit/64-bit version) / Windows 7 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version) / Windows 8.1 (32-bit/64-bit version) / Windows 10 (32-bit/64-bit version) CX-One Ver. 4.□ includes CX-Integrator Ver. 2.□. For details, refer to the CX-One catalog (Cat. No. R134).	1 license*	DVD	CXONE-AL01D-V4	-


* Multi licenses (3, 10, 30, or 50 licenses) and DVD media without licenses are also available for the CX-One.

Specifications

Item Model	CS1W-CRM21				
Applicable PLC	All CS-series PLCs				
Unit classification	CS-series Special I/O Unit				
Current consumption (Power supplied from PLC's Power Supply Unit)	400 mA max. at 5 VDC				
Communications power supply connector	One communications power supply connector for Slave Units and Repeater Units on the trunk line when using Flat Cable *				
Communications power supply connector allowable current capacity	5 A max.				
Maximum number of mountable Master Units	One word number assigned: 80 Units Two word numbers assigned: 48 Units Four word numbers assigned: 24 Units Eight word numbers assigned: 12 Units				
Mounting location	According to CS/CJ-series Special I/O Unit specifications.				
Communications power ON/OFF monitoring	The ON/OFF status of the communications power supply can be detected at the communications power supply connector.				
Data stored in Master Unit (built-in EEPROM)	 The following device parameters: Registration Table Registration Table Check Type Registered Slave Unit Participation Monitoring Time, Registered Slave Unit Participation Standby Mode, and Event Disable Setting Software Settings Table Communications Error Communications Stop Mode Communications Error Input Data Zero Clear Mode Network settings Part of error history (depends on type of error; mainly serious error related to communications stopping) 				
Noise immunity	Conforms to IEC 61000-4-4 2 kV (applied to PLC power supply).				
Vibration resistance	10 to 61.2 Hz with single-amplitude of 0.1 mm, 61.2 to 150 Hz and 14.7 m/s ² in X, Y, and Z directions for 80 min each (sweep time of 8 min \times 10 sweeps = 80 min)				
Shock resistance	196 m/s ² (3 times each in X, Y, and Z directions)				
Dielectric strength	 1,000 VAC for 1 min, Leakage current: 1 mA max. Between communications connector or external current supply connector and GR terminal on Power Supply Unit Between communications connector or external current supply connector and all Unit connectors 				
Insulation resistance	20 M Ω min. (between isolated circuits)				
Ambient operating temperature	0 to 55°C				
Ambient operating humidity	10 to 90% (no condensation)				
Ambient operating atmosphere	No corrosive gases				
Storage temperature	-20 to 75°C				
Weight	190 g max. (Master Unit only)				

 $\ensuremath{\boldsymbol{\ast}}$ The Master Unit does not required communications power.

External Interface



Communications Power Supply Connector

Connect this connector to a 24-VDC power supply when using Flat Cable (4-conductor). Doing so will supply communications power to the Slave Units and Repeater Units on the trunk line from the communications connector through the Flat Cable.



Communications power + Communications power -

Note: Do not connect anything to this connector when using Round Cable.

Ferrules

The following ferrules are recommended for the communications power supply cable.

Model	Applicable wire size	Crimping tool	Manufacturer
AI0, 5-10 WH	0.5 mm/AWG20	CRIMPFOX UD6 (product number 1204436) or the CRIMPFOX ZA3 Series	Phoenix Contact K.K.
H 0.5/16 orange	0.5 mm/AWG20	Crimper PZ 1.5 (Product number 900599)	Weidmuller Co. Ltd.


The following screwdriver is recommended for removing ferrules.


Model	Manufacturer
XW4Z-00C	OMRON Corporation

Dimensions


(Unit: mm)







Dimensions When the Cable is Attached



Note: Minimum cable bend R

• Flat cable I (w/o sheath): The bend R should be 10 times (R25.4) of the external coating.

• Round Cable I (2 core): The bend R should be 5 times (R38) of the max. external coating.

Related Manual

The manuals related the CS Series CompoNet Master Unit are configured as in the following table. Please also refer to them.

Cat.No.	Name	Contents
W456	CJ1W-CRM21/CJ1W-CRM21 CompoNet Master Units Operation Manual	Contains general information on CompoNet networks, information on communications specifications and wiring methods common to communications networks, and information on CS/CJ-series Master Units.
W342	SYSMAC CS/CJ/CP Series SYSMAC One NSJ Series Communications Commands Reference Manual	Contains information on communications commands for CS/CJ-series Master Units.
W457	CompoNet Slave Units and Repeater Unit Operation Manual	Contains information on the specifications of CompoNet Slave Units and Repeater Units.

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

CS1W-OC201 CS1W-OD212 CS1W-BC032 CS1H-CPU67H CS1G-CPU43H CS1W-ETN21 CS1W-MCH71 CS1W-BC052 CS1W-BC102 CS1G-CPU44H CS1G-CPU42H CS1W-MD262 CS1W-OA201 CS1G-CPU45H CS1H-CPU65H CS1H-CPU63H CS1W-B102 CS1W-GPI01 CS1W-OD211 CS1W-OD262 CS1W-MD561 CS1H-CPU64H CS1W-OC211 CS1W-OA211 CS1W-BC022 CS1W-BC082 CS1W-OD232 CS1W-BI052 CS1W-DA041 CS1H-CPU66H CS1W-NC471 CS1W-NC271 CS1W-NCF71 CS1W-DA08C CS1W-SPU02-V2 CS1W-SPU01-V2 CS1D-BI092 CS1D-CPU42S CS1D-CPU44S CS1W-LCB05 CS1W-MC221-V1 CS1W-MC421-V1 CS1W-MD261 CS1W-RPT01 CS1W-RPT02 CS1W-RPT03 CS1W-SCB21-V1 CS1W-SCB41-V1 CS1W-SCU21-V1 CS1W-SLK21 CS1W-SP001 CS1W-AT114 CS1W-AT115 CS1W-AT131 CS1W-AT132 CS1W-AT133 CS1W-AT134 CS1W-SIM2 CS1D-CPU65H CS1D-CPU65P CS1D-CPU65S CS1D-CPU67H CS1D-CPU67P CS1D-CPU67S CS1W-PRM21 CS1W-DRM21-V1 CS1W-CRM21 CS1W-DA08V CS1W-DES96 CS1W-DES96-DRM CS1W-FLN01 CS1W-FLN02 CS1W-IA111 CS1W-IA211 CS1D-DPL01 CS1D-DPL02D CS1D-IC102D CS1D-II102D CS1D-PA207R CS1D-CPU24 CS1D-SP001 CS1D-SP002 CS1W-AT031 CS1W-AT031 CS1W-AT032 CS1W-AT033 CS1W-AT034 CS1W-AT035 CS1W-AT111 CS1W-AT112 CS1W-AT113