B3SE Ultra-thin Sealed Surface-mounting Tactile Switch

PCB surface-mounting 6-mm square type that achieves high durability with an ultra-thin, sealed structure.

- A height of 2 mm contributes to the development of thinner and smaller devices.
- Sealed construction conforming to IP67 (IEC 60529) provides high contact reliability in dusty environments. (* Excluding the terminal section.)
- Crisp click feeling and high durability of 1million operations.
- Surface-mounting pin type is suitable for high-density mounting.
- A small package containing 100 embossed taping reels is available, in addition to the standard package containing 2000 reels.



RoHS Compliant

List of Model

$6 \times 6 \text{ mm Models}$

Туре	Contact material	Plunger	Height	Operating force (OF)	Plunger color	Embossed tape		
						Model	Minimum packing unit	
B3SE	Silver plated		2.0 mm	1.96 N {200 gf}	Blue	B3SE-1002P	2,000	
						B3SE-1002P-R100	100	

Note:Orders must be made in multiples of the minimum order. Switches are not sold individually.


Ratings/Characteristics

Rating (resistive load)	1 to 50 mA at 3 to 12 VDC		
Minimum applicable load (reference value)	10 μA at 1 VDC (resistive load)		
Ambient operating tem- perature	-25 $^\circ\!\mathrm{C}$ to +70 $^\circ\!\mathrm{C}$ at 60%RH max. (with no icing or condensation)		
Ambient operating hu- midity	35% to 85% (at +5 to +35°C)		
Contact form	SPST-NO		
Contact resistance (ini- tial value)	100 mΩ max.		
Insulation resistance	100 M Ω min. (at 250 VDC with insulation tester)		
Dielectric strength	250 VAC, 50/60 Hz for 1 min		
Bounce time	5 ms max.		
Vibration resistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude		
Shock resistance	Destruction: 980 m/s ² {approx. 100 G} max.		
Durability	1,000,000 operations min.		
Degree of protection	IEC IP67		
Washing	Not possible		

Operating Characteristics

Item	Operation type	B3SE-1002P		
Operating force (OF)		$1.96 \pm 0.49 \text{ N} \{200 \pm 50 \text{ gf}\}$		
Releasing force (RF)		0.35 N min. {35 gf}		
Pretravel (PT)		$0.3\pm0.2~\text{mm}$		


Model Structure



B3SE

Dimensions (Unit: mm)

B3SE-1002P B3SE-1002P-R100



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions. No terminal numbers are indicated on the Switches.

Precautions

Be sure to read the precautions common to all Tactile Switches on pages for correct use.

Please check each region's Terms & Conditions by region website.

OMRON Corporation Electronic and Mechanical Components Company

Regional Contact Americas

Americas https://www.components.omron.com/ Asia-Pacific https://ecb.omron.com.sg/ Korea https://www.omron-ecb.co.kr/ Europe http://components.omron.eu/ China https://www.ecb.omron.com.cn/ Japan https://www.omron.co.jp/ecb/

© OMRON Corporation 2017-2018 All Rights Reserved.

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. A262-E1-02 0918(0817)(O)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron: B3SE-1002P B3SE-1002