



## Test Procedure for the NCP380HMU10AGEVB Evaluation Board

### Equipment Needed:

1. Power Supply (5V, 3A)
2. Potentiometer/Load (100Ω, 10W)
3. Multimeter

Note: Cables should be as short as possible to lower their inductance value – otherwise you may harm either the input or output pins of the device

### Set-up & Test:

1. Apply  $V_{in} = 4V$  dc (Over Current Limit = 1A) on IN test point.
2. Connect a 100Ω, 10W load between Vout test point and GND strap.
3. Toggle EN strap between Low and High sides.
4. OUT must change from 0 to 4V by toggling the EN strap.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[NCP380HMU10AGEVB](#)