

AR0230AT

CMOS Image Sensor, 2 MP, 1/3"

Product Overview

For complete documentation, see the data sheet.

The AR0230AT is a 1/2.7-inch CMOS digital image sensor with an active-pixel array of 1928Hx1088V. It captures images in either linear or high dynamic range modes, with rolling-shutter readout. It includes sophisticated camera functions such as in-pixel binning, windowing and both video and single frame modes. It is designed for both low light and high dynamic range scene performance. It is programmable through a simple two wire serial interface. The AR0230AT produces extraordinarily clear, sharp digital pictures, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications.

Features

- High Dynamic Range

Applications

- Automotive

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Package Type
AR0230ATSC00XUEA0-DRBR		<div><div>A</div><div>Pb</div><div>P</div><div>H</div></div>	Active	CMOS	2.1	30	1/2.7 inch		3.0 x 3.0		RGB	IBGA-80

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

[AR0230ATSC00XUEAH-GEVB](#) [AR0230ATSM00XUEAH-GEVB](#)