MUN5332DW1, NSBC143EPDXV6, NSBC143EPDP6

Complementary Bias Resistor Transistors R1 = 4.7 kΩ, R2 = 4.7 kΩ

NPN and PNP Transistors with Monolithic Bias Resistor Network

This series of digital transistors is designed to replace a single device and its external resistor bias network. The Bias Resistor Transistor (BRT) contains a single transistor with a monolithic bias network consisting of two resistors; a series base resistor and a base-emitter resistor. The BRT eliminates these individual components by integrating them into a single device. The use of a BRT can reduce both system cost and board space.

Features

- Simplifies Circuit Design
- Reduces Board Space
- Reduces Component Count
- S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable*
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

(T_A = 25°C both polarities Q_1 (PNP) & Q_2 (NPN), unless otherwise noted)

Rating	Symbol	Max	Unit
Collector-Base Voltage	V_{CBO}	50	Vdc
Collector-Emitter Voltage	V_{CEO}	50	Vdc
Collector Current – Continuous	I_C	100	mAdc
Input Forward Voltage	$V_{IN(fwd)}$	30	Vdc
Input Reverse Voltage	$V_{IN(rev)}$	10	Vdc

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ORDERING INFORMATION

Device	Package	Shipping†
MUN5332DW1T1G, NSVMUN5332DW1T1G*	SOT−363	3,000/Tape & Reel
NSVMUN5332DW1T3G*	SOT−363	10,000/Tape & Reel
NSBC143EPDXV6T1G	SOT−563	4,000/Tape & Reel
NSBC143EPDP6T5G	SOT−963	8,000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ON Semiconductor®

www.onsemi.com

PIN CONNECTIONS



MARKING DIAGRAMS

SOT−363
CASE 419B



SOT−563
CASE 463A



SOT−963
CASE 527AD



32/V = Specific Device Code
M = Date Code*
▪ = Pb-Free Package

(Note: Microdot may be in either location)

*Date Code orientation may vary depending upon manufacturing location.

© Semiconductor Components Industries, LLC, 2013

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
MUN5332DW1 (SOT−363) ONE JUNCTION HEATED			
Total Device Dissipation T_A = 25°C (Note 31) (Note 32) Derate above 25°C (Note 31) (Note 32)	P_D	 187 256 1.5 2.0	 mW mW/°C
Thermal Resistance, (Note 31) Junction to Ambient (Note 32)	$R_{\theta JA}$	670 490	°C/W
MUN5332DW1 (SOT−363) BOTH JUNCTION HEATED (Note 33)			
Total Device Dissipation T_A = 25°C (Note 31) (Note 32) Derate above 25°C (Note 31) (Note 32)	P_D	 250 385 2.0 3.0	 mW mW/°C
Thermal Resistance, Junction to Ambient (Note 31) (Note 32)	$R_{\theta JA}$	 493 325	°C/W
Thermal Resistance, Junction to Lead (Note 31) (Note 32)	$R_{\theta JL}$	 188 208	°C/W
Junction and Storage Temperature Range	T_J, T_{stg}	−55 to +150	°C
NSBC143EPDXV6 (SOT−563) ONE JUNCTION HEATED			
Total Device Dissipation T_A = 25°C (Note 31) Derate above 25°C (Note 31)	P_D	 357 2.9	 mW mW/°C
Thermal Resistance, Junction to Ambient (Note 31)	$R_{\theta JA}$	 350	°C/W
NSBC143EPDXV6 (SOT−563) BOTH JUNCTION HEATED (Note 33)			
Total Device Dissipation T_A = 25°C (Note 31) Derate above 25°C (Note 31)	P_D	 500 4.0	 mW mW/°C
Thermal Resistance, Junction to Ambient (Note 31)	$R_{\theta JA}$	 250	°C/W
Junction and Storage Temperature Range	T_J, T_{stg}	−55 to +150	°C
NSBC143EPDP6 (SOT−963) ONE JUNCTION HEATED			
Total Device Dissipation T_A = 25°C (Note 34) (Note 35) Derate above 25°C (Note 34) (Note 35)	P_D	 231 269 1.9 2.2	 MW mW/°C
Thermal Resistance, Junction to Ambient (Note 34) (Note 35)	$R_{\theta JA}$	 540 464	°C/W
NSBC143EPDP6 (SOT−963) BOTH JUNCTION HEATED (Note 33)			
Total Device Dissipation T_A = 25°C (Note 34) (Note 35) Derate above 25°C (Note 34) (Note 35)	P_D	 339 408 2.7 3.3	 MW mW/°C
Thermal Resistance, Junction to Ambient (Note 34) (Note 35)	$R_{\theta JA}$	 369 306	°C/W
Junction and Storage Temperature Range	T_J, T_{stg}	−55 to +150	°C

31. FR−4 @ Minimum Pad.
32. FR−4 @ 1.0 × 1.0 Inch Pad.
33. Both junction heated values assume total power is sum of two equally powered channels.
34. FR−4 @ 100 mm^2, 1 oz. copper traces, still air.
35. FR−4 @ 500 mm^2, 1 oz. copper traces, still air.

ELECTRICAL CHARACTERISTICS (T_A = 25°C both polarities Q_1 (PNP) & Q_2 (NPN), unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS					
Collector-Base Cutoff Current (V_{CB} = 50 V, I_E = 0)	I_{CBO}	–	–	100	nAdc
Collector-Emitter Cutoff Current (V_{CE} = 50 V, I_B = 0)	I_{CEO}	–	–	500	nAdc
Emitter-Base Cutoff Current (V_{EB} = 6.0 V, I_C = 0)	I_{EBO}	–	–	1.5	mAdc
Collector-Base Breakdown Voltage (I_C = 10 μA, I_E = 0)	$V_{(BR)CBO}$	50	–	–	Vdc
Collector-Emitter Breakdown Voltage (Note 36) (I_C = 2.0 mA, I_B = 0)	$V_{(BR)CEO}$	50	–	–	Vdc
ON CHARACTERISTICS					
DC Current Gain (Note 36) (I_C = 5.0 mA, V_{CE} = 10 V)	h_{FE}	15	30	–	
Collector-Emitter Saturation Voltage (Note 36) (I_C = 10 mA, I_B = 1.0 mA)	$V_{CE(sat)}$	–	–	0.25	V
Input Voltage (Off) (V_{CE} = 5.0 V, I_C = 100 μA) (NPN) (V_{CE} = 5.0 V, I_C = 100 μA) (PNP)	$V_{i(off)}$	– –	1.2 1.2	– –	Vdc
Input Voltage (On) (V_{CE} = 0.2 V, I_C = 20 mA) (NPN) (V_{CE} = 0.2 V, I_C = 20 mA) (PNP)	$V_{i(on)}$	– –	2.4 2.8	– –	Vdc
Output Voltage (On) (V_{CC} = 5.0 V, V_B = 2.5 V, R_L = 1.0 kΩ)	V_{OL}	–	–	0.2	Vdc
Output Voltage (Off) (V_{CC} = 5.0 V, V_B = 0.25 V, R_L = 1.0 kΩ)	V_{OH}	4.9	–	–	Vdc
Input Resistor	R1	3.3	4.7	6.1	kΩ
Resistor Ratio	R_1/R_2	0.8	1.0	1.2	

36. Pulsed Condition: Pulse Width = 300 ms, Duty Cycle ≤ 2%.



(1) SOT−363; 1.0 × 1.0 Inch Pad
(2) SOT−563; Minimum Pad
(3) SOT−963; 100 mm^2, 1 oz. Copper Trace

Figure 77. Derating Curve

TYPICAL CHARACTERISTICS – NPN TRANSISTOR
MUN5332DW1, NSBC143EPDXV6



Figure 78. $V_{CE(sat)}$, vs. I_C



Figure 79. DC Current Gain



Figure 80. Output Capacitance



Figure 81. Output Current vs. Input Voltage



Figure 82. Input Voltage vs. Output Current

TYPICAL CHARACTERISTICS – PNP TRANSISTOR
MUN5332DW1, NSBC143EPDXV6



Figure 83. $V_{CE(sat)}$ vs. I_C



Figure 84. DC Current Gain



Figure 85. Output Capacitance



Figure 86. Output Current vs. Input Voltage



Figure 87. Input Voltage vs. Output Current

TYPICAL CHARACTERISTICS – NPN TRANSISTOR
NSBC143EPDP6



Figure 88. $V_{CE(sat)}$, vs. I_C



Figure 89. DC Current Gain



Figure 90. Output Capacitance



Figure 91. Output Current vs. Input Voltage



Figure 92. Input Voltage vs. Output Current

TYPICAL CHARACTERISTICS – PNP TRANSISTOR
NSBC143EPDP6



Figure 93. $V_{CE(sat)}$ vs. I_C



Figure 94. DC Current Gain



Figure 95. Output Capacitance



Figure 96. Output Current vs. Input Voltage



Figure 97. Input Voltage vs. Output Current

PACKAGE DIMENSIONS

SC−88/SC70−6/SOT−363
CASE 419B−02
ISSUE Y



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.20 PER END.
4. DIMENSIONS D AND E1 AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY AND DATUM H.
5. DATUMS A AND B ARE DETERMINED AT DATUM H.
6. DIMENSIONS b AND c APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.08 AND 0.15 FROM THE TIP.
7. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 TOTAL IN EXCESS OF DIMENSION b AT MAXIMUM MATERIAL CONDITION. THE DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OF THE FOOT.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
A	---	---	1.10	---	---	0.043
A1	0.00	---	0.10	0.000	---	0.004
A2	0.70	0.90	1.00	0.027	0.035	0.039
b	0.15	0.20	0.25	0.006	0.008	0.010
C	0.08	0.15	0.22	0.003	0.006	0.009
D	1.80	2.00	2.20	0.070	0.078	0.086
E	2.00	2.10	2.20	0.078	0.082	0.086
E1	1.15	1.25	1.35	0.045	0.049	0.053
e	0.65 BSC			0.026 BSC		
L	0.26	0.36	0.46	0.010	0.014	0.018
L2	0.15 BSC			0.006 BSC		
aaa	0.15			0.006		
bbb	0.30			0.012		
ccc	0.10			0.004		
ddd	0.10			0.004		

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

SOT−563, 6 LEAD
CASE 463A
ISSUE G



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
A	0.50	0.55	0.60	0.020	0.021	0.023
b	0.17	0.22	0.27	0.007	0.009	0.011
C	0.08	0.12	0.18	0.003	0.005	0.007
D	1.50	1.60	1.70	0.059	0.062	0.066
E	1.10	1.20	1.30	0.043	0.047	0.051
e	0.5 BSC			0.02 BSC		
L	0.10	0.20	0.30	0.004	0.008	0.012
H_E	1.50	1.60	1.70	0.059	0.062	0.066

SOLDERING FOOTPRINT*



*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

SOT−963
CASE 527AD
ISSUE E



TOP VIEW



SIDE VIEW



BOTTOM VIEW

NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	MILLIMETERS		
DIM	MIN	NOM	MAX
A	0.34	0.37	0.40
b	0.10	0.15	0.20
C	0.07	0.12	0.17
D	0.95	1.00	1.05
E	0.75	0.80	0.85
e		0.35 BSC	
H_E	0.95	1.00	1.05
L		0.19 REF	
L2	0.05	0.10	0.15

RECOMMENDED MOUNTING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor:

NSBC143EPDP6T5G NSVMUN5332DW1T1G