

MOSFET – N-Channel, POWERTRENCH®

80 V, 80 A, 4.5 mΩ

FDWS86368-F085

Features

- Typical $R_{DS(on)}$ = 3.7 mΩ at V_{GS} = 10 V, I_D = 80 A
- Typical $Q_{g(tot)}$ = 57 nC at V_{GS} = 10 V, I_D = 80 A
- UIS Capability
- Wettable Flanks for Automatic Optical Inspection (AOI)
- AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free and is RoHS Compliant

Applications

- Automotive Engine Control
- PowerTrain Management
- Solenoid and Motor Drivers
- Integrated Starter/Alternator
- Primary Switch for 12 V Systems

MOSFET MAXIMUM RATINGS (T_J = 25°C, Unless otherwise noted)


Symbol	Parameter	Ratings	Units
V_{DSS}	Drain-to-Source Voltage	80	V
V_{GS}	Gate-to-Source Voltage	±20	V
I_D	Drain Current (T_C = 25°C) Continuous (V_{GS} = 10 V) (Note 1) Pulsed	80 (See Figure 4)	A
E_{AS}	Single Pulse Avalanche Energy (Note 2)	82	mJ
P_D	Power Dissipation Derate Above 25°C	214 1.43	W W/°C
T_J, T_{STG}	Operating and Storage Temperature	–55 to +175	°C
$R_{\theta JC}$	Thermal Resistance, Junction to Case	0.7	°C/W
$R_{\theta JA}$	Maximum Thermal Resistance, Junction to Ambient (Note 3)	50	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. Current is limited by bondwire configuration.
2. Starting T_J = 25°C, L = 40 μH, I_{AS} = 64 A, V_{DD} = 80 V during inductor charging and V_{DD} = 0 V during time in avalanche.
3. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design, while $R_{\theta JA}$ is determined by the board design. The maximum rating presented here is based on mounting on a 1 in² pad of 2 oz copper.

V_{DSS}	$R_{DS(on)}$ MAX	I_D MAX
80 V	4.5 mΩ @ 10 V	80 A

ELECTRICAL CONNECTION




N-Channel MOSFET



DFNW8
CASE 507AU

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
WL = Assembly Lot
FDWS = Device Code
86368 = Device Code

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping†
FDWS86368-F085	DFNW8 (Power56) (Pb-Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please

FDWS86368–F085

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
--------	-----------	-----------------	------	------	------	-------

OFF CHARACTERISTICS

$B_{V_{DSS}}$	Drain-to-Source Breakdown Voltage	$I_D = 250\ \mu\text{A}$, $V_{GS} = 0\ \text{V}$	80			V
I_{DSS}	Drain-to-Source Leakage Current	$V_{DS} = 80\ \text{V}$, $V_{GS} = 0\ \text{V}$, $T_J = 25^\circ\text{C}$			1	μA
		$V_{DS} = 80\ \text{V}$, $V_{GS} = 0\ \text{V}$, $T_J = 175^\circ\text{C}$ (Note 4)			1	mA
I_{GSS}	Gate-to-Source Leakage Current	$V_{GS} = \pm 20\ \text{V}$			± 100	nA

ON CHARACTERISTICS

$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250\ \mu\text{A}$	2.0	3.0	4.0	V
$R_{DS(on)}$	Drain to Source On Resistance	$I_D = 80\ \text{A}$, $V_{GS} = 10\ \text{V}$, $T_J = 25^\circ\text{C}$		3.7	4.5	m Ω
		$I_D = 80\ \text{A}$, $V_{GS} = 10\ \text{V}$, $T_J = 175^\circ\text{C}$ (Note 4)		7.4	9.0	

DYNAMIC CHARACTERISTICS

C_{iss}	Input Capacitance	$V_{DS} = 40\ \text{V}$, $V_{GS} = 0\ \text{V}$, $f = 1\ \text{MHz}$			4350		pF
C_{oss}	Output Capacitance				636		pF
C_{rss}	Reverse Transfer Capacitance				20		pF
R_g	Gate Resistance	$f = 1\ \text{MHz}$			2.5		Ω
$Q_{g(TOT)}$	Total Gate Charge	$V_{GS} = 0\ \text{V}$ to $10\ \text{V}$	$V_{DD} = 64\ \text{V}$, $I_D = 80\ \text{A}$		57	75	nC
$Q_{g(th)}$	Threshold Gate Charge	$V_{GS} = 0\ \text{V}$ to $2\ \text{V}$			8		nC
Q_{gs}	Gate-to-Source Gate Charge				23		nC
Q_{gd}	Gate-to-Drain "Miller" Charge				11		nC

SWITCHING CHARACTERISTICS

t_{on}	Turn-On Time	$V_{DD} = 40\ \text{V}$, $I_D = 80\ \text{A}$, $V_{GS} = 10\ \text{V}$, $R_{GEN} = 6\ \Omega$			60	ns
$t_{d(on)}$	Turn-On Delay			23		ns
t_r	Rise Time			22		ns
$t_{d(off)}$	Turn-Off Delay			32		ns
t_f	Fall Time			13		ns
t_{off}	Turn-Off Time				59	ns

DRAIN-SOURCE DIODE CHARACTERISTICS

V_{SD}	Source-to-Drain Diode Voltage	$V_{GS} = 0\ \text{V}$, $I_{SD} = 80\ \text{A}$ $V_{GS} = 0\ \text{V}$, $I_{SD} = 40\ \text{A}$			1.25 1.2	V
t_{rr}	Reverse-Recovery Time	$I_F = 80\ \text{A}$, $\Delta I_{SD}/\Delta t = 100\ \text{A}/\mu\text{s}$, $V_{DD} = 64\ \text{V}$		58	75	ns
Q_{rr}	Reverse-Recovery Charge			49	67	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The maximum value is specified by design at $T_J = 175^\circ\text{C}$. Product is not tested to this condition in production.

TYPICAL CHARACTERISTICS




Figure 1. Normalized Power Dissipation vs. Case Temperature




Figure 2. Maximum Continuous Drain Current vs. Case Temperature




Figure 3. Normalized Maximum Transient Thermal Impedance




Figure 4. Peak Current Capability

TYPICAL CHARACTERISTICS




Figure 5. Forward Bias Safe Operating Area




Figure 6. Unclamped Inductive Switching Capability




Figure 7. Transfer Characteristics




Figure 8. Forward Diode Characteristics




Figure 9. Saturation Characteristics




Figure 10. Saturation Characteristics

TYPICAL CHARACTERISTICS




Figure 11. $R_{DS(on)}$ vs. Gate VoltageFigure 12. Normalized $R_{DS(on)}$ vs. Junction Temperature

Figure 13. Normalized Gate Threshold Voltage vs. Temperature




Figure 14. Normalized Drain to Source Breakdown Voltage vs. Junction Temperature




Figure 15. Capacitance vs. Drain to Source Voltage









Figure 16. Single Pulse Maximum Power Dissipation

PACKAGE DIMENSIONS

DFNW8 5.2x6.3, 1.27P
CASE 507AU
ISSUE A

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.



*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.90	1.00	1.10
A1	-	-	0.05
A2	0.65	0.75	0.85
A3	0.30 REF		
b	0.47	0.52	0.57
b1	0.13	0.18	0.23
b2	(0.54)		
D	5.00	5.10	5.20
D1	4.80	4.90	5.00
D2	3.72	3.82	3.92
E	6.20	6.30	6.40
E1	5.70	5.80	5.90
E2	3.38	3.48	3.58
E3	0.30 REF		
E4	0.45 REF		
e	1.27 BSC		
e/2	0.635BSC		
k	1.30	1.40	1.50
L	0.64	0.74	0.84
z	0.24	0.29	0.34
z1	(0.28)		
θ	0°	---	12°

POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**’s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided “as-is” and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. “Typical” parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including “Typicals” must be validated for each customer application by customer’s technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800–282–9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[FDWS86368-F085](#)