

IGBT - Field Stop, Trench

650 V, 75 A

FGH75T65SQD

Description



Using novel field stop IGBT technology, **onsemi**'s new series of field stop 4th generation IGBTs offer the optimum performance for solar inverter, UPS, Welder, Telecom, ESS and PFC applications where low conduction and switching losses are essential.

Features

- Maximum Junction Temperature : $T_J = 175^{\circ}\text{C}$
- Positive Temperature Co-efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage: $V_{CE(sat)} = 1.6 \text{ V(Typ.) @ } I_C = 75 \text{ A}$
- 100% of the Parts Tested for $I_{LM}(1)$
- High Input Impedance
- Fast Switching
- Tighten Parameter Distribution
- These Devices are Pb-Free and are RoHS Compliant


Applications

- Solar Inverter, UPS, Welder, Telecom, ESS, PFC



TO-247-3LD
CASE 340CH

MARKING DIAGRAM



\$Y = **onsemi** Logo
 &Z = Assembly Plant Code
 &3 = Numeric Date Code
 &K = Lot Code
 FGH75T65SQD = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

FGH75T65SQD

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Description		Symbol	Rating	Unit
Collector to Emitter Voltage		V _{CES}	650	V
Gate to Emitter Voltage		V _{GES}	±20	V
Transient Gate to Emitter Voltage			±30	V
Collector Current	T _C = 25°C	I _C	150	A
Collector Current	T _C = 100°C		75	A
Pulsed Collector Current	T _C = 25°C	I _{LM} (Note 1)	300	A
Pulsed Collector Current		I _{CM} (Note 2)	300	A
Diode Forward Current	T _C = 25°C	I _F	75	A
Diode Forward Current	T _C = 100°C		50	A
Pulsed Diode Maximum Forward Current		I _{FM} (Note 2)	300	A
Maximum Power Dissipation	T _C = 25°C	P _D	375	W
Maximum Power Dissipation	T _C = 100°C		188	W
Operating Junction Temperature		T _J	–55 to +175	°C
Storage Temperature Range		T _{stg}	–55 to +175	°C
Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds		T _L	300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. V_{CC} = 400 V, V_{GE} = 15 V, I_C = 300 A, R_G = 3 Ω, Inductive Load
2. Repetitive rating: Pulse width limited by max. junction temperature.

THERMAL CHARACTERISTICS

Parameter	Symbol	FGH75T65SQD–F155	Unit
Thermal Resistance, Junction to Case	R _{θJC} (IGBT)	0.4	°C/W
Thermal Resistance, Junction to Case	R _{θJC} (Diode)	0.65	°C/W
Thermal Resistance, Junction to Ambient	R _{θJA}	40	°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FGH75T65SQD–F155	FGH75T65SQD	TO–247–3 (Pb–Free)	Tube	–	–	30

ELECTRICAL CHARACTERISTICS OF THE IGBT (T_C = 25°C unless otherwise noted)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
-----------	--------	-----------------	------	------	------	------

OFF CHARACTERISTICS

Collector to Emitter Breakdown Voltage	BV _{CES}	V _{GE} = 0 V, I _C = 1 mA	650	–	–	V
Temperature Coefficient of Breakdown Voltage	ΔBV _{CES} /ΔT _J	I _C = 1 mA, Reference to 25°C	–	0.6	–	V/°C
Collector Cut–Off Current	I _{CES}	V _{CE} = V _{CES} , V _{GE} = 0 V	–	–	250	μA
G–E Leakage Current	I _{GES}	V _{GE} = V _{GES} , V _{CE} = 0 V	–	–	±400	nA

ON CHARACTERISTICS

G–E Threshold Voltage	V _{GE(th)}	I _C = 75 mA, V _{CE} = V _{GE}	2.6	4.5	6.4	V
Collector to Emitter Saturation Voltage	V _{CE(sat)}	I _C = 75 A, V _{GE} = 15 V	–	1.6	2.1	V
		I _C = 75 A, V _{GE} = 15 V, T _C = 175°C	–	1.92	–	V

FGH75T65SQD

ELECTRICAL CHARACTERISTICS OF THE IGBT ($T_C = 25^\circ\text{C}$ unless otherwise noted) (continued)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
DYNAMIC CHARACTERISTICS						
Input Capacitance	C _{ies}	V _{CE} = 30 V, V _{GE} = 0 V, f = 1 MHz	–	4845	–	pF
Output Capacitance	C _{oes}		–	155	–	pF
Reverse Transfer Capacitance	C _{res}		–	14	–	pF
SWITCHING CHARACTERISTICS						
Turn–On Delay Time	t _{d(on)}	V _{CC} = 400 V, I _C = 18.8 A, R _G = 4.7 Ω, V _{GE} = 15 V, Inductive Load, T _C = 25°C	–	23	–	ns
Rise Time	t _r		–	10	–	ns
Turn–Off Delay Time	t _{d(off)}		–	120	–	ns
Fall Time	t _f		–	7	–	ns
Turn–On Switching Loss	E _{on}		–	300	–	μJ
Turn–Off Switching Loss	E _{off}		–	70	–	μJ
Total Switching Loss	E _{ts}		–	370	–	μJ
Turn–On Delay Time	t _{d(on)}	V _{CC} = 400 V, I _C = 37.5 A, R _G = 4.7 Ω, V _{GE} = 15 V, Inductive Load, T _C = 25°C	–	26	–	ns
Rise Time	t _r		–	19	–	ns
Turn–Off Delay Time	t _{d(off)}		–	114	–	ns
Fall Time	t _f		–	11	–	ns
Turn–On Switching Loss	E _{on}		–	746	–	μJ
Turn–Off Switching Loss	E _{off}		–	181	–	μJ
Total Switching Loss	E _{ts}		–	927	–	μJ
Turn–On Delay Time	t _{d(on)}	V _{CC} = 400 V, I _C = 18.8 A, R _G = 4.7 Ω, V _{GE} = 15 V, Inductive Load, T _C = 175°C	–	22	–	ns
Rise Time	t _r		–	12	–	ns
Turn–Off Delay Time	t _{d(off)}		–	135	–	ns
Fall Time	t _f		–	14	–	ns
Turn–On Switching Loss	E _{on}		–	760	–	μJ
Turn–Off Switching Loss	E _{off}		–	180	–	μJ
Total Switching Loss	E _{ts}		–	940	–	μJ
Turn–On Delay Time	t _{d(on)}	V _{CC} = 400 V, I _C = 37.5 A, R _G = 4.7 Ω, V _{GE} = 15 V, Inductive Load, T _C = 175°C	–	24	–	ns
Rise Time	t _r		–	24	–	ns
Turn–Off Delay Time	t _{d(off)}		–	125	–	ns
Fall Time	t _f		–	10	–	ns
Turn–On Switching Loss	E _{on}		–	1520	–	μJ
Turn–Off Switching Loss	E _{off}		–	401	–	μJ
Total Switching Loss	E _{ts}		–	1921	–	μJ
Total Gate Charge	Q _g	V _{CE} = 400 V, I _C = 75 A, V _{GE} = 15 V	–	128	–	nC
Gate to Emitter Charge	Q _{ge}		–	23	–	nC
Gate to Collector Charge	Q _{gc}		–	29	–	nC

FGH75T65SQD

ELECTRICAL CHARACTERISTICS OF THE DIODE ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parametr	Symbol	Test Conditions		Min	Typ	Max	Unit
Diode Forward Voltage	V _{FM}	I _F = 50 A	T _C = 25°C	–	2.0	2.6	V
			T _C = 175°C	–	1.64	–	
Reverse Recovery Energy	E _{rec}	I _F = 50 A, dI _F / dt = 200 A/μs	T _C = 175°C	–	61	–	μJ
Diode Reverse Recovery Time	t _{rr}		T _C = 25°C	–	43	–	ns
			T _C = 175°C	–	210	–	
Diode Reverse Recovery Charge	Q _{rr}		T _C = 25°C	–	90	–	nC
			T _C = 175°C	–	1280	–	

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage Characteristics




Figure 4. Saturation Voltage vs. Case Temperature at Variant Current Level




Figure 5. Saturation Voltage vs V_{GE}




Figure 6. Saturation Voltage vs V_{GE}

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristic




Figure 9. Turn-On Characteristics vs. Gate Resistance




Figure 10. Turn-Off Characteristics vs. Gate Resistance




Figure 11. Switching Loss vs. Gate Resistance




Figure 12. Turn-On Characteristics vs. Collector Current

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 13. Turn-Off Characteristics vs. Collector Current




Figure 14. Switching Loss vs. Collector Current




Figure 15. Load Current vs. Frequency




Figure 16. SOA Characteristics




Figure 17. Forward Characteristics




Figure 18. Reverse Recovery Current

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 19. Reverse Recovery Time




Figure 20. Stored Charge




Figure 21. Transient Thermal Impedance of IGBT





Figure 22. Transient Thermal Impedance of Diode


TO-247-3LD
CASE 340CH
ISSUE A

DATE 09 OCT 2019



NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
- D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

GENERIC
MARKING DIAGRAM*


XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON13853G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-247-3LD	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[FGH75T65SQD-F155](#)