

NTGD4167C

MOSFET – POWER, Dual, Complementary, TSOP-6 30 V, +2.9/-2.2 A

Features

- Complementary N-Channel and P-Channel MOSFET
- Small Size (3 x 3 mm) Dual TSOP-6 Package
- Leading Edge Trench Technology for Low On Resistance
- Reduced Gate Charge to Improve Switching Response
- Independently Connected Devices to Provide Design Flexibility
- This is a Pb-Free Device

Applications

- DC-DC Conversion Circuits
- Load/Power Switching with Level Shift

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	30	V
Gate-to-Source Voltage (N-Ch & P-Ch)			V _{GS}	±12	V
N-Channel Continuous Drain Current (Note 1)	Steady State	T _A = 25°C T _A = 85°C	I _D	2.6 1.9	A
	t ≤ 5 s	T _A = 25°C		2.9	
	P-Channel Continuous Drain Current (Note 1)	Steady State		T _A = 25°C T _A = 85°C	
t ≤ 5 s		T _A = 25°C	-2.2		
Power Dissipation (Note 1)		Steady State	T _A = 25°C	P _D	0.9
	t ≤ 5 s	1.1			
Pulsed Drain Current	N-Ch	t _p = 10 μs	I _{DM}	8.6	A
	P-Ch			-6.3	
Operating Junction and Storage Temperature			T _J , T _{STG}	-55 to 150	°C
Source Current (Body Diode)			I _S	±0.9	A
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			T _L	260	°C

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Ambient – Steady State (Note 1)	R _{θJA}	140	°C/W
Junction-to-Ambient – t ≤ 5 s (Note 1)	R _{θJA}	110	°C/W

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


1. Surface Mounted on FR4 Board using 1 in sq pad size (Cu area = 1.127 in sq [1 oz] including traces).




ON Semiconductor®

<http://onsemi.com>

V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX (Note 1)
N-Ch 30 V	90 mΩ @ 4.5 V	2.6 A
	125 mΩ @ 2.5 V	2.2 A
P-Ch -30 V	170 mΩ @ -4.5 V	-1.9 A
	300 mΩ @ -2.5 V	-1.0 A



N-CHANNEL MOSFET




P-CHANNEL MOSFET



TSOP-6
CASE 318G
STYLE 13

MARKING DIAGRAM




TA = Specific Device Code

M = Date Code

▪ = Pb-Free Package

(Note: Microdot may be in either location)

PIN CONNECTION



(Top View)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 9 of this data sheet.

NTGD4167C

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Symbol	N/P	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	N	V _{GS} = 0 V	I _D = 250 μA	30		V
		P		I _D = -250 μA	-30		
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J	N			21.4		mV/°C
		P			22.2		
Zero Gate Voltage Drain Current	I _{DSS}	N	V _{GS} = 0 V, V _{DS} = 24 V	T _J = 25 °C		1.0	μA
		P	V _{GS} = 0 V, V _{DS} = -24 V			-1.0	
		N	V _{GS} = 0 V, V _{DS} = 24 V	T _J = 85 °C		10	
		P	V _{GS} = 0 V, V _{DS} = -24 V			-10	
Gate-to-Source Leakage Current	I _{GSS}	N	V _{DS} = 0 V, V _{GS} = ±12 V			±100	nA
		P	V _{DS} = 0 V, V _{GS} = ±12 V			±100	

ON CHARACTERISTICS (Note 2)

Gate Threshold Voltage	V _{GS(TH)}	N	V _{GS} = V _{DS}	I _D = 250 μA	0.5	0.9	1.5	V
		P		I _D = -250 μA	-0.5	-1.1	-1.5	
Drain-to-Source On Resistance	R _{DS(on)}	N	V _{GS} = 4.5 V, I _D = 2.6 A			52	90	mΩ
			V _{GS} = 2.5 V, I _D = 2.2 A			67	125	
		P	V _{GS} = -4.5 V, I _D = -1.9 A			130	170	
			V _{GS} = -2.5 V, I _D = -1.0 A			202	300	
Forward Transconductance	g _{FS}	N	V _{DS} = 15 V, I _D = 2.6 A			2.6		S
		P	V _{DS} = -15 V, I _D = -1.9 A			2.6		

CHARGES AND CAPACITANCES

Input Capacitance	C _{ISS}	N	f = 1 MHz, V _{GS} = 0 V	V _{DS} = 15 V		295		pF
Output Capacitance	C _{OSS}					48		
Reverse Transfer Capacitance	C _{RSS}					27		
Input Capacitance	C _{ISS}	P		V _{DS} = -15 V		419		
Output Capacitance	C _{OSS}					51		
Reverse Transfer Capacitance	C _{RSS}					26		
Total Gate Charge	Q _{G(TOT)}	N	V _{GS} = 4.5 V, V _{DS} = 15 V, I _D = 2.0 A			3.7	5.5	nC
Threshold Gate Charge	Q _{G(TH)}					0.6		
Gate-to-Source Gate Charge	Q _{GS}					0.9		
Gate-to-Drain “Miller” Charge	Q _{GD}					0.8		
Total Gate Charge	Q _{G(TOT)}	P	V _{GS} = -4.5 V, V _{DS} = -15 V, I _D = -2.0 A			3.9	6.0	
Threshold Gate Charge	Q _{G(TH)}					0.6		
Gate-to-Source Gate Charge	Q _{GS}					1.0		
Gate-to-Drain “Miller” Charge	Q _{GD}					1.0		

SWITCHING CHARACTERISTICS (Note 3)

Turn-On Delay Time	t _{d(ON)}	N	V _{GS} = 4.5 V, V _{DD} = 15 V, I _D = 1.0 A, R _G = 6.0 Ω		7.0		ns
Rise Time	t _r				4.0		
Turn-Off Delay Time	t _{d(OFF)}				14		
Fall Time	t _f				2.0		
Turn-On Delay Time	t _{d(ON)}	P	V _{GS} = -4.5 V, V _{DD} = -15 V, I _D = -1.0 A, R _G = 6.0 Ω		8.0		
Rise Time	t _r				8.0		
Turn-Off Delay Time	t _{d(OFF)}				22		
Fall Time	t _f				8.0		

2. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.

NTGD4167C

3. Switching characteristics are independent of operating junction temperatures.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Symbol	N/P	Test Conditions	Min	Typ	Max	Unit	
DRAIN-SOURCE DIODE CHARACTERISTICS								
Forward Diode Voltage	V _{SD}	N	V _{GS} = 0 V, T _J = 25 °C	I _S = 0.9 A		0.7	1.2	V
		P		I _S = -0.9 A		-0.8	-1.2	
Reverse Recovery Time	t _{RR}	N	V _{GS} = 0 V, dI _S / dt = 100 A/μs, I _S = 0.9 A		8.0		ns	
Charge Time	t _a				5.0			
Discharge Time	t _b				3.0			
Reverse Recovery Charge	Q _{RR}				3.0		nC	
Reverse Recovery Time	t _{RR}	P	V _{GS} = 0 V, dI _S / dt = 100 A/μs, I _S = -0.9 A		12		ns	
Charge Time	t _a				10			
Discharge Time	t _b				2.0			
Reverse Recovery Charge	Q _{RR}				7.0		nC	

N-CHANNEL TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Region vs. Gate-To-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Temperature




Figure 5. On-Resistance Variation with Temperature




Figure 6. Capacitance Variation




Figure 7. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 8. Diode Forward Voltage versus Current




Figure 9. Threshold Voltage




Figure 10. Single Pulse Maximum Power Dissipation




Figure 11. Maximum Rated Forward Biased Safe Operating Area

NTGD4167C




Figure 12. FET Thermal Response

P-CHANNEL TYPICAL CHARACTERISTICS




Figure 13. On-Region Characteristics




Figure 14. Transfer Characteristics




Figure 15. On-Region vs. Gate-To-Source Voltage




Figure 16. On-Resistance vs. Drain Current and Temperature




Figure 17. On-Resistance Variation with Temperature




Figure 18. Capacitance Variation

NTGD4167C




Figure 19. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 20. Diode Forward Voltage versus Current




Figure 21. Threshold Voltage




Figure 22. Single Pulse Maximum Power Dissipation




Figure 23. Maximum Rated Forward Biased Safe Operating Area

NTGD4167C




Figure 24. FET Thermal Response

ORDERING INFORMATION

Device	Package	Shipping [†]
NTGD4167CT1G	TSOP6 (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS

ON Semiconductor®





SCALE 2:1

TSOP-6

CASE 318G-02

ISSUE V

DATE 12 JUN 2012



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H.
5. PIN ONE INDICATOR MUST BE LOCATED IN THE INDICATED ZONE.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.01	0.06	0.10
b	0.25	0.38	0.50
c	0.10	0.18	0.26
D	2.90	3.00	3.10
E	2.50	2.75	3.00
E1	1.30	1.50	1.70
e	0.85	0.95	1.05
L	0.20	0.40	0.60
L2	0.25 BSC		
M	0°	—	10°

STYLE 1:

- PIN 1. DRAIN
- PIN 2. DRAIN
- PIN 3. GATE
- PIN 4. SOURCE
- PIN 5. DRAIN
- PIN 6. DRAIN

STYLE 2:

- PIN 1. EMITTER 2
- PIN 2. BASE 1
- PIN 3. COLLECTOR 1
- PIN 4. EMITTER 1
- PIN 5. BASE 2
- PIN 6. COLLECTOR 2

STYLE 3:

- PIN 1. ENABLE
- PIN 2. N/C
- PIN 3. R BOOST
- PIN 4. Vz
- PIN 5. V in
- PIN 6. V out

STYLE 4:

- PIN 1. N/C
- PIN 2. V in
- PIN 3. NOT USED
- PIN 4. GROUND
- PIN 5. ENABLE
- PIN 6. LOAD

STYLE 5:

- PIN 1. EMITTER 2
- PIN 2. BASE 2
- PIN 3. COLLECTOR 1
- PIN 4. EMITTER 1
- PIN 5. BASE 1
- PIN 6. COLLECTOR 2

STYLE 6:

- PIN 1. COLLECTOR
- PIN 2. COLLECTOR
- PIN 3. BASE
- PIN 4. EMITTER
- PIN 5. COLLECTOR
- PIN 6. COLLECTOR

STYLE 7:

- PIN 1. COLLECTOR
- PIN 2. COLLECTOR
- PIN 3. BASE
- PIN 4. N/C
- PIN 5. COLLECTOR
- PIN 6. EMITTER

STYLE 8:

- PIN 1. Vbus
- PIN 2. D(in)
- PIN 3. D(in)+
- PIN 4. D(out)+
- PIN 5. D(out)
- PIN 6. GND

STYLE 9:

- PIN 1. LOW VOLTAGE GATE
- PIN 2. DRAIN
- PIN 3. SOURCE
- PIN 4. DRAIN
- PIN 5. DRAIN
- PIN 6. HIGH VOLTAGE GATE

STYLE 10:

- PIN 1. D(OUT)+
- PIN 2. GND
- PIN 3. D(OUT)-
- PIN 4. D(IN)-
- PIN 5. VBUS
- PIN 6. D(IN)+

STYLE 11:

- PIN 1. SOURCE 1
- PIN 2. DRAIN 2
- PIN 3. DRAIN 2
- PIN 4. SOURCE 2
- PIN 5. GATE 1
- PIN 6. DRAIN 1/GATE 2

STYLE 12:

- PIN 1. I/O
- PIN 2. GROUND
- PIN 3. I/O
- PIN 4. I/O
- PIN 5. VCC
- PIN 6. I/O

STYLE 13:

- PIN 1. GATE 1
- PIN 2. SOURCE 2
- PIN 3. GATE 2
- PIN 4. DRAIN 2
- PIN 5. SOURCE 1
- PIN 6. DRAIN 1

STYLE 14:

- PIN 1. ANODE
- PIN 2. SOURCE
- PIN 3. GATE
- PIN 4. CATHODE/DRAIN
- PIN 5. CATHODE/DRAIN
- PIN 6. CATHODE/DRAIN

STYLE 15:

- PIN 1. ANODE
- PIN 2. SOURCE
- PIN 3. GATE
- PIN 4. DRAIN
- PIN 5. N/C
- PIN 6. CATHODE


STYLE 16:

- PIN 1. ANODE/CATHODE
- PIN 2. BASE
- PIN 3. EMITTER
- PIN 4. COLLECTOR
- PIN 5. ANODE
- PIN 6. CATHODE

STYLE 17:


- PIN 1. EMITTER
- PIN 2. BASE
- PIN 3. ANODE/CATHODE
- PIN 4. ANODE
- PIN 5. CATHODE
- PIN 6. COLLECTOR

RECOMMENDED SOLDERING FOOTPRINT*




DIMENSIONS: MILLIMETERS

GENERIC MARKING DIAGRAM*



IC



STANDARD

XXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
▪ = Pb-Free Package

XXX = Specific Device Code
M = Date Code
▪ = Pb-Free Package

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present.

DOCUMENT NUMBER:	98ASB14888C	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TSOP-6	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[NTGD4167CT1G](#)