

MCR703A Series

Preferred Device

Sensitive Gate Silicon Controlled Rectifiers Reverse Blocking Thyristors

PNPN devices designed for high volume, low cost consumer applications such as temperature, light and speed control; process and remote control; and warning systems where reliability of operation is critical.

Features

- Small Size
- Passivated Die Surface for Reliability and Uniformity
- Low Level Triggering and Holding Characteristics
- Recommend Electrical Replacement for C106
- Surface Mount Package – Case 369C
- To Obtain “DPAK” in Straight Lead Version (Shipped in Sleeves): Add '1' Suffix to Device Number, i.e., MCR706A1
- Epoxy Meets UL 94 V-0 @ 0.125 in
- ESD Ratings: Human Body Model, 3B > 8000 V
Machine Model, C > 400 V
- Pb-Free Packages are Available

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

| Rating | Symbol | Max | Unit |
|---|--------------------------|-------------------|------------------------|
| Peak Repetitive Off-State Voltage (Note 1) ($T_C = -40$ to $+110^\circ\text{C}$, Sine Wave, 50 to 60 Hz, $R_{GK} = 1\text{ k}\Omega$) MCR703A MCR706A MCR708A | V_{DRM} , V_{RRM} | 100 400 600 | V |
| Peak Non-Repetitive Off-State Voltage (Sine Wave, 50 to 60 Hz, $R_{GK} = 1\text{ k}\Omega$, $T_C = -40$ to $+110^\circ\text{C}$) MCR703A MCR706A MCR708A | V_{RSM} | 150 450 650 | V |
| On-State RMS Current (180° Conduction Angles; $T_C = 90^\circ\text{C}$) | $I_{T(RMS)}$ | 4.0 | A |
| Average On-State Current (180° Conduction Angles) $T_C = -40$ to $+90^\circ\text{C}$ $T_C = +100^\circ\text{C}$ | $I_{T(AV)}$ | 2.6 1.6 | A |
| Non-Repetitive Surge Current (1/2 Sine Wave, 60 Hz, $T_J = 110^\circ\text{C}$) (1/2 Sine Wave, 1.5 ms, $T_J = 110^\circ\text{C}$) | I_{TSM} | 25 35 | A |
| Circuit Fusing ($t = 8.3\text{ msec}$) | I^2t | 2.6 | A^2sec |
| Forward Peak Gate Power (Pulse Width $\leq 1.0\text{ }\mu\text{sec}$, $T_C = 90^\circ\text{C}$) | P_{GM} | 0.5 | W |
| Forward Average Gate Power ($t = 8.3\text{ msec}$, $T_C = 90^\circ\text{C}$) | $P_{G(AV)}$ | 0.1 | W |
| Forward Peak Gate Current (Pulse Width $\leq 1.0\text{ }\mu\text{sec}$, $T_C = 90^\circ\text{C}$) | I_{GM} | 0.2 | A |
| Operating Junction Temperature Range | T_J | -40 to $+110$ | $^\circ\text{C}$ |
| Storage Temperature Range | T_{stg} | -40 to $+150$ | $^\circ\text{C}$ |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.




ON Semiconductor®

<http://onsemi.com>



SCRs
4.0 AMPERES RMS
100 – 600 VOLTS




MARKING DIAGRAMS



DPAK
CASE 369C
STYLE 5



DPAK-3
CASE 369D
STYLE 5



Y = Year
WW = Work Week
70xA = Device Code
x = 3, 6 or 8
G = Pb-Free Package

PIN ASSIGNMENT

| | |
|---|---------|
| 1 | Gate |
| 2 | Anode |
| 3 | Cathode |
| 4 | Anode |

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

MCR703A Series

THERMAL CHARACTERISTICS

| Characteristic | Symbol | Max | Unit |
|---|-----------------|-----|----------------------|
| Thermal Resistance, Junction-to-Case | $R_{\theta JC}$ | 3.0 | $^{\circ}\text{C/W}$ |
| Thermal Resistance, Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 80 | $^{\circ}\text{C/W}$ |
| Maximum Lead Temperature for Soldering Purposes 1/8" from Case for 10 Seconds | T_L | 260 | $^{\circ}\text{C}$ |

2. Case 369C when surface mounted on minimum pad sizes recommended.

ELECTRICAL CHARACTERISTICS ($T_C = 25^{\circ}\text{C}$ unless otherwise noted)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|----------------|--------|-----|-----|-----|------|
|----------------|--------|-----|-----|-----|------|

OFF CHARACTERISTICS

| | | | | | |
|---|--------------------|---|---|-----|---------------|
| Peak Repetitive Forward or Reverse Blocking Current ($V_{AK} = \text{Rated } V_{DRM}$ or V_{RRM} ; $R_{GK} = 1 \text{ k}\Omega$) | I_{DRM}, I_{RRM} | – | – | 10 | μA |
| $T_C = 110^{\circ}\text{C}$ | | – | – | 200 | |

ON CHARACTERISTICS

| | | | | | |
|---|-----------|-----|------|-----|---------------|
| Peak Forward "On" Voltage ($I_{TM} = 8.2 \text{ A}$ Peak, Pulse Width = 1 to 2 ms, 2% Duty Cycle) | V_{TM} | – | – | 2.2 | V |
| Gate Trigger Current (Continuous dc) (Note 3) ($V_{AK} = 12 \text{ Vdc}$, $R_L = 24 \Omega$) | I_{GT} | – | 25 | 75 | μA |
| $T_C = 25^{\circ}\text{C}$ | | – | – | 300 | |
| $T_C = -40^{\circ}\text{C}$ | | | | | |
| Gate Trigger Voltage (Continuous dc) (Note 3) ($V_{AK} = 12 \text{ Vdc}$, $R_L = 24 \Omega$) | V_{GT} | – | – | 0.8 | V |
| $T_C = 25^{\circ}\text{C}$ | | – | – | 1.0 | |
| $T_C = -40^{\circ}\text{C}$ | | | | | |
| Gate Non-Trigger Voltage (Note 3) ($V_{AK} = 12 \text{ Vdc}$, $R_L = 100 \Omega$, $T_C = 110^{\circ}\text{C}$) | V_{GD} | 0.2 | – | – | V |
| Holding Current ($V_{AK} = 12 \text{ Vdc}$, $R_{GK} = 1 \text{ k}\Omega$) $T_C = 25^{\circ}\text{C}$ (Initiating Current = 20 mA) $T_C = -40^{\circ}\text{C}$ | I_H | – | – | 5.0 | mA |
| | | – | – | 10 | |
| Peak Reverse Gate Blocking Voltage ($I_{GR} = 10 \mu\text{A}$) | V_{RGM} | 10 | 12.5 | 18 | V |
| Peak Reverse Gate Blocking Current ($V_{GR} = 10 \text{ V}$) | I_{RGM} | – | – | 1.2 | μA |
| Total Turn-On Time (Source Voltage = 12 V, $R_S = 6 \text{ k}\Omega$) ($I_{TM} = 8.2 \text{ A}$, $I_{GT} = 2 \text{ mA}$, Rated V_{DRM}) (Rise Time = 20 ns, Pulse Width = 10 μs) | t_{gt} | – | 2.0 | – | μs |

DYNAMIC CHARACTERISTICS

| | | | | | |
|---|---------|---|----|-----|------------------------|
| Critical Rate of Rise of Off-State Voltage ($V_D = \text{Rated } V_{DRM}$, $R_{GK} = 1 \text{ k}\Omega$, Exponential Waveform, $T_C = 110^{\circ}\text{C}$) | dv/dt | – | 10 | – | $\text{V}/\mu\text{s}$ |
| Repetitive Critical Rate of Rise of On-State Current ($C_f = 60 \text{ Hz}$, $I_{PK} = 30 \text{ A}$, $PW = 100 \mu\text{s}$, $diG/dt = 1 \text{ A}/\mu\text{s}$) | di/dt | – | – | 100 | $\text{A}/\mu\text{s}$ |

3. R_{GK} current not included in measurement.

ORDERING INFORMATION

| Device | Package Type | Package | Shipping† |
|------------|--------------|-------------------|------------------|
| MCR703AT4 | DPAK | 369C | 2500 Tape & Reel |
| MCR703AT4G | DPAK | 369C (Pb-Free) | 2500 Tape & Reel |
| MCR706AT4 | DPAK | 369C | 2500 Tape & Reel |
| MCR706AT4G | DPAK | 369C (Pb-Free) | 2500 Tape & Reel |
| MCR708A | DPAK | 369C | 75 Units / Rail |
| MCR708AG | DPAK | 369C (Pb-Free) | 75 Units / Rail |
| MCR708A1 | DPAK-3 | 369D | 75 Units / Rail |
| MCR708A1G | DPAK-3 | 369D (Pb-Free) | 75 Units / Rail |
| MCR708AT4 | DPAK | 369C | 2500 Tape & Reel |
| MCR708AT4G | DPAK | 369C (Pb-Free) | 2500 Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MCR703A Series

Voltage Current Characteristic of SCR

| Symbol | Parameter |
|-----------|---|
| V_{DRM} | Peak Repetitive Off-State Forward Voltage |
| I_{DRM} | Peak Forward Blocking Current |
| V_{RRM} | Peak Repetitive Off-State Reverse Voltage |
| I_{RRM} | Peak Reverse Blocking Current |
| V_{TM} | Peak On-State Voltage |
| I_H | Holding Current |





Figure 1. RMS Current Derating




Figure 2. On-State Power Dissipation




Figure 3. On-State Characteristics




Figure 4. Transient Thermal Response

MCR703A Series




Figure 5. Typical Gate Trigger Current versus Junction Temperature




Figure 6. Typical Gate Trigger Voltage versus Junction Temperature




Figure 7. Typical Holding Current versus Junction Temperature





Figure 8. Typical Latching Current versus Junction Temperature

MCR703A Series

PACKAGE DIMENSIONS

DPAK CASE 369C-01 ISSUE A




- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES | | MILLIMETERS | |
|-----|-----------|-------|-------------|------|
| | MIN | MAX | MIN | MAX |
| A | 0.235 | 0.245 | 5.97 | 6.22 |
| B | 0.250 | 0.265 | 6.35 | 6.73 |
| C | 0.086 | 0.094 | 2.19 | 2.38 |
| D | 0.027 | 0.035 | 0.69 | 0.88 |
| E | 0.018 | 0.023 | 0.46 | 0.58 |
| F | 0.037 | 0.045 | 0.94 | 1.14 |
| G | 0.180 BSC | | 4.58 BSC | |
| H | 0.034 | 0.040 | 0.87 | 1.01 |
| J | 0.018 | 0.023 | 0.46 | 0.58 |
| K | 0.102 | 0.114 | 2.60 | 2.89 |
| L | 0.090 BSC | | 2.29 BSC | |
| R | 0.180 | 0.215 | 4.57 | 5.45 |
| S | 0.025 | 0.040 | 0.63 | 1.01 |
| U | 0.020 | --- | 0.51 | --- |
| V | 0.035 | 0.050 | 0.89 | 1.27 |
| Z | 0.155 | --- | 3.93 | --- |

- STYLE 5:
1. GATE
 2. ANODE
 3. CATHODE
 4. ANODE

SOLDERING FOOTPRINT*




SCALE 3:1 $\left(\frac{\text{mm}}{\text{inches}} \right)$

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MCR703A Series

PACKAGE DIMENSIONS

DDAK-3 CASE 369D-01 ISSUE B




NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES | | MILLIMETERS | |
|-----|-----------|-------|-------------|------|
| | MIN | MAX | MIN | MAX |
| A | 0.235 | 0.245 | 5.97 | 6.35 |
| B | 0.250 | 0.265 | 6.35 | 6.73 |
| C | 0.086 | 0.094 | 2.19 | 2.38 |
| D | 0.027 | 0.035 | 0.69 | 0.88 |
| E | 0.018 | 0.023 | 0.46 | 0.58 |
| F | 0.037 | 0.045 | 0.94 | 1.14 |
| G | 0.090 BSC | | 2.29 BSC | |
| H | 0.034 | 0.040 | 0.87 | 1.01 |
| J | 0.018 | 0.023 | 0.46 | 0.58 |
| K | 0.350 | 0.380 | 8.89 | 9.65 |
| R | 0.180 | 0.215 | 4.45 | 5.45 |
| S | 0.025 | 0.040 | 0.63 | 1.01 |
| V | 0.035 | 0.050 | 0.89 | 1.27 |
| Z | 0.155 | --- | 3.93 | --- |

STYLE 5:

- PIN 1. GATE
- ANODE
- CATHODE
- ANODE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[MCR703AT4](#) [MCR706AT4](#) [MCR708A](#) [MCR708A1](#) [MCR708AT4](#)