

# NTTFS4C25N

## MOSFET – Power, Single, N-Channel, $\mu$ 8FL 30 V, 27 A

### Features

- Low  $R_{DS(on)}$  to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### Applications

- DC-DC Converters
- Power Load Switch
- Notebook Battery Management

### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise stated)

| Parameter   |  | Symbol                     | Value       | Unit               |   |
|---|--|----------------------------|-------------|--------------------|---|
| Drain-to-Source Voltage   |  | $V_{DSS}$                  | 30          | V                  |   |
| Gate-to-Source Voltage  |  | $V_{GS}$                   | $\pm 20$    | V                  |   |
| Continuous Drain Current $R_{\theta JA}$ (Note 1)   | Steady State   | $T_A = 25^{\circ}\text{C}$ | $I_D$       | 7.7                | A |
|   |  | $T_A = 85^{\circ}\text{C}$ |             | 5.8                |   |
| Power Dissipation $R_{\theta JA}$ (Note 1)  |  | $T_A = 25^{\circ}\text{C}$ | $P_D$       | 1.63               | W |
| Continuous Drain Current $R_{\theta JA} \leq 10$ s (Note 1)   |  | $T_A = 25^{\circ}\text{C}$ | $I_D$       | 12.2               | A |
|   |  | $T_A = 85^{\circ}\text{C}$ |             | 9.1                |   |
| Power Dissipation $R_{\theta JA} \leq 10$ s (Note 1)  |  | $T_A = 25^{\circ}\text{C}$ | $P_D$       | 4.1                | W |
| Continuous Drain Current $R_{\theta JA}$ (Note 2)   |  | $T_A = 25^{\circ}\text{C}$ | $I_D$       | 5.0                | A |
|   |  | $T_A = 85^{\circ}\text{C}$ |             | 3.8                |   |
| Power Dissipation $R_{\theta JA}$ (Note 2)  |  | $T_A = 25^{\circ}\text{C}$ | $P_D$       | 0.69               | W |
| Continuous Drain Current $R_{\theta JC}$ (Note 1)   |  | $T_C = 25^{\circ}\text{C}$ | $I_D$       | 27                 | A |
|   |  | $T_C = 85^{\circ}\text{C}$ |             | 20                 |   |
| Power Dissipation $R_{\theta JC}$ (Note 1)  |  | $T_C = 25^{\circ}\text{C}$ | $P_D$       | 20.2               | W |
| Pulsed Drain Current  | $T_A = 25^{\circ}\text{C}$ , $t_p = 10\text{ }\mu\text{s}$ | $I_{DM}$                   | 81          | A                  |   |
| Operating Junction and Storage Temperature  |  | $T_J$ , $T_{stg}$          | -55 to +150 | $^{\circ}\text{C}$ |   |
| Source Current (Body Diode)   |  | $I_S$                      | 17          | A                  |   |
| Drain to Source $dV/dt$   |  | $dV/dt$                    | 6.0         | V/ns               |   |
| Single Pulse Drain-to-Source Avalanche Energy ( $T_J = 25^{\circ}\text{C}$ , $V_{DD} = 50\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_L = 16\text{ A}_{pk}$ , $L = 0.1\text{ mH}$ , $R_G = 25\text{ }\Omega$ ) (Note 3) |  | $E_{AS}$                   | 13          | mJ                 |   |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s)   |  | $T_L$                      | 260         | $^{\circ}\text{C}$ |   |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
2. Surface-mounted on FR4 board using the minimum recommended pad size.




ON Semiconductor®

<http://onsemi.com>


| $V_{(BR)DSS}$ | $R_{DS(on)}$ MAX        | $I_D$ MAX |
|---------------|-------------------------|-----------|
| 30 V          | 17 m $\Omega$ @ 10 V    | 27 A      |
|               | 26.5 m $\Omega$ @ 4.5 V |           |

### N-Channel MOSFET



WDFN8  
( $\mu$ 8FL)  
CASE 511AB

### MARKING DIAGRAM



4C25 = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

### ORDERING INFORMATION

| Device        | Package         | Shipping†          |
|---------------|-----------------|--------------------|
| NTTFS4C25NTAG | WDFN8 (Pb-Free) | 1500 / Tape & Reel |
| NTTFS4C25NTWG | WDFN8 (Pb-Free) | 5000 / Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

# NTTFS4C25N

3. This is the absolute maximum rating. Parts are 100% tested at  $T_J = 25^\circ\text{C}$ ,  $V_{GS} = 10\text{ V}$ ,  $I_L = 11\text{ Apk}$ ,  $E_{AS} = 6\text{ mJ}$ .

## THERMAL RESISTANCE MAXIMUM RATINGS

| Parameter   | Symbol          | Value | Unit               |
|---|-----------------|-------|--------------------|
| Junction-to-Case (Drain)                                | $R_{\theta JC}$ | 6.2   | $^\circ\text{C/W}$ |
| Junction-to-Ambient – Steady State (Note 4)             | $R_{\theta JA}$ | 76.7  |                    |
| Junction-to-Ambient – Steady State (Note 5)             | $R_{\theta JA}$ | 210   |                    |
| Junction-to-Ambient – ( $t \leq 10\text{ s}$ ) (Note 4) | $R_{\theta JA}$ | 30.8  |                    |

4. Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.  
5. Surface-mounted on FR4 board using the minimum recommended pad size.

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise specified)

| Parameter | Symbol | Test Condition | Min | Typ | Max | Unit |
|-----------|--------|----------------|-----|-----|-----|------|
|-----------|--------|----------------|-----|-----|-----|------|

### OFF CHARACTERISTICS

|   |                   |   |                           |      |           |                      |
|---|-------------------|---|---------------------------|------|-----------|----------------------|
| Drain-to-Source Breakdown Voltage                         | $V_{(BR)DSS}$     | $V_{GS} = 0\text{ V}$ , $I_D = 250\text{ }\mu\text{A}$  | 30                        |      |           | V                    |
| Drain-to-Source Breakdown Voltage (transient)             | $V_{(BR)DSSst}$   | $V_{GS} = 0\text{ V}$ , $I_{D(aval)} = 4.4\text{ A}$ ,<br>$T_{case} = 25^\circ\text{C}$ , $t_{transient} = 100\text{ ns}$ | 34                        |      |           | V                    |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $V_{(BR)DSS}/T_J$ |   |                           | 15.3 |           | mV/ $^\circ\text{C}$ |
| Zero Gate Voltage Drain Current                           | $I_{DSS}$         | $V_{GS} = 0\text{ V}$ ,<br>$V_{DS} = 24\text{ V}$   | $T_J = 25^\circ\text{C}$  |      | 1.0       | $\mu\text{A}$        |
|   |                   |   | $T_J = 125^\circ\text{C}$ |      | 10        |                      |
| Gate-to-Source Leakage Current                            | $I_{GSS}$         | $V_{DS} = 0\text{ V}$ , $V_{GS} = \pm 20\text{ V}$  |                           |      | $\pm 100$ | nA                   |

### ON CHARACTERISTICS (Note 6)

|  |                  |  |     |     |      |                      |
|--|------------------|--|-----|-----|------|----------------------|
| Gate Threshold Voltage                     | $V_{GS(TH)}$     | $V_{GS} = V_{DS}$ , $I_D = 250\text{ }\mu\text{A}$ | 1.3 |     | 2.2  | V                    |
| Negative Threshold Temperature Coefficient | $V_{GS(TH)}/T_J$ |  |     | 4.5 |      | mV/ $^\circ\text{C}$ |
| Drain-to-Source On Resistance              | $R_{DS(on)}$     | $V_{GS} = 10\text{ V}$ , $I_D = 10\text{ A}$       |     | 13  | 17   | m $\Omega$           |
|  |                  | $V_{GS} = 4.5\text{ V}$ , $I_D = 9\text{ A}$       |     | 21  | 26.5 |                      |
| Forward Transconductance                   | $g_{FS}$         | $V_{DS} = 1.5\text{ V}$ , $I_D = 15\text{ A}$      |     | 23  |      | S                    |
| Gate Resistance                            | $R_G$            | $T_A = 25^\circ\text{C}$                           |     | 1.0 |      | $\Omega$             |

### CHARGES AND CAPACITANCES

|                              |                   |  |  |       |  |    |
|------------------------------|-------------------|--|--|-------|--|----|
| Input Capacitance            | $C_{ISS}$         | $V_{GS} = 0\text{ V}$ , $f = 1\text{ MHz}$ , $V_{DS} = 15\text{ V}$    |  | 500   |  | pF |
| Output Capacitance           | $C_{OSS}$         |  |  | 295   |  |    |
| Reverse Transfer Capacitance | $C_{RSS}$         |  |  | 85    |  |    |
| Capacitance Ratio            | $C_{RSS}/C_{ISS}$ | $V_{GS} = 0\text{ V}$ , $V_{DS} = 15\text{ V}$ , $f = 1\text{ MHz}$    |  | 0.170 |  |    |
| Total Gate Charge            | $Q_{G(TOT)}$      | $V_{GS} = 4.5\text{ V}$ , $V_{DS} = 15\text{ V}$ ; $I_D = 20\text{ A}$ |  | 5.1   |  | nC |
| Threshold Gate Charge        | $Q_{G(TH)}$       |  |  | 0.9   |  |    |
| Gate-to-Source Charge        | $Q_{GS}$          |  |  | 1.7   |  |    |
| Gate-to-Drain Charge         | $Q_{GD}$          |  |  | 2.7   |  |    |
| Gate Plateau Voltage         | $V_{GP}$          |  |  | 3.3   |  | V  |
| Total Gate Charge            | $Q_{G(TOT)}$      | $V_{GS} = 10\text{ V}$ , $V_{DS} = 15\text{ V}$ ; $I_D = 20\text{ A}$  |  | 10.3  |  | nC |

### SWITCHING CHARACTERISTICS (Note 7)

6. Pulse Test: pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$ .  
7. Switching characteristics are independent of operating junction temperatures.

# NTTFS4C25N

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise specified)

| Parameter | Symbol | Test Condition | Min | Typ | Max | Unit |
|-----------|--------|----------------|-----|-----|-----|------|
|-----------|--------|----------------|-----|-----|-----|------|

### SWITCHING CHARACTERISTICS (Note 7)

|                     |              |  |  |     |  |    |
|---------------------|--------------|--|--|-----|--|----|
| Turn-On Delay Time  | $t_{d(ON)}$  | $V_{GS} = 4.5\text{ V}, V_{DS} = 15\text{ V},$<br>$I_D = 10\text{ A}, R_G = 3.0\ \Omega$ |  | 8.0 |  | ns |
| Rise Time           | $t_r$        |  |  | 32  |  |    |
| Turn-Off Delay Time | $t_{d(OFF)}$ |  |  | 10  |  |    |
| Fall Time           | $t_f$        |  |  | 3.0 |  |    |
| Turn-On Delay Time  | $t_{d(ON)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 15\text{ V},$<br>$I_D = 15\text{ A}, R_G = 3.0\ \Omega$  |  | 4.0 |  | ns |
| Rise Time           | $t_r$        |  |  | 25  |  |    |
| Turn-Off Delay Time | $t_{d(OFF)}$ |  |  | 13  |  |    |
| Fall Time           | $t_f$        |  |  | 2.0 |  |    |

### DRAIN-SOURCE DIODE CHARACTERISTICS

|                         |          |   |                           |  |      |     |    |
|-------------------------|----------|---|---------------------------|--|------|-----|----|
| Forward Diode Voltage   | $V_{SD}$ | $V_{GS} = 0\text{ V},$<br>$I_S = 10\text{ A}$                                     | $T_J = 25^\circ\text{C}$  |  | 0.87 | 1.2 | V  |
|                         |          |   | $T_J = 125^\circ\text{C}$ |  | 0.75 |     |    |
| Reverse Recovery Time   | $t_{RR}$ | $V_{GS} = 0\text{ V}, dI_S/dt = 100\text{ A}/\mu\text{s},$<br>$I_S = 30\text{ A}$ |                           |  | 18.2 |     | ns |
| Charge Time             | $t_a$    |   |                           |  | 9.8  |     |    |
| Discharge Time          | $t_b$    |   |                           |  | 8.4  |     |    |
| Reverse Recovery Charge | $Q_{RR}$ |   |                           |  | 5.7  |     | nC |

6. Pulse Test: pulse width  $\leq 300\ \mu\text{s}$ , duty cycle  $\leq 2\%$ .

7. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs.  $V_{GS}$




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy vs. Starting Junction Temperature

# NTTFS4C25N

## TYPICAL CHARACTERISTICS




Figure 13. Thermal Response




Figure 14.  $G_{FS}$  vs.  $I_D$




Figure 15. Avalanche Characteristics


# NTTFS4C25N

## PACKAGE DIMENSIONS

WDFN8 3.3x3.3, 0.65P

CASE 511AB

ISSUE D




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

| DIM | MILLIMETERS |      |      | INCHES    |       |       |
|-----|-------------|------|------|-----------|-------|-------|
|     | MIN         | NOM  | MAX  | MIN       | NOM   | MAX   |
| A   | 0.70        | 0.75 | 0.80 | 0.028     | 0.030 | 0.031 |
| A1  | 0.00        | ---  | 0.05 | 0.000     | ---   | 0.002 |
| b   | 0.23        | 0.30 | 0.40 | 0.009     | 0.012 | 0.016 |
| c   | 0.15        | 0.20 | 0.25 | 0.006     | 0.008 | 0.010 |
| D   | 3.30 BSC    |      |      | 0.130 BSC |       |       |
| D1  | 2.95        | 3.05 | 3.15 | 0.116     | 0.120 | 0.124 |
| D2  | 1.98        | 2.11 | 2.24 | 0.078     | 0.083 | 0.088 |
| E   | 3.30 BSC    |      |      | 0.130 BSC |       |       |
| E1  | 2.95        | 3.05 | 3.15 | 0.116     | 0.120 | 0.124 |
| E2  | 1.47        | 1.60 | 1.73 | 0.058     | 0.063 | 0.068 |
| E3  | 0.23        | 0.30 | 0.40 | 0.009     | 0.012 | 0.016 |
| e   | 0.65 BSC    |      |      | 0.026 BSC |       |       |
| G   | 0.30        | 0.41 | 0.51 | 0.012     | 0.016 | 0.020 |
| K   | 0.65        | 0.80 | 0.95 | 0.026     | 0.032 | 0.037 |
| L   | 0.30        | 0.43 | 0.56 | 0.012     | 0.017 | 0.022 |
| L1  | 0.06        | 0.13 | 0.20 | 0.002     | 0.005 | 0.008 |
| M   | 1.40        | 1.50 | 1.60 | 0.055     | 0.059 | 0.063 |
| θ   | 0 °         | ---  | 12 ° | 0 °       | ---   | 12 °  |

### SOLDERING FOOTPRINT\*



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marketing.pdf](http://www.onsemi.com/site/pdf/Patent-Marketing.pdf). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada  
Europe, Middle East and Africa Technical Support:  
Phone: 421 33 790 2910  
Japan Customer Focus Center  
Phone: 81-3-5817-1050

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor:](#)

[NTTFS4C25NTWG](#) [NTTFS4C25NTAG](#)