


Octal Buffer/Line Driver with 3-STATE Outputs

74VHC240


TSSOP20, 4.4x6.5
CASE 948AQ

General Description


The VHC240 is an advanced high speed CMOS octal bus buffer fabricated with silicon gate CMOS technology. It achieves high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation. The VHC240 is an inverting 3-STATE buffer having two active-LOW output enables. This device is designed to drive buslines or buffer memory address registers.

An input protection circuit ensures that 0 V to 5.5 V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5 V to 3 V systems and two supply systems such as battery backup. This circuit prevents device destruction due to mismatched supply and input voltages.

Features

- High Speed: $t_{PD} = 3.6 \text{ ns}$ (Typ) at $T_A = 25^\circ\text{C}$
- Low Power Dissipation: $I_{CC} = 4 \mu\text{A}$ (Max) @ $T_A = 25^\circ\text{C}$
- High Noise Immunity: $V_{NIH} = V_{NIL} = 28\% V_{CC}$ (Min)
- Power Down Protection is Provided on All Inputs
- Low Noise: $V_{OLP} = 0.9 \text{ V}$ (Max)
- Pin and Function Compatible with 74HC240
- This is a Pb-Free Device


MARKING DIAGRAM



XXXXXX = Specific Device Code
A = Assembly Location
L = Wafer Lot
Y = Year
W = Work Week
■ = Pb-Free Package

(Note: Microdot may be in either location)

CONNECTION DIAGRAM



PIN DESCRIPTIONS

Pin Names	Description
$\overline{OE}_1, \overline{OE}_2$	3-STATE Output Enable Inputs
I_0-I_7	Inputs
$\overline{O}_0-\overline{O}_7$	Outputs 3-STATE Outputs

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.

74VHC240

Logic Symbol




Figure 1. Logic Symbol

TRUTH TABLES

Inputs		Outputs
\overline{OE}_1	I_n	(Pins 12, 14, 16, 18)
L	H	H
L	L	L
H	X	Z

Inputs		Outputs
\overline{OE}_1	I_n	(Pins 3, 5, 7, 9)
L	H	H
L	L	L
H	X	Z

H = HIGH Voltage Level
 L = LOW Voltage Level
 X = Immaterial
 Z = High Impedance

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter		Value	Unit
V_{CC}	DC Supply Voltage		-0.5 to +6.5	V
V_{IN}	DC Input Voltage		-0.5 to +6.5	V
V_{OUT}	DC Output Voltage		-0.5 to $V_{CC} + 0.5$	V
I_{IN}	DC Input Current, per Pin		± 20	mA
I_{OUT}	DC Output Current, per Pin		± 25	mA
I_{CC}	DC Supply Current, V_{CC} and GND Pins		± 75	mA
I_{IK}	Input Clamp Current		-20	mA
I_{OK}	Output Clamp Current		± 20	mA
T_{STG}	Storage Temperature Range		-65 to +150	°C
T_L	Lead Temperature, 1 mm from Case for 10 Seconds		260	°C
T_J	Junction Temperature under Bias		+150	°C
θ_{JA}	Thermal Resistance (Note 2)		150	°C/W
P_D	Power Dissipation in Still Air at 25°C		833	mW
MSL	Moisture Sensitivity		Level 1	
F_R	Flammability Rating	Oxygen Index: 28 to 34	UL 94 V-0 @ 0.240 in	
V_{ESD}	ESD Withstand Voltage (Note 3)	Human Body Model	2000	V
		Charged Device Model	N/A	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Applicable to devices with outputs that may be tri-stated.
2. Measured with minimum pad spacing on an FR4 board, using 76 mm-by-114 mm, 2-ounce copper trace no air flow per JESD51-7.
3. HBM tested to EIA / JESD22-A114-A. CDM tested to JESD22-C101-A. JEDEC recommends that ESD qualification to EIA/JESD22-A115A (Machine Model) be discontinued.

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter		Min	Max	Unit
V _{CC}	DC Supply Voltage		2.0	5.5	V
V _{IN}	DC Input Voltage (Note 4)		0	5.5	V
V _{OUT}	DC Output Voltage (Note 4)		0	V _{CC}	V
T _A	Operating Temperature		−40	+85	°C
t _r , t _f	Input Rise or Fall Rate	V _{CC} = 3.0 V to 3.6 V	0	100	ns/V
		V _{CC} = 4.5 V to 5.5 V	0	20	

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

4. Unused inputs must always be tied to an appropriate logic voltage level (e.g., either GND or V_{CC}). Unused outputs must be left open.

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = 25^\circ\text{C}$			$T_A = -40^\circ\text{C to }+85^\circ\text{C}$		Unit
				Min	Typ	Max	Min	Max	
V_{IH}	HIGH Level Input Voltage		2.0	1.50	–	–	1.50	–	V
			3.0–5.5	$0.7 \times V_{CC}$	–	–	$0.7 \times V_{CC}$	–	
V_{IL}	LOW Level Input Voltage		2.0	–	–	0.50	–	0.50	V
			3.0–5.5	–	–	$0.3 \times V_{CC}$	–	$0.3 \times V_{CC}$	
V_{OH}	HIGH Level Output Voltage	$V_{IN} = V_{IH}$ or V_{IL}	$I_{OH} = -50\text{ }\mu\text{A}$	2.0	1.9	2.0	–	1.9	V
				3.0	2.9	3.0	–	2.9	
				4.5	4.4	4.5	–	4.4	
			$I_{OH} = -4\text{ mA}$	3.0	2.58	–	–	2.48	
			$I_{OH} = -8\text{ mA}$	4.5	3.94	–	–	3.80	
V_{OL}	LOW Level Output Voltage	$V_{IN} = V_{IH}$ or V_{IL}	$I_{OL} = 50\text{ }\mu\text{A}$	2.0	–	0.0	0.1	–	V
				3.0	–	0.0	0.1	–	
				4.5	–	0.0	0.1	–	
			$I_{OL} = 4\text{ mA}$	3.0	–	–	0.36	–	0.44
			$I_{OL} = 8\text{ mA}$	4.5	–	–	0.36	–	0.44
I_{OZ}	3–STATE Output Off–State Current	$V_{IN} = V_{IH}$ or V_{IL} ; $V_{OUT} = V_{CC}$ or GND	5.5	–	–	± 0.25	–	± 2.5	μA
I_{IN}	Input Leakage Current	$V_{IN} = 5.5\text{ V}$ or GND	0–5.5	–	–	± 0.1	–	± 1.0	μA
I_{CC}	Quiescent Supply Current	$V_{IN} = V_{CC}$ or GND	5.5	–	–	4.0	–	40.0	μA

NOISE CHARACTERISTICS

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = 25^\circ\text{C}$		Unit
				Typ	Limits	
V_{OLP} (Note 5)	Quiet Output Maximum Dynamic V_{OL}	$C_L = 50\text{ pF}$	5.0	0.6	0.9	V
V_{OLV} (Note 5)	Quiet Output Minimum Dynamic V_{OL}	$C_L = 50\text{ pF}$	5.0	–0.6	–0.9	V
V_{IHD} (Note 5)	Minimum HIGH Level Dynamic Input Voltage	$C_L = 50\text{ pF}$	5.0	–	3.5	V
V_{ILD} (Note 5)	Maximum LOW Level Dynamic Input Voltage	$C_L = 50\text{ pF}$	5.0	–	1.5	V

5. Parameter guaranteed by design.

74VHC240

AC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Conditions		V _{CC} (V)	T _A = 25°C			T _A = −40°C to +85°C		Unit
					Min	Typ	Max	Min	Max	
t _{PLH} , t _{PHL}	Propagation Delay Time		C _L = 15 pF	3.3 ±0.3	–	5.3	7.5	1.0	9.0	ns
			C _L = 50 pF		–	7.8	11.0	1.0	12.5	
			C _L = 15 pF	5.0 ±0.5	–	3.6	5.5	1.0	6.5	
			C _L = 50 pF		–	5.1	7.5	1.0	8.5	
t _{PZL} , t _{PZH}	3–STATE Output Enable Time	R _L = 1 kΩ	C _L = 15 pF	3.3 ±0.3	–	6.6	10.6	1.0	12.5	ns
			C _L = 50 pF		–	9.1	14.1	1.0	16.0	
			C _L = 15 pF	5.0 ±0.5	–	4.7	7.3	1.0	8.5	
			C _L = 50 pF		–	6.2	9.3	1.0	10.5	
t _{PLZ} , t _{PHZ}	3–STATE Output Disable Time	R _L = 1 kΩ	C _L = 50 pF	3.3 ±0.3	–	10.3	14.0	1.0	16.0	ns
			C _L = 50 pF	5.0 ±0.5	6.7	–	9.2	1.0	10.5	
t _{OSLH} , t _{OSHL}	Output to Output Skew	(Note 6)	C _L = 50 pF	3.3 ±0.3	–	–	1.5	–	1.5	ns
			C _L = 50 pF	5.0 ±0.5	–	–	1.0	–	1.0	
C _{IN}	Input Capacitance	V _{CC} = Open			–	4	10	–	10	pF
C _{OUT}	Output Capacitance	V _{CC} = 5.0 V			–	6	–	–	–	pF
C _{PD}	Power Dissipation Capacitance	(Note 7)			–	17	–	–	–	pF

6. Parameter guaranteed by design. t_{OSLH} – |t_{PLHmax} – t_{PLHmin}|; t_{OSHL} – |t_{PHLmax} – t_{PHLmin}|

7. C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I_{CC} (opr.) = C_{PD} · V_{CC} · f_{IN} + I_{CC}/8 (per bit).


ORDERING INFORMATION

Device	Marking	Package	Shipping†
74VHC240MTCX	VHC 240	TSSOP20 (Pb–Free)	2500 Units / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


TSSOP20, 4.4x6.5
CASE 948AQ
ISSUE A

DATE 19 MAR 2009




TOP VIEW

SYMBOL	MIN	NOM	MAX
A			1.20
A1	0.05		0.15
A2	0.80		1.05
b	0.19		0.30
c	0.09		0.20
D	6.40	6.50	6.60
E	6.30	6.40	6.50
E1	4.30	4.40	4.50
e	0.65 BSC		
L	0.45	0.60	0.75
L1	1.00 REF		
θ	0°		8°



SIDE VIEW



END VIEW

Notes:

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MO-153.

DOCUMENT NUMBER:	98AON34453E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TSSOP20, 4.4X6.5	PAGE 1 OF 1

onsemi and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[74VHC240SJX](#) [74VHC240MTC](#) [74VHC240MTCX](#) [74VHC240SJ](#) [74VHC240M](#) [74VHC240MX](#)