

AP0102AT

Image Signal Processor, 1 MP

Product Overview

For complete documentation, see the data sheet.

AP0102AT is a dedicated automotive image co-processor that enables flexible camera platforms using high performance ON Semiconductor megapixel high dynamic range (HDR) sensors. The two-chip solution of sensor and co-processor allows for multiple camera price and performance points with re-use of circuit board design, fast time to market and design flexibility. Sensor performance is enhanced by the reduction in heat resulting from a separate co-processor chip while at the same time enabling high performance features. The AP0102AT supports 185-degree fisheye lens distortion correction, perspective correction and multiple view options such as split side view, triptych and trailer hitch. This co-processor works with ON Semiconductor's AR0132AT, AR0140AT and AR0136AT HDR automotive sensors, and is ideal for digital rear view cameras.

Features

- HDR

Applications

- Automotive

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Frame Rate (fps)	Video	Output Format	Compatible Sensors	Package Type
AP0102AT2L00 XPGA0-DR		<div><div>A</div><div>Pb</div><div>P</div><div>H</div></div>	Active	45				VFBGA-100
AP0102AT2L00 XPGA0-TR		<div><div>A</div><div>Pb</div><div>P</div><div>H</div></div>	Active	45				VFBGA-100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[AP0102AT2L00XPGA0-DR](#) [AP0102AT2L00XPGA0-TR](#)