

Small Signal Diode

BAS29

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted.)


| Symbol | Parameter | Value | Unit |
|--------------------|---------------------------------------------------------------------------------------------|-------------|--------|
| V _{RRM} | Maximum Repetitive Reverse Voltage | 120 | V |
| I _{F(AV)} | Average Rectified Forward Current | 200 | mA |
| I _{FSM} | Non-Repetitive Peak Forward Current Pulse Width = 1.0 Second Pulse Width = 1.0 Second | 1.0 2.0 | A A |
| T _{STG} | Storage Temperature Range | -55 to +150 | °C |
| T _J | Operating Junction Temperature | 150 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. These ratings are based on a maximum junction temperature of 150°C.
2. These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

THERMAL CHARACTERISTICS


| Symbol | Parameter | Value | Unit |
|------------------|-----------------------------------------|-------|------|
| P _D | Power Dissipation | 350 | mW |
| R _{θJA} | Thermal Resistance, Junction to Ambient | 357 | °C/W |



SOT-23 (TO-236)
CASE 318



MARKING DIAGRAM



L20 = Specific Device Code
M = Data Code

ORDERING INFORMATION

| Device | Package | Shipping [†] |
|--------|-------------------------------------|-----------------------|
| BAS29 | SOT-23-3 (Pb-Free / Halide Free) | 3000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted.)

| Symbol | Parameter | Test Conditions | Min | Max | Unit |
|-----------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------|-----|--------------------------------------|----------|
| V _R | Breakdown Voltage | I _R = 1.0 mA | 120 | – | V |
| V _{F*} | Forward Voltage | I _F = 10 mA I _F = 50 mA I _F = 100 mA I _F = 200 mA I _F = 400 mA | – | 0.75 0.84 0.90 1.00 1.25 | V |
| I _{R*} | Reverse Current | V _R = 90 V V _R = 90 V, T _A = 150°C | – | 100 100 | nA μA |
| C _T | Total Capacitance | V _R = 0, f = 1.0 MHz | – | 2.0 | pF |
| t _{rr} | Reverse Recovery Time | I _F = I _R = 30 mA, I _{RR} = 3.0 mA, R _L = 100 Ω | – | 50 – | ns |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

*Pulse test: Pulse width = 300 μs, Duty Cycle = 2%

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[BAS29](#)