


OD6038 XC Series



DC Fan 12V

60x38mm (2.36"x 1.5")




Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector Weight: ~ 125 g * Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer m1	
Connecion	3x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp		
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)		

Part Number	OD6038-12HBXC01A
Nominal Voltage	12V DC
Voltage Range	10.8 ~ 13.2V DC
Nominal Current	2.10 A
Rated Power	28.8 W
Rated Speed (RPM)	14500
Airflow (CFM)	76
Noise Level (dB)	64
Max. Static Pressure	2.4" H ₂ O

*Output type.....Open collector type

*Electrical design suggestion:



*Transistor Q1 at "ON" position
Collector current..... I_c =10mA Max
Saturation Voltage..... V_{OL} =1.0V Max
(Between Collector and Emitter at I_c =10mA)


*Transistor Q1 at "OFF" position
Release Voltage..... V_{OH} =15V Max

OD6038 XC Series



DC Fan 12V


60x38mm (2.36"x 1.5")



Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector PWM Input Weight: ~ 125 g * Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer Blue PWM	
Connecion	4x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp		
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C	m1	
Life (L10)	70,000 hours (40C)		

Part Number	OD6038-12HBXC10A
Nominal Voltage	12V DC
Voltage Range	10.8 ~ 13.2V DC
Nominal Current	2.10 A
Rated Power	28.8 W
Rated Speed (RPM)	14500
Airflow (CFM)	76
Noise Level (dB)	64
Max. Static Pressure	2.4" H ₂ O

(External signal function design is decided by customer)




- *TRANSISTOR Q1 AT "ON" POSITION
COLLECTOR CURRENT----- $I_c = 10\text{mA MAX}$
SATURATION VOLTAGE----- $V_{ol} = 1\text{ V MAX}$
- *TRANSISTOR Q1 AT "OFF" POSITION
RELEASE VOLTAGE----- $V_{oh} = 15\text{ V MAX}$
- *DIGITAL PWM SPEED CONTROL POSITION
PWM INPUT VOLTAGE HIGH----- $V_{ih} = 5.5\text{ V MAX}$
PWM INPUT VOLTAGE LOW----- $V_{il} = 0.5\text{ V MAX}$
- *PWM INPUT FREQUENCY----- $FPWM: 18\text{KHZ} \sim 30\text{KHZ}$

OD6038 XC Series



DC Fan 12V

60x38mm (2.36"x 1.5")




Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector	
Connecion	3x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC	Weight: ~ 125 g	
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp	* Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer	
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)	m1	

Part Number	OD6038-12HHBXC01A
Nominal Voltage	12V DC
Voltage Range	10.8 ~ 13.2V DC
Nominal Current	2.70 A
Rated Power	36 W
Rated Speed (RPM)	16000
Airflow (CFM)	86
Noise Level (dB)	66
Max. Static Pressure	2.95" H2O

*Output type.....Open collector type

*Electrical design suggestion:



*Transistor Q1 at "ON" position
Collector current..... I_c =10mA Max
Saturation Voltage..... V_{OL} =1.0V Max
(Between Collector and Emitter at I_c =10mA)


*Transistor Q1 at "OFF" position
Release Voltage..... V_{OH} =15V Max

OD6038 XC Series



DC Fan 12V


60x38mm (2.36"x 1.5")



Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector PWM Input Weight: ~ 125 g * Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer Blue PWM	
Connection	4x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp		
Temperature Range	-10C ~ 70C		
Storage Temperature	-40C ~ +80C	m1	
Life (L10)	70,000 hours (40C)		

Part Number	OD6038-12HHBXC10A
Nominal Voltage	12V DC
Voltage Range	10.8 ~ 13.2V DC
Nominal Current	2.70 A
Rated Power	36 W
Rated Speed (RPM)	16000
Airflow (CFM)	86
Noise Level (dB)	66
Max. Static Pressure	2.95" H ₂ O

(External signal function design is decided by customer)




- *TRANSISTOR Q1 AT "ON" POSITION
- COLLECTOR CURRENT----- $I_c = 10\text{mA MAX}$
- SATURATION VOLTAGE----- $V_{ol} = 1\text{ V MAX}$
- *TRANSISTOR Q1 AT "OFF" POSITION
- RELEASE VOLTAGE----- $V_{oh} = 15\text{ V MAX}$
- *DIGITAL PWM SPEED CONTROL POSITION
- PWM INPUT VOLTAGE HIGH----- $V_{ih} = 5.5\text{ V MAX}$
- PWM INPUT VOLTAGE LOW----- $V_{il} = 0.5\text{ V MAX}$
- *PWM INPUT FREQUENCY----- $FPWM: 18\text{KHZ} \sim 30\text{KHZ}$


OD6038 XC Series



DC Fan 12V

60x38mm (2.36"x 1.5")




Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector Weight: ~ 125 g * Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer	
Connecion	3x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp	m1	
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)		

Part Number	OD6038-12LBXC01A
Nominal Voltage	12V DC
Voltage Range	10.8 ~ 13.2V DC
Nominal Current	1.45 A
Rated Power	21.6 W
Rated Speed (RPM)	13000
Airflow (CFM)	68
Noise Level (dB)	61
Max. Static Pressure	1.95" H ₂ O

*Output type.....Open collector type

*Electrical design suggestion:



*Transistor Q1 at "ON" position
Collector current..... I_c =10mA Max
Saturation Voltage..... V_{OL} =1.0V Max
(Between Collector and Emitter at I_c =10mA)


*Transistor Q1 at "OFF" position
Release Voltage..... V_{OH} =15V Max

OD6038 XC Series



DC Fan 24V


60x38mm (2.36"x 1.5")



Frame & Impeller	PBT, UL94V-O plastic	Tachometer - Open Collector PWM Input Weight: ~ 125 g * Connection UL1007, 24AWG, ~320mm Red (+) Black (-) White Tachometer Blue PWM	
Connection	4x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 minute at 500 VAC, max leakage < 500 MicroAmp		
Temperature Range	-10C ~ 70C		
Storage Temperature	-40C ~ +80C	m1	
Life (L10)	70,000 hours (40C)		

Part Number	OD6038-24HHBXC10A
Nominal Voltage	24V DC
Voltage Range	21.6 ~ 26.4V DC
Nominal Current	1.25 A
Rated Power	30 W
Rated Speed (RPM)	16000
Airflow (CFM)	86
Noise Level (dB)	69.5
Max. Static Pressure	2.95" H ₂ O

(External signal function design is decided by customer)



- *TRANSISTOR Q1 AT "ON" POSITION
- COLLECTOR CURRENT----- $I_c = 10\text{mA MAX}$
- SATURATION VOLTAGE----- $V_{OL} = 1\text{ V MAX}$
- *TRANSISTOR Q1 AT "OFF" POSITION
- RELEASE VOLTAGE----- $V_{OH} = 15\text{ V MAX}$
- *DIGITAL PWM SPEED CONTROL POSITION
- PWM INPUT VOLTAGE HIGH----- $V_{IH} = 5.5\text{ V MAX}$
- PWM INPUT VOLTAGE LOW----- $V_{IL} = 0.5\text{ V MAX}$
- *PWM INPUT FREQUENCY----- $FPWM: 18\text{KHZ} \sim 30\text{KHZ}$

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OD6038-12HHBXC01A](#) [OD6038-24HHBXC10A](#) [OD6038-12HHBXC10A](#) [OD6038-12LBXC01A](#)