


OD8032 Series



DC Fan - 12, 24, 48V
80x32mm (3.15"x 1.25")



Frame	PBT, UL94V-0 plastic	<u>Available Options</u> Tachometer (FG) Alarm (RD) Thermal Speed Control (Thermistor) PWM Input (Manual Speed Control) <u>Operating Temperature</u> Ball: -20C ~ +70C Sleeve: 10C ~ +50C Bearing <u>Storage Temp</u> -40C ~ +80C <u>Life Expectancy (L10)</u> Ball: 70,000 hours (40C) Sleeve: 35,000 hours (40C) Weight: ~ 0.24 lbs. m1	
Impeller	PBT, UL94V-0 plastic		
Connection	2x Lead wires (24AWG)		
Motor	Brushless DC, auto restart, polarity protected		
Bearing System	Dual ball or Sleeve		
Insulation Resistance	>100M ohm between lead-wire and frame (500VDC)		
Dielectric Strength	1 min at 1500 VAC, 50/60Hz		


Model Number	Speed (RPM)	Airflow (CFM)	Noise (dB)	Volts DC	Voltage Range	Real Current (Amps)	Max. Static Pressure (\"H ₂ O)
OD8032-12H*	3800	49.8	41.0	12	10.8~13.2	0.19	.28
OD8032-12M*	3400	44.8	36.7	12	10.8~13.2	0.16	.24
OD8032-12L*	3000	40.0	35.0	12	10.8~13.2	0.11	.19
OD8032-24H*	3800	49.8	41.8	24	21.6~26.4	0.12	.28
OD8032-24M*	3400	44.8	36.7	24	21.6~26.4	0.10	.24
OD8032-24L*	3000	39.6	35.5	24	21.6~26.4	0.07	.19
OD8032-48H*	3800	50.0	42.0	48	24~56	0.07	.28
OD8032-48L*	3000	39.6	35.5	48	24~56	0.06	.19

* Indicate "B" (Ball Bearing), "S" (Sleeve Bearing)

OD8032-12HHB02A



DC Fan, 12VDC
80x32mm (3.15x1.25in)




Frame & Impeller	PBT, UL94V-0 plastic	Available Options IP55 Other speeds and voltages Tachometer PWM *Connection: Wire Leads - UL1007 24AWG Red(+), Black (-), Yellow Alarm Weight: 108 g	
Connection	3x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 second at 500VAC max leakage 500 microamp		
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)		

Model Number	OD8032-12HHB02A	Output of locked signal *Output type.....Open collector type *Electrical design suggestion: (External signal function design is decided by customer) *Transistor Q1 at "ON" position Collector current.....$I_C=5mA$ Max Saturation Voltage.....$V_{CE}=1.0V$ Max (Between Collector and Emitter at $I_C=5mA$) *Transistor Q1 at "OFF" position Release Voltage.....$V_{CE}=15V$ Max *Output waveform
Part Number	184151231	
Nominal Voltage	12 VDC	
Voltage Range	7~13.2 VDC	
Nominal Current	.23 A	
Rated Power	4.56 Watts	
Rated Speed (RPM)	4200	
Airflow (CFM)	55.5	
Noise Level (dB)	44	
Max. Static Pressure	.32 "H ₂ O	

OD8032-24HHB



DC Fan, 24VDC
80x32mm (3.15x1.25in)




Frame & Impeller	PBT, UL94V-0 plastic	<u>Available Options</u> IP55 Other speeds and voltages Tachometer PWM Alarm *Connection: Wire Leads - UL1007 24AWG Red(+), Black (-), Weight: 108 g	
Connection	2x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 second at 500VAC max leakage 500 microamp		
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)		

Model Number	OD8032-24HHB
Part Number	184251001
Nominal Voltage	24 VDC
Voltage Range	17~26.4 VDC
Nominal Current	.15 A
Rated Power	4.32 Watts
Rated Speed (RPM)	4200
Airflow (CFM)	55.5
Noise Level (dB)	44
Max. Static Pressure	.32 "H ₂ O

OD8032-24HHB02A



DC Fan, 24VDC
80x32mm (3.15x1.25in)



Frame & Impeller	PBT, UL94V-0 plastic	Available Options IP55 Other speeds and voltages Tachometer PWM *Connection: Wire Leads - UL1007 24AWG Red(+), Black (-), Yellow Alarm Weight: 108 g	
Connection	3x Lead wires *		
Motor	Brushless DC, auto restart, polarity protected.		
Bearing System	Dual ball bearing		
Insulation Resistance	Min. 10M at 500VDC		
Dielectric Strength	1 second at 500VAC max leakage 500 microamp		
Temperature Range	-10C ~ +70C		
Storage Temperature	-40C ~ +80C		
Life (L10)	70,000 hours (40C)		

Model Number	OD8032-24HHB02A	Output of locked signal *Output type.....Open collector type *Electrical design suggestion: (External signal function design is decided by customer) *Transistor Q1 at "ON" position Collector current..... $I_C=10\text{mA Max}$ Saturation Voltage..... $V_{CE}=1.0\text{V Max}$ (Between Collector and Emitter at $I_C=10\text{mA}$) *Transistor Q1 at "OFF" position Release Voltage..... $V_{ON}=30\text{V Max}$ *Output waveform Supply voltage: LOCK, LOCK RELEASE Fan rotation: (High/Low speed indicator) Fan current: (High/Low current indicator) Locked signal: (Pulse width $T \leq 10\text{SEC}$)
Part Number	184251231	
Nominal Voltage	24 VDC	
Voltage Range	17~26.4 VDC	
Nominal Current	.15 A	
Rated Power	4.32 Watts	
Rated Speed (RPM)	4200	
Airflow (CFM)	55.5	
Noise Level (dB)	44	
Max. Static Pressure	.32 "H ₂ O	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OD8032-24MB](#) [OD8032-24HB](#) [OD8032-24LB](#) [OD8032-12LB](#) [OD8032-12HB](#) [OD8032-12MB](#) [OD8032-48LB](#)
[OD8032-48MB](#) [OD8032-24HS](#) [OD8032-12HB01](#) [OD8032-24HB01A](#) [OD8032-48HS](#) [OD8032-12HS](#) [OD8032-12MS](#)
[OD8032-24HHB02A](#) [OD8032-24HHB](#) [OD8032-12HHB02A](#) [OD8032-48HB01A](#)