



MCH3105/MCH3205

Bipolar Transistor

(-50V, (-)3A, Low $V_{CE(sat)}$, (PNP)NPN Single MCPH3

ON Semiconductor®

<http://onsemi.com>

Applicaitions

- DC / DC converters, relay drivers, lamp drivers, motor drivers, flash

Features

- Adoption of FBET, MBIT processes
- Low collector-to-emitter saturation voltage
- Ultrasmall package facilitates miniaturization in end products (mounting height : 0.85mm)
- High allowable power dissipation
- Large current capacity
- High-speed switching

Specifications () : MCH3105

Absolute Maximum Ratings at $T_a=25^\circ\text{C}$


Parameter	Symbol	Conditions	Ratings	Unit
Collector-to-Base Voltage	V_{CBO}		(-50)80	V
Collector-to-Emitter Voltage	V_{CES}		(-50)80	V
	V_{CEO}		(-50)50	V
Emitter-to-Base Voltage	V_{EBO}		(-6)6	V
Collector Current	I_C		(-3)3	A
Collector Current (Pulse)	I_{CP}		(-6)6	A
Base Current	I_B		(-600)600	mA
Collector Dissipation	P_C	When mounted on ceramic substrate (600mm ² ×0.8mm)	0.8	W
Junction Temperature	T_j		150	°C
Storage Temperature	T_{stg}		-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ)


7019A-004




Product & Package Information

- Package : MCPH3
- JEITA, JEDEC : SC-70, SOT-323
- Minimum Packing Quantity : 3,000 pcs./reel


Packing Type : TL



Marking




MCH3105



MCH3205

Electrical Connection




MCH3105 / MCH3205

Electrical Characteristics at Ta=25°C

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Collector Cutoff Current	ICBO	VCE=(-)40V, IE=0A			(-)1	μA
Emitter Cutoff Current	IEBO	VEB=(-)4V, IC=0A			(-)1	μA
DC Current Gain	hFE	VCE=(-)2V, IC=(-)100mA	200		560	
Gain-Bandwidth Product	fT	VCE=(-)10V, IC=(-)500mA		(360)380		MHz
Output Capacitance	Cob	VCE=(-)10V, f=1MHz		(24)13		pF
Collector-to-Emitter Saturation Voltage	VCE(sat)1	IC=(-)1A, IB=(-)50mA		(-100)80	(-200)120	mV
	VCE(sat)2	IC=(-)2A, IB=(-)100mA		(-185)140	(-500)210	mV
Base-to-Emitter Saturation Voltage	VBE(sat)	IC=(-)2A, IB=(-)100mA		(-)0.88	(-)1.2	V
Collector-to-Base Breakdown Voltage	V(BR)CBO	IC=(-)10μA, IE=0A	(-50)80			V
Collector-to-Emitter Breakdown Voltage	V(BR)CES	IC=(-)100μA, RBE=0Ω	(-50)80			V
	V(BR)CEO	IC=(-)1mA, RBE=∞	(-)50			V
Emitter-to-Base Breakdown Voltage	V(BR)EBO	IE=(-)10μA, IC=0A	(-)6			V
Turn-On Time	ton	See specified Test Circuit.		(30)35		ns
Storage Time	tstg			(230)300		ns
Fall Time	tf			(15)22		ns



Switching Time Test Circuit











IC=10IB1= -10IB2=1A
(For PNP, the polarity is reversed.)









Ordering Information

Device	Package	Shipping	memo
MCH3105-TL-E	MCPH3	3,000pcs./reel	Pb Free
MCH3205-TL-E	MCPH3	3,000pcs./reel	



MCH3105 / MCH3205






Taping Specification

MCH3105-TL-E, MCH3205-TL-E

1. Packing Format

Package Name	Carrier Tape Type	Maximum Number of devices contained (pcs)			Packing format	
		Reel	Inner box	Outer box	Inner BOX (C-1)	Outer BOX (A-7)
MCPH3	MCPH3	3,000	15,000	90,000	5 reels contained Dimensions:mm (external) 183×72×185	6 inner boxes contained Dimensions:mm (external) 440×195×210

Packing method




Reel label

Type No.
LOT No.
Quantity
Origin

Reel label, Inner box label
(unit:mm)

Outer box label

It is a label at the time of factory shipments.
The form of a label may change in physical
distribution process.




NOTE (1)

The LEAD FREE * description shows that the surface
treatment of the terminal is lead free.


Label	JEITA Phase
LEAD FREE 3	JEITA Phase 3A
LEAD FREE 4	JEITA Phase 3

2. Taping configuration

2-1. Carrier tape size (unit:mm)




2-2. Device placement direction




Those with pin 1 index on the feed hole side.....TL

Outline Drawing

MCH3105-TL-E, MCH3205-TL-E



Land Pattern Example



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor:](#)

[MCH3205-TL-E](#) [MCH3105-TL-E](#)