

# KAI-0340 Imager Board User's Manual

## Description

The KAI-0340 Imager Evaluation Board, referred to in this document as the Imager Board, is designed to be used as part of a two-board set, used in conjunction with a Timing Generator Board. ON Semiconductor offers an Imager Board / Timing Generator Board package that has been designed and configured to operate with the KAI-0340 Image Sensor.

The Timing Generator Board generates the timing signals necessary to operate the CCD, and provides the power required by the Imager Board. The timing signals, in LVDS format, and the power, are provided to the Imager Board via the interface connector (J1). In addition, the Timing Generator Board performs the processing and digitization of the analog video output of the Imager Board.

The KAI-0340 Imager Board has been designed to operate the KAI-0340 with the specified performance at 40 MHz pixel clocking rate and nominal operating conditions. (See the KAI-0340 Performance Specifications for details).



**ON Semiconductor®**

<http://onsemi.com>

## EVAL BOARD USER'S MANUAL

For testing and characterization purposes, the KAI-0340 Imager board provides the ability to adjust many of the CCD bias voltages and CCD clock level voltages by adjusting potentiometers on the board. The Imager Board provides the means to modify other device operating parameters (e.g., CCD reset clock pulse width) by populating components differently on the board.

Some circuitry on the Imager Board (e.g., remote DAC control of bias and clock level voltages) is intended for ON Semiconductor test purposes only, and may not be populated.

## IMAGER BOARD INPUT REQUIREMENTS

**Table 1. POWER REQUIREMENTS**

Power Supplies	Minimum	Typical	Maximum	Units
+5 V_MTR Supply	4.9	5	5.1	V
		800		mA
-5 V_MTR Supply	-5.1	-5	-4.9	V
		200		mA
VPLUS Supply	18	20	21	V
		250		mA
VMINUS Supply	-21	-20	-18	V
		250		mA

**Table 2. SIGNAL LEVEL REQUIREMENTS**

Input Signals (LVDS)	V <sub>min</sub>	V <sub>threshold</sub>	V <sub>max</sub>	Units	Signal	Comments
IMAGER_IN0	0	±0.1	2.4	V	AMP ENABLE	Output Amplifier Enable
IMAGER_IN1	0	±0.1	2.4	V	H1A	H1A clock
IMAGER_IN2	0	±0.1	2.4	V	H1B	H1B clock
IMAGER_IN3	0	±0.1	2.4	V	H2A	H2A clock
IMAGER_IN4	0	±0.1	2.4	V	H2B	H2B clock
IMAGER_IN5	0	±0.1	2.4	V	RESET	Reset clock
IMAGER_IN6	0	±0.1	2.4	V	V1	V1 clock

Table 2. SIGNAL LEVEL REQUIREMENTS

Input Signals (LVDS)	V <sub>min</sub>	V <sub>threshold</sub>	V <sub>max</sub>	Units	Signal	Comments
IMAGER_IN7	0	±0.1	2.4	V	V2	V2 clock
IMAGER_IN8	0	±0.1	2.4	V	VCLK_ENABLE	Outer V2 clock control
IMAGER_IN9	0	±0.1	2.4	V	V3RD	V2 Clock 3 <sup>rd</sup> level
IMAGER_IN10	0	±0.1	2.4	V	FDG	Outer Fast Dump clock
IMAGER_IN11	0	±0.1	2.4	V	VES	Electronic Shutter clock
IMAGER_IN12	0	±0.1	2.4	V	VIDEO_MUX	VOOUT_MUX (J2) control
IMAGER_IN13	0	±0.1	2.4	V	FDG_CENTER	Center Fast Dump clock
IMAGER_IN14	0	±0.1	2.4	V		(not used)
IMAGER_IN15	0	±0.1	2.4	V		(not used)

## KAI-0340 IMAGER BOARD ARCHITECTURE OVERVIEW

The following sections describe the functional blocks of the KAI-0340 Imager Board (Refer to Figure 1).

### Power Filtering and Regulation

Power is supplied to the Imager Board via the J1 interface connector. The power supplies are de-coupled and filtered with ferrite beads and capacitors to suppress noise. Voltage regulators are used to create the +15 V and –15 V supplies from the VPLUS and VMINUS supplies.

### LVDS Receivers / TTL Buffers

LVDS timing signals are input to the Imager Board via the J1 interface connector. These signals are shifted to TTL levels before being sent to the CCD clock drivers.

### Reset Clock One-Shot

The pulse width of the RESET\_CCD clock is set by a programmable One-Shot. The One-Shot can be configured to provide a RESET\_CCD clock signal with a pulse width from 5 ns to 15 ns. If pulse width control functionality is provided by the Timing Board, the One-Shot may be removed and bypassed by installing R170.

### CCD Pixel-Rate Clock Drivers (H1, H2 & Reset Clocks)

The pixel rate CCD clock drivers utilize two fast switching transistors that are designed to translate TTL-level input clock signals to the voltage levels required by the CCD. The high level and low level of the CCD clocks are set by potentiometers, and are buffered by operational amplifiers configured as voltage followers.

### CCD VCLK Drivers

The vertical clock (VCLK) drivers consist of MOSFET driver IC's. These drivers are designed to translate the TTL-level clock signals to the voltage levels required by the CCD. The high, middle, and low voltage levels of the vertical clocks are set by potentiometers buffered by operational amplifiers. The VHIG and VLOW op-amps have a gain of 1.25, to allow the magnitude of the voltages to be adjusted to 12.5 V when using DAC control.

The current sources for these voltage levels are high current (up to 600 mA) transistors. The V2\_CCD high level clock voltage is switched from V\_MID to V\_HIGH once per frame to transfer the charge from the photodiodes to the vertical CCDs.

The V1 clock driver is a 2-level driver circuit, switching between VMID and VLOW voltage levels. There are two 3-level clock driver circuits, V2 and V2C, which are identical except for the input logic, which is controlled by the VCLK\_ENABLE signal. This signal is used to control the outer V2 clocks to implement certain imaging modes where only the center rows are read out.

### CCD FDG Driver

The Fast Dump clock drivers consist of a transistor that will switch the voltage on the FD and FDC pins of the CCD from FDG\_LOW to FDG\_HIGH during Fast Dump Gate operations. When not in operation, or when the Fast Dump Gate feature is not being utilized, the FDG pin of the CCD is held at FDG\_LOW. The FDG\_HIGH and FDG\_LOW voltage levels of the FDG driver are set by potentiometers, buffered by operational amplifiers configured as voltage followers.

The FD and FDC CCD inputs are clocked separately, to implement certain imaging modes where only the center columns are read out.

### VSUB/VES Circuit

The quiescent CCD substrate voltage (VSUB) is set by a potentiometer and resistor divider network. The VSUB voltage is buffered by an operational amplifier configured with a gain of 1.40, to allow the voltage to be adjusted to nearly 14.0 V.

For electronic shutter operation, the VES signal drives a transistor amplifier circuit which AC-couples the voltage difference between the VPLUS and VMINUS supplies onto the Substrate voltage. This creates the necessary potential to clear all charge from the photodiodes, thereby acting as an electronic shutter to control exposure.

### VDD Bias Voltages

The VDDL and VDDR video output amplifier supplies in the CCD are coupled directly to the +15 V regulated supply on the Imager Board. The Imager Board contains optional circuitry which allows this voltage to be adjusted through the Alternate VDD bias circuit. This circuitry is for ON Semiconductor use only, and is not enabled.

The Imager Board contains optional circuitry to control a multiplexer which switches the VDD voltage from +15 V to ALT\_VDD. This circuitry is for ON Semiconductor use only, and is not enabled.

### ESD Bias Voltage

The RESET and HCLK gates on the KAI-0340 CCD are protected from ESD damage by internal circuitry. The ESD bias voltage is set by a potentiometer, buffered by an operational amplifier configured as a voltage follower. The ESD bias voltage must be more negative than any of the protected gates during operation and powerup. In order to ensure these conditions are met, diodes are connected external to the CCD between the protected gates and VESD, and between VSUB and VESD.

It is also recommended that during powerup of the Timing Board and Imager Board, the VMINUS supply is applied before, or simultaneously with, the other power supplies. For more information, refer to the KAI-0340 CCD Image Sensor Device Performance Specification.

### CCD Image Sensor

This evaluation board supports the KAI-0340 Interline Image Sensor.

### Emitter-Followers

The VOUT\_LEFT\_CCD and VOUT\_RIGHT\_CCD video output signals are buffered using bipolar junction transistors in the emitter-follower configuration. These circuits also provide the necessary 5 mA current sink for the CCD output circuits. The voltage gain of this stage is approximately 0.96.

### Line Drivers

The buffered VOUT\_LEFT\_CCD and VOUT\_RIGHT\_CCD signals are AC-coupled and driven from the Imager Board by operational amplifiers in a non-inverting configuration. The operational amplifiers are configured to have a gain of 1.25, which yields an overall gain of 0.6 when driving the properly terminated 75  $\Omega$  video coaxial cabling from the SMB connector. This is done to prevent overloading the AFE on the Timing Board.

The video output of either channel may be multiplexed to the VOUT\_MUX output. The multiplexer is controlled by the VIDEO\_MUX signal. This circuitry is for Truesense Imaging use only, and is not enabled.

## KAI-0340 OPERATIONAL SETTINGS

The Imager board is configured to operate the KAI-0340 Image Sensor under the following operating conditions:

### Bias Voltages

The following voltages are fixed, or adjusted with a potentiometer as noted. The nominal values listed in Table 3

were correct at the time of this document's publication, but may be subject to change; refer to the KAI-0340 device specification.

**Table 3. BIAS VOLTAGES**

Description	Symbol	Min	Nom	Max	Units	Potentiometer	Notes
Left Output Amplifier Supply	VDDL		15.0		V		
Right Output Amplifier Supply	VDDR		15.0		V		
ESD Protection	ESD	-6.0	-9.0	-11.0	V	R11	1
Substrate	VSUB	8.5	TBD	14.0	V	R17	1, 2
Ground	GND		0				

1. The Min and Max voltages in the table indicate the imager board potentiometer adjustable voltage range. These values may exceed the specified CCD operating conditions. See the KAI-0340 device specification for details.
2. The recommended VSUB voltage is specified for each CCD image sensor, and is labeled on the container as VAB.

### Clock Voltages

The following clock voltage levels are fixed, or adjusted with a potentiometer as noted. The nominal values listed in

Table 4 were correct at the time of this document's publication, but may be subject to change; refer to the KAI-0340 device specification.

**Table 4. CLOCK VOLTAGES**

Description	Symbol	Level	Min	Nom	Max	Units	Potentiometer	Notes
Horizontal CCD Clock	Hxx_CCD	Low	-8.0	-5.0	-1.0	V	R126	3, 8
		High	-5.0	0.0	5.0	V	R92	4, 8
Vertical CCD Clock	Vx_CCD	Low	-12.0	-9.0	-6.0	V	R52	5, 8
		Mid	-3.0	0.0	3.0	V	R81	6, 8
	V2x_CCD	High	6.0	10.0	12.0	V	R71	8
Reset Clock	RESET_CCD	Low	-8.0	-3.0	-1.0	V	R153	8
		High	0.5	2.0	5.0	V	R135	8
Fast Dump Clock	Fdx_CCD	Low	-11.5	-9.0	-5.0	V	R62	7, 8
VDD	+15 V	High	2.5	5.0	7.5	V	R45	8
		High		15.0		V	Fixed	

3. The H1A\_CCD, H1B\_CCD, H2A\_CCD, and H2B\_CCD low levels are controlled by the same potentiometer (R126).
4. The H1A\_CCD, H1B\_CCD, H2A\_CCD, and H2B\_CCD high levels are controlled by the same potentiometer (R92).
5. V1\_CCD and V2\_CCD low levels are controlled by the same potentiometer (R52).
6. V1\_CCD and V2\_CCD mid levels are controlled by the same potentiometer (R81).
7. FD is used to flush the outer columns when only the center columns are read out.
8. The Min and Max voltages in the table indicate the imager board potentiometer adjustable voltage range. These values may exceed the specified CCD operating conditions. See the KAI-0340 device specification for details.

### Reset Clock Pulse Width

The pulse width of RESET\_CCD is set by configuring P[2..0], the inputs to the programmable one-shot U14. P[2..0] can be tied high or low to achieve the desired pulse width by populating the resistors R161-164 accordingly.

This feature is optional, as the pulsewidth may also be controlled from the Timing Board. In that case, U14 should be removed, and R170 should be installed to bypass this circuitry.

**Table 5. RESET CLOCK PULSE WIDTH**

Pulse Width	P0	P1	P2	R161	R162	R163	R164	Notes
15 ns	0	0	0	IN	IN	OUT	OUT	
5 ns	1	0	0	IN	OUT	IN	OUT	Default Setting
7.5 ns	0	1	0	OUT	IN	OUT	IN	
10 ns	1	1	0	OUT	OUT	IN	IN	

# BLOCK DIAGRAM AND PERFORMANCE DATA




Figure 1. KAI-0340 Imager Board Block Diagram

## Photon Transfer




Figure 2. Measured Performance – Dynamic Range and Noise Floor

## CONNECTOR ASSIGNMENTS AND PINOUTS

## SMB Connectors J3 and J4

The emitter–follower buffered VOUT\_LEFT and VOUT\_RIGHT signals are driven from the Imager Board via the SMB connectors J4 and J3, respectively. VOUT\_LEFT is the primary output from KAI–0340; VOUT\_RIGHT is only used when the CCD is clocked in

dual–channel mode. Coaxial cable with a characteristic impedance of 75  $\Omega$  should be used to connect the imager board to the Timing Generator Board to match the series and terminating resistors used on these boards.

Table 6. J1 INTERFACE CONNECTOR PIN ASSIGNMENTS

Pin	Signal	Pin	Signal
1	N.C.	2	N.C.
3	AGND	4	AGND
5	IMAGER_IN11+	6	IMAGER_IN11–
7	AGND	8	AGND
9	IMAGER_IN10+	10	IMAGER_IN10–
11	AGND	12	AGND
13	IMAGER_IN9+	14	IMAGER_IN9–
15	AGND	16	AGND
17	IMAGER_IN8+	18	IMAGER_IN8–
19	AGND	20	AGND
21	IMAGER_IN7+	22	IMAGER_IN7–
23	AGND	24	AGND
25	IMAGER_IN6+	26	IMAGER_IN6–
27	AGND	28	AGND
29	IMAGER_IN5+	30	IMAGER_IN5–
31	AGND	32	AGND
33	IMAGER_IN4+	34	IMAGER_IN4–
35	AGND	36	AGND
37	IMAGER_IN3+	38	IMAGER_IN3–
39	AGND	40	AGND
41	IMAGER_IN2+	42	IMAGER_IN2–
43	AGND	44	AGND
45	IMAGER_IN1+	46	IMAGER_IN1–
47	N.C.	48	N.C.
49	AGND	50	AGND
51	N.C.	52	N.C.
53	VMINUS_MTR	54	VMINUS_MTR
55	N.C.	56	N.C.
57	AGND	58	AGND
59	IMAGER_IN0+	60	IMAGER_IN0–
61	–5 V_MTR	62	–5 V_MTR
63	IMAGER_IN15+	64	IMAGER_IN15–
65	AGND	66	AGND
67	IMAGER_IN14+	68	IMAGER_IN14–
69	+5 V_MTR	70	+5 V_MTR
71	IMAGER_IN13+	72	IMAGER_IN13–
73	AGND	74	AGND
75	IMAGER_IN12+	76	IMAGER_IN12–
77	VPLUS_MTR	78	VPLUS_MTR
79	N.C.	80	N.C.

### Warnings and Advisories

ON Semiconductor is not responsible for customer damage to the Imager Board or Imager Board electronics. The customer assumes responsibility and care must be taken when probing, modifying, or integrating the ON Semiconductor Evaluation Board Kits.

When programming the Timing Board, the Imager Board must be disconnected from the Timing Board before power is applied. If the Imager Board is connected to the Timing Board during the reprogramming of the Altera PLD, damage to the Imager Board will occur.

Purchasers of an Evaluation Board Kit may, at their discretion, make changes to the Timing Generator Board firmware. ON Semiconductor can only support firmware developed by, and supplied by, ON Semiconductor. Changes to the firmware are at the risk of the customer.

### Ordering Information

Please address all inquiries and purchase orders to:

Truesense Imaging, Inc.  
1964 Lake Avenue  
Rochester, New York 14615  
Phone: (585) 784-5500  
E-mail: [info@truesenseimaging.com](mailto:info@truesenseimaging.com)

ON Semiconductor reserves the right to change any information contained herein without notice. All information furnished by ON Semiconductor is believed to be accurate.

**onsemi**, **onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and will only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

**THE BOARD IS PROVIDED BY ONSEMI TO YOU "AS IS" AND WITHOUT ANY REPRESENTATIONS OR WARRANTIES WHATSOEVER. WITHOUT LIMITING THE FOREGOING, ONSEMI (AND ITS LICENSORS/SUPPLIERS) HEREBY DISCLAIMS ANY AND ALL REPRESENTATIONS AND WARRANTIES IN RELATION TO THE BOARD, ANY MODIFICATIONS, OR THIS AGREEMENT, WHETHER EXPRESS, IMPLIED, STATUTORY OR OTHERWISE, INCLUDING WITHOUT LIMITATION ANY AND ALL REPRESENTATIONS AND WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, TITLE, NON-INFRINGEMENT, AND THOSE ARISING FROM A COURSE OF DEALING, TRADE USAGE, TRADE CUSTOM OR TRADE PRACTICE.**

**onsemi** reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by **onsemi** shall not constitute any representation or warranty by **onsemi**, and no additional obligations or liabilities shall arise from **onsemi** having provided such information or services.

**onsemi** products including the boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. You agree to indemnify, defend and hold harmless **onsemi**, its directors, officers, employees, representatives, agents, subsidiaries, affiliates, distributors, and assigns, against any and all liabilities, losses, costs, damages, judgments, and expenses, arising out of any claim, demand, investigation, lawsuit, regulatory action or cause of action arising out of or associated with any unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of any products and/or the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

**FCC WARNING** – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by **onsemi** to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

**onsemi** does not convey any license under its patent rights nor the rights of others.

**LIMITATIONS OF LIABILITY:** **onsemi** shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if **onsemi** is advised of the possibility of such damages. In no event shall **onsemi**'s aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

The board is provided to you subject to the license and other terms per **onsemi**'s standard terms and conditions of sale. For more information and documentation, please visit [www.onsemi.com](http://www.onsemi.com).

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[KAI-0340-10-40-A-EVK](#)