




Features

- 10 mm² PIN detector
- Low dark current
- High shunt resistance
- High sensitivity
- Fully depleteble

Description

Circular active area PIN photodiode with 10 mm² active area. Metal can type isolated and hermetic TO8 package with clear glass window.

Application

- Precision photometry
- Medical equipment
- Pulsed light sensor

RoHS


2002/95/EC




Absolute maximum ratings

Symbol	Parameter	Min	Max	Unit
T _{STG}	Storage temp	-55	125	°C
T _{OP}	Operating temp	-40	100	°C
V _{max}	Max reverse voltage		300	V
I _{PEAK}	Peak DC current		10	mA

Schematic



Spectral response (23 °C)



Electro-optical characteristics @ 23 °C

Symbol	Characteristic	Test Condition	Min	Typ	Max	Unit
	Active area		diameter 3578			μm
	Active area		10			mm ²
I _D	Dark current	V _R = 10 V		0.1	0.4	nA
		V _R = 150 V		0.6	2.0	nA
T _K (I _D)	Temperature coefficient	V _R = 10 V; change of dark current		13		%/K
C	Capacitance	V _R = 10 V; f = 10 kHz		12		pF
		V _R = 150 V; f = 10 kHz		4.5		pF
	Responsivity	λ = 800 nm		0.61		A/W
		λ = 900 nm		0.69		A/W
t _R	Rise time	V _R = 150 V; λ = 905 nm; R _L = 50 Ω		6		ns
	Shunt Resistance	V _R = 10 mV	500	1000		MΩ
	N.E.P.	V _R = 150 V; λ = 905 nm		2.1 E-14		W/√Hz
V _{BR}	Breakdown voltage	I _R = 2 μA	300	500		V

European, International Sales:







First Sensor AG
Peter-Behrens-Strasse 15
12459 Berlin
Germany
T +49 30 6399 2399
F +49 30 639923-752
sales.opto@first-sensor.com

USA:



First Sensor Inc.
5700 Corsa Avenue #105
Westlake Village
CA 91362 USA
T +1 818 706 3400
F +1 818 889 7053
sales.us@first-sensor.com

Quantum efficiency (23 °C)

Capacitance as fct of reverse bias (23 °C)

Dark current as fct of bias (23 °C)

Temperature coefficient of responsivity (10 V, 23 °C)


Package dimension:

Small quantities: Foam pad, boxed (12 cm x 16.5 cm)

Handling:

Please refer to document "Instructions for handling and processing"

Disclaimer: Due to our strive for continuous improvement, specifications are subject to change within our PCN policy according to JESD46C.

European, International Sales:



First Sensor AG
Peter-Behrens-Strasse 15
12459 Berlin
Germany
T +49 30 6399 2399
F +49 30 639923-752
sales.opto@first-sensor.com

USA:



First Sensor Inc.
5700 Corsa Avenue #105
Westlake Village
CA 91362 USA
T +1 818 706 3400
F +1 818 889 7053
sales.us@first-sensor.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

First Sensor:

[PC10-7-T08I](#)