

BK200AAB Nickel Metal Hydride

Features & Benefits

- Efficient, lower cost charge requirements with excellent cycle life.
- Options for broader operating temperatures.
- Versatile Applications including: Security, Medical, Automotive and Industrial Infrastructure.
- Higher levels of energy density, demanded by today's electronics.
- No transportation issues.
- Cells designed specifically to meet different, rigorous environments.

Specifications

Nominal

Capacity: 2000 mAh Typical

Nominal Voltage: 1.2V

Weight: Approximately 29g


Operating Temperature: 0°C - +45°C

Dimensions





Unit: mm

Typical Charge Characteristics



Typical Discharge Characteristics



For more information on how Panasonic can assist you with your battery power solution needs call **877-726-2228**, visit www.na.industrial.panasonic.com/products/batteries or e-mail oembatteries@us.panasonic.com.

The data in this document is for descriptive purposes only and is not intended to make or imply any guarantee or warranty.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic:](#)

[BK-200AAB9B](#)