

Panasonic Industry

Signal Relays (2A or less)

GN RELAYS

High sensitivity, 100 mW operating power, 2 Form C, 1A, compact size and slim relays





*1: The "W" and "Y" at the end of the part number only appears on the inner and outer packing.

- It does not appear on the relay itself. *2: Please inquire if you require a relay, between 1.5 and 24 V DC, with a voltage not listed.
- *3: Each reel is packed with humidity indicators and silica gel in the moisuture proof pack.

TYPES

PC board terminal

Tube packing

Contact	Rated coil	Part No.			Standard packing	
arrangement	voltage	Single side stable	1 coil latching	High sensitive single side stable	Carton (1 Tube packing)	Outer carton
	1.5 V DC	AGN2001H	AGN2101H	AGN2601H	-	
	3 V DC	AGN20003	AGN21003	AGN26003		
	4.5 V DC	AGN2004H	AGN2104H	AGN2604H		
2 Form C	6 V DC	AGN20006	AGN21006	AGN26006	50 pcs.	1,000 pcs.
	9 V DC	AGN20009	AGN21009	AGN26009		
	12 V DC	AGN20012	AGN21012	AGN26012		
	24 V DC	AGN20024	AGN21024	AGN26024		

Surface-mount terminal

Tube packing

Contact	Rated coil voltage	Part No.			Standard packing	
arrangement		Single side stable	1 coil latching	High sensitive single side stable	Carton (1 Tube packing)	Outer carton
	1.5 V DC	AGN200*1H	AGN210*1H	AGN260*1H	-	
	3 V DC	AGN200*03	AGN210*03	AGN260*03		1,000 pcs.
	4.5 V DC	AGN200*4H	AGN210*4H	AGN260*4H		
2 Form C	6 V DC	AGN200*06	AGN210*06	AGN260*06	50 pcs.	
	9 V DC	AGN200*09	AGN210*09	AGN260*09		
	12 V DC	AGN200*12	AGN210*12	AGN260*12		
	24 V DC	AGN200*24	AGN210*24	AGN260*24		

Note : "*" : For each surface-mount terminal identitication, input the following letter. A type : A, S type : S.

Tape and reel packing: Z

Contact	Rated coil - voltage	Part No.			Standard	Standard packing	
arrangement		Single side stable	1 coil latching	High sensitive single side stable	Carton (1Reel)	Outer carton	
	1.5 V DC	AGN200*1HZ	AGN210*1HZ	AGN260*1HZ			
	3 V DC	AGN200*03Z	AGN210*03Z	AGN260*03Z	_		
	4.5 V DC	AGN200*4HZ	AGN210*4HZ	AGN260*4HZ			
2 Form C	6 V DC	AGN200*06Z	AGN210*06Z	AGN260*06Z	500 pcs.	1,000 pcs.	
	9 V DC	AGN200*09Z	AGN210*09Z	AGN260*09Z			
	12 V DC	AGN200*12Z	AGN210*12Z	AGN260*12Z	1		
	24V DC	AGN200*24Z	AGN210*24Z	AGN260*24Z]		

Notes : 1. "*" : For each surface-mount terminal identitication, input the following letter. A type : A, S type : S. 2. For taping packaging X, W, and Y, change "Z" at the end of the part number to "X", "W", and "Y".

RATING

Coil data

- Operating characteristics such as "Operate voltage" and "Release voltage" are influenced by mounting conditions or ambient temperature, etc.
- Therefore, please use the relay within ±5% of rated coil voltage.
- "Initial" means the condition of products at the time of delivery.

Single side stable

Rated coil voltage	Operate voltage* (at 20°C)	Release voltage* (at 20°C)	Rated operating current (±10%, at 20°C)	Coil resistance (±10%, at 20°C)	Rated operating power	Max. allowable voltage (at 20°C)
1.5 V DC			93.8 mA	16 Ω		
3 V DC			46.7 mA	64.2 Ω		
4.5 V DC	Max. 75% V of rated coil voltage		31 mA	145 Ω	140 mW	150% V of
6 V DC		Min. 10% V of rated coil voltage	23.3 mA	257 Ω		rated coil voltage
9 V DC	(Initial)	(Initial)	15.5 mA	579 Ω		
12 V DC	-		11.7 mA	1,028 Ω		
24 V DC			9.6 mA	2,504 Ω	230 mW	120% V of rated coil voltage

*square, pulse drive (JIS C 5442)

1 coil latching

Rated coil voltage	Set voltage* (at 20°C)	Reset voltage* (at 20°C)	Rated operating current (±10%, at 20°C)	Coil resistance (±10%, at 20°C)	Rated operating power	Max. allowable voltage (at 20°C)
1.5 V DC			66.7 mA	22.5 Ω		
3 V DC			33.3 mA	90 Ω		
4.5 V DC	Max. 75% V of	Max. 75% V of	22.2 mA	202.5 Ω	100 mW	
6 V DC	rated coil voltage	rated coil voltage	16.7 mA	360 Ω	100 11100	150% V of rated coil voltage
9 V DC	(Initial)	(Initial) (Initial) -	11.1 mA	810 Ω	_	
12 V DC			8.3 mA	1,440 Ω		
24 V DC			5 mA	4,800 Ω	120 mW	

*square, pulse drive (JIS C 5442)

High sensitive single side stable

Rated coil voltage	Operate voltage* (at 20°C)	Release voltage* (at 20°C)	Rated operating current (±10%, at 20°C)	Coil resistance (±10%, at 20°C)	Rated operating power	Max. allowable voltage (at 20°C)
1.5 V DC			66.7 mA	22.5 Ω		
3 V DC			33.3 mA	90 Ω		
4.5 V DC	Max. 80% V of rated coil voltage (Initial)		22.2 mA	202.5 Ω	100 mW	150% V of
6 V DC		Min. 10% V of rated coil voltage	16.7 mA	360 Ω		rated coil voltage
9 V DC		(Initial)	11.1 mA	810 Ω		
12 V DC			8.3 mA	1,440 Ω		
24 V DC			5 mA	4,800 Ω	120 mW	120% V of rated coil voltage

*square, pulse drive (JIS C 5442)

Specifications

Item		Specifications		
	Contact arrangement	2 Form C		
	Contact resistance (initial)	Max. 100 m Ω (by voltage drop 6 V DC 1 A)		
	Contact material	AgPd + Au-clad (Stationary contact), AgPd (Movable contact)		
Contact data	Contact rating (resistive)	1 A 30 V DC, 0.3 A 125 V AC		
Contact data	Max. switching power (resistive)	30 W (DC), 37.5 VA (AC)		
	Max. switching voltage	110 V DC, 125 V AC		
	Max. switching current	1 A (DC), 1 A (AC)		
	Min. switching load (reference value)*1	10 µA 10 mV DC		
Insulation resista	ance (initial)	Min. 1,000 M Ω (at 500 V DC, Measured portion is the same as the case of dielectric strength.)		
	Between open contacts	750 Vrms for 1 min (detection current: 10 mA)		
Dielectric strength (initial)	Between contact and coil	1,500 Vrms for 1 min (detection current: 10 mA)		
	Between contact sets	1,000 Vrms for 1 min (detection current: 10 mA)		
Surge	Between open contacts	1,500 V 10 × 160 μs		
withstand voltage (initial)	Between contact and coil	2,500 V 2 × 10 μs		
Time characteristics	Operate (Set) time	Max. 4 ms at rated coil voltage (at 20°C, without bounce) [Max. 4 ms (at 20°C, without bounce)]		
(initial)	Release (Reset) time	Max. 4 ms at rated coil voltage (at 20°C, without bounce, without diode) [Max. 4 ms (at 20°C, without bounce)]		
Shock	Functional	750 m/s² (half-sine shock pulse: 6 ms, detection time: 10 μs)		
resistance	Destructive	1,000 m/s ² (half-sine shock pulse: 6 ms)		
Vibration	Functional	10 to 55 Hz (at double amplitude of: 3.3 mm, detection time: 10 µs)		
resistance	Destructive	10 to 55 Hz (at double amplitude of: 5 mm)		
Expected life	Mechanical life	Min. 50 x 10 ⁶ ope. (Switching frequency: at 180 times/min)		
Conditions	Conditions for usage, transport and storage* ²	Ambient temperature: -40 to +85°C (Single side stable, 1 coil latching), -40 to +70°C (High sensitive single side stable) (Allowable temperature is from -40 to +70°C at our standard packing condition.) Humidity: 5 to 85% RH (Avoid icing and condensation)		
Unit weight		Approx. 1 g		

Note: For AC load, please inquire our sales representative for details.
*1. This value is a rough indication of the lower limit at which switching is possible at micro load level. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.
*2. For ambient temperature, please refer to the "GUIDELINES FOR RELAY USAGE".

Electrical life

Conditions: resistance load, switching frequency at 20 times / minute.

Туре	Switching capacity	Number of operations
2 Form C	1 A 30 V DC	Min. 100 × 10 ³ ope.
	0.3 A 125 V AC	Min. 100 × 10 ³ ope.

REFERENCE DATA

1. Max. switching capacity



100


50


40 30

20

10

No. of operations, ×10⁴






125V AC

resistive load

30V DC resistive load

5. Mechanical life




100

0


3. Coil temperature rise value (Average)

 Ambient temperature characteristic (Average)

Tested sample : AGQ200A4H, 6 pcs.



Tested sample : AGN2004H, 15 pcs. Operating speed : 180 cpm




6. Electrical life test (1 A 30 V DC Resistive load) Tested sample : AGN2004H, 6 pcs. Cl Operating speed : 20 cpm

110 120 130 140

Coil applied voltage, %V


150

Change of operate and release voltage




- 4 —

Change of contact resistance



8. Functional shock




7-2. Operate and release time (with diode)



7-1. Operate and release time

Surface-mount terminal



PACKING STYLE

Tube packing


1. The relay is packing in a tube with the relay orientation mark on the left side, as shown in the figure below.


Be sure to maintain relays in the correct orientation when mounting on PC boards.

2. Conditions for operation, transport and storage : –40 to 70° C.


Taping packaging

1. Tape dimensions






Orientation (indicates PIN No.1) stripe



2. Dimensions of plastic reel



3. Conditions for operation, transport and storage : -40 to 70°C.

Unit: mm

EXAMPLE OF RECOMMENDED SOLDERING CONDITIONS

For cautions for use, please read "Relay Soldering and Cleaning Guidelines" and "SMT Soldering Guidelines".

PC board terminal

In case of hand soldering, the following conditions should be observed.

The effect on the relay depends on the PC board used. Please verify the actual PC board to be used.

θA	utomatic	soldering	(Flow)
----	----------	-----------	--------

Recommended conditions	Temperature	Time	Measurement location
Preheating	Max. 120°C	Within 120 seconds	Solder surface terminal
Soldering	260°C ± 5°C	Within 6 seconds	Solder temperature


Hand soldering

	3		
Recommended conditions	Temperature	Time	Measurement location
Soldering	Max. 350°C	Within 3 seconds	Tip temperature


Surface-mount terminal

In case of automatic soldering (reflow), the following conditions should be observed.

IRS (infrared reflow soldering method) heating conditions



Measuring position of temperature profile



Note : The soldering temperature profile indicates the pad temperature. In some cases, the ambient temperature may be greatly increased. Check for the specific mounting condition.

Other things to observe

- Exceeding the stipulated conditions when soldering may affect coaxial switch performance. Be sure to consult us beforehand.
- Since thermal stress on a relay will depend on the PC board and process conditions, please be sure to test using the actual PC board.

Mounting cautions

Cautions to observe when mounting temperature increases in the relay are greatly dependent on the way different parts are located a PC board and the heating method of the reflow device. Therefore, please conduct testing on the actual device beforehand after making sure the parts soldered on the relay terminals and the top of the relay case are within the temperature conditions.

- Creep-up, wettability and solder strength will differ depending on changes in the mounting conditions and type of solder.
 Please evaluate based on actual production conditions.
- Only apply coating after the relay has returned to room temperature.

Each standard may be updated at any time, so please check our Website for the latest information.

UL/C-UL (Approved)

SAFETY STANDARDS

File No.	Contact rating	Operations	Ambient temperature
	1 A 30 V DC General use	100 × 10 ³	40°C
E43149	0.3 A 110 V DC General use	30 × 10 ³	40°C
	0.3 A 125 V AC Resistive	100 × 10 ³	40°C

BSI (Approved)

BSI standard approved by File No. VC648944 (basic insulation).

CSA (Approved)


CSA standard approved by C-UL.

GUIDELINES FOR USAGE

For cautions for use, please read "GUIDELINES FOR SIGNAL RELAYS USAGE" and "GUIDELINES FOR RELAY USAGE".

Cautions for usage of GN relay

- Latching
- Use latching when conditions involve continuous carrying current.
- Regarding the set and reset pulse time, for the purpose of reliable operation under ambient temperature fl uctuations and diff erent operating conditions, we recommend setting the coil applied set and reset pulse time to 10 ms or more at the rated coil voltage.
- The relay is shipped in the reset position. But jolts during transport or impacts during installation can change the reset position. It is, therefore, advisable to build a circuit in which the relay can be initialized (set and reset) just after turning on the power.
- Precautions for usage of automatic insertion machine Set the chucking pressure of the pick-up mechanism by the automatic mounting machine with the pressure shown in table 1 to maintain the internal function of the relay.



Please chuck the portion. Avoid chucking the center of the relay. In addition, excessive chucking pressure to the pinpoint of the relay should be also avoided.

Table 1: Chucking pressure

A, B and D direction	Max. 9.8 N (1 kgf)
C and E direction	Max. 4.9 N (500 gf)

For cautions for use, please read "GUIDELINES FOR RELAY USAGE".

https://industrial.panasonic.com/ac/e/control/relay/cautions_use/index.jsp

PRECAUTIONS FOR COIL INPUT

Long term current carrying

A circuit that will be carrying a current continuously for long periods without relay switching operation. (circuits for emergency lamps, alarm devices and error inspection that, for example, revert only during malfunction and output warnings with form B contacts)

Continuous, long-term current to the coil will facilitate deterioration of coil insulation and characteristics due to heating of the coil itself. For circuits such as these, please use a magnetic-hold type latching relay. If you need to use a single stable relay, use a sealed type relay that is not easily affected by ambient conditions and make a failsafe circuit design that considers the possibility of contact failure or disconnection.

DC Coil operating power

Steady state DC current should be applied to the coil.

The wave form should be rectangular. If it includes ripple, the ripple factor should be less than 5%. However, please check with the actual circuit since the electrical characteristics may vary.

The rated coil voltage should be applied to the coil and the set/reset pulse time of latching type relay differs for each relays, please refer to the relay's individual specifications.

Coil connection

When connecting coils of polarized relays, please check coil polarity(+,-) at the internal connection diagram (Schematic).

If any wrong connection is made, it may cause unexpected malfunction, like abnormal heat, fire and so on, and circuit do not work.

Avoid impressing voltages to the set coil and reset coil at the same time.

Maximum allowable voltage and temperature rise

Proper usage requires that the rated coil voltage be impressed on the coil.

Note, however, that if a voltage greater than or equal to the maximum continuous voltage is impressed on the coil, the coil may burn or its layers short due to the temperature rise.


Furthermore, do not exceed the usable ambient temperature range listed in the catalog.

Temperature rise due to pulse voltage

When a pulse voltage with ON time of less than 2 minutes is used, the coil temperature rise bares no relationship to the ON time.

This varies with the ratio of ON time to OFF time, and compared with continuous current passage, it is rather small. The various relays are essentially the same in this respect.

Current passage time	%		
For continuous passage	Temperature rise value is 100%		
ON : OFF = 3 : 1	About 80%		
ON : OFF = 1 : 1	About 50%		
ON : OFF = 1 : 3	About 35%		



Operate voltage change due to coil temperature rise (hot start) In DC relays, after continuous passage of current in the coil, if the current is turned OFF, then immediately turned ON again, due to the temperature rise in the coil, the operate voltage will become somewhat higher. Also, it will be the same as using it in a higher temperature atmosphere.

The resistance/temperature relationship for copper wire is about 0.4% for 1°C, and with this ratio the coil resistance increases.

That is, in order to operate of the relay, it is necessary that the voltage be higher than the operate voltage and the operate voltage rises in accordance with the increase in the resistance value.

However, for some polarized relays, this rate of change is considerably smaller.

NOTES

Usage, Storage, and Transport Conditions


During usage, storage, or transportation, avoid locations subject to direct sunlight and maintain normal temperature, humidity, and pressure conditions.


The allowable specifications for environments suitable for usage, storage, and transportation are given below.

 Temperature: The allowable temperature range differs for each relay, so refer to the relay's individual specifications. In addition, when transporting or storing relays while they are tube packaged, there are cases when the temperature may differ from the allowable range. In this situation, be sure to consult the individual specifications.

2) Humidity: 5 to 85% RH

The humidity range varies with the temperature. Use within the range indicated in the graph. (The allowable temperature depends on the relays.)





3) Pressure: 86 to 106 kPa

Condensation

Condensation occurs when the ambient temperature drops suddenly from a high temperature and humidity, or the relay and microwave device is suddenly transferred from a low ambient temperature to a high temperature and humidity.

Condensation causes the failures like insulation deterioration, wire disconnection and rust etc.

Panasonic Corporation does not guarantee the failures caused by condensation.

The heat conduction by the equipment may accelerate the cooling of device itself, and the condensation may occur.

Please conduct product evaluations in the worst condition of the actual usage. (Special attention should be paid when high temperature heating parts are close to the device. Also please consider the condensation may occur inside of the device.)

Icing

Condensation or other moisture may freeze on relays when the temperature become lower than 0°C.

This icing causes the sticking of movable portion, the operation delay and the contact conduction failure etc.

Panasonic Corporation does not guarantee the failures caused by the icing.

The heat conduction by the equipment may accelerate the cooling of relay itself and the icing may occur.

Please conduct product evaluations in the worst condition of the actual usage.

Low temperature and low humidity

The plastic becomes brittle if the switch is exposed to a low temperature, low humidity environment for long periods of time.

High temperature and high humidity

Storage for extended periods of time (including transportation periods) at high temperature or high humidity levels or in atmospheres with organic gases or sulfide gases may cause a sulfide film or oxide film to form on the surfaces of the contacts and/or it may interfere with the functions.

Check out the atmosphere in which the units are to be stored and transported.

Package

In terms of the packing format used, make every effort to keep the effects of moisture, organic gases and sulfide gases to the absolute minimum.

Storage requirements

Since the surface-mount terminal type is sensitive to humidity it is packaged with tightly sealed anti-humidity packaging. However, when storing, please be careful of the following.

- Please use promptly once the anti-humidity pack is opened. (within 72 hours, Max. 30°C / 70% RH).
 If left with the pack open, the relay will absorb moisture which will cause thermal stress when reflow mounting and thus cause the case to expand. As a result, the seal may break.
- If relays will not be used within 72 hours, please store relays in a humidity controlled desiccator or in an anti-humidity bag to which silica gel has been added.

* If the relay is to be soldered after it has been exposed to excessive humidity atmosphere, cracks and leaks can occur. Be sure to mount the relay under the required mounting conditions.


- 3) When relays (which is packaged with humidity indicator and silica gel) meeting one of below criteria, please bake (dry) before use.
 - When the storage conditions specified in 1) are exceeded.
 - When humidity indicator is in **I** or **I** status according to judgement standard.

<How to judge>

Please check humidity indicator color and decide if baking is necessary or not.

• : indicate brown, \circ : Other than brown (blueish color)


\square	5%	10%	60%	Bake treatment necessity judgment
Ι	•	•	•	No need to bake
Π	0	•	•	No need to bake
Ш	0	0	•	Need to bake
IV	0	0	0	Need to bake



Humidity indicator card

<Baking (Drying) conditions>

• With reel : 45°C, 96 hours or more.



• Without reel (including relay only) : 60°C, 35 hours or more.



 The following cautionary label is affixed to the anti-humidity pack.

Caution

This vacuum-sealed bag contains

Moisture Sensitive Products

After this bag is opened, the product must be used

within 72 hours

If product is not used within 72 hours, baking is necessary. For baking conditions please contact us.

Silicon

When a source of silicone substances (silicone rubber, silicone oil, silicone coating materials and silicone filling materials etc.) is used around the relay, the silicone gas (low molecular siloxane etc.) may be produced

This silicone gas may penetrate into the inside of the relay. When the relay is kept and used in this condition, silicone compound may adhere to the relay contacts which may cause the contact failure.

Do not use any sources of silicone gas around the relay (Including plastic seal types).

NOx Generation

When relay is used in an atmosphere high in humidity to switch a load which easily produces an arc, the NOx created by the arc and the water absorbed from outside the relay combine to produce nitric acid.

This corrodes the internal metal parts and adversely affects operation.

Avoid use at an ambient humidity of 85% RH or higher (at 20°C).

If use at high humidity is unavoidable, please contact our sales representative.

OTHERS

Cleaning

- Although the environmentally sealed type relay (plastic sealed type,etc.) can be cleaned, avoid immersing the relay into cold liquid (such as cleaning solvent) immediately after soldering. Doing so may deteriorate the sealing performance.
- 2) Surface-mount terminal type relay is sealed type and it can be cleaned by immersion.

Use pure water or alcohol-based cleaning solvent.

 Cleaning with the boiling method is recommended (The temperature of cleaning liquid should be 40°C or lower). Avoid ultrasonic cleaning on relays.
Use of ultrasonic cleaning may cause breaks in the coil or

slight sticking of the contacts due to the ultrasonic energy.

Please refer to **"the latest product specifications"** when designing your product. •Requests to customers: https://industrial.panasonic.com/ac/e/salespolicies/

Please contact

Panasonic Corporation

Electromechanical Control Business Division 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan industral.panasonic.com/ac/e/



©Panasonic Corporation 2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

AGN200A03 AGN200A4H AGN200A4HZ AGN2004H AGN200A12 AGN200A12Z AGN20012 AGN20024 AGN200S03 AGN210A4HZ AGN20009 AGN200A03X AGN200A09Z AGN200S06 AGN200S06Z AGN210A03Z AGN210A06 AGN210A09Z AGN210A12Z AGN210S03 AGN210S03Z AGN210S12 AGN200S03Z AGN2003 AGN21003 AGN200S4H AGN200S4HZ AGN210A4H AGN210S4H AGN210S4HZ AGN2104H AGN200A06 AGN200A06Z AGN200S12Z AGN21012 AGN200A24 AGN200A24Z AGN200S24Z AGN200S12 AGN210A03 AGN20006 AGN2604H AGN26012 AGN26024 AGN260A12 AGN260A24 AGN260S03