Panasonic

INDUSTRY

Conductive Polymer Aluminum Solid Capacitors

Radial Lead Type






Features

- Super low ESR (5 mΩ max.)
- Large capacitance (2700 µF max.)
- RoHS compliance, Halogen free


Chacifications									
Specifications									
Size code	B9	C55	C6	C9	E7	E9	E12	E13	F13
Category temp. range					–55 ℃ to	+105 ℃			
Rated voltage range (V)	2.5	6.3	2.5	to 16	6.3 to 16	2.5 to 16	16	2.5 to 6.3	2.5 to 16
Nominal cap.range (µF)	100 to 560	220	100 to 560	100 to 820	150 to 1000	180 to 1000	180 to 270	470 to 820	470 to 2700
Capacitance tolerance				±	20 % (120	Hz / +20 ℃)			
DC leakage current		Please see the attached characteristics list							
Dissipation factor (tan δ)				Please see	the attach	ned character	istics list		
	+105 ℃ 5	000 h, rat	ed voltage	applied					
Endurance	Capac	itance cha	ange \	Within ±20 % of the initial value					
Eliquiance	Dissipati	ion factor	(tanδ) :	≦ 150 % of	the initial li	mit			
	DC lea	akage cur	rent \	Within the initial limit					
	+60 ℃, 90	% to 95	% RH, 10	00 h, No-ap	plied volta	ge			
Damp heat	Capacitance change			Within ±20 % of the initial value					
(Steady state) Dissipation factor $(\tan \delta) \le 150 \%$ of the initial limit									
	DC lea	akage cur	rent \	Within the initial limit (after voltage processing)					


Marking



* Depends on the case size.

Dimensions (not to scale)





Flat rubber is used for B9, C55, C6, C9, E7, and E9 size.

				Unit: mm
Size code	øD±0.5	L max.	F±0.5	ød±0.05
B9	5.0	9.0	2.0	0.6
C55	6.3	5.5	2.5	0.45
C6	6.3	6.0	2.5	0.5
C9	6.3	9.0	2.5	0.6
E7	8.0	7.0	3.5	0.6*2
E9	8.0	9.0	3.5	0.6
E12	8.0	12.0	3.5	0.6
E13	8.0	13.0	3.5	0.6
F13	10.0	13.0	5.0	0.6

^{*1: 16}SEPC100M: 0.45±0.05

^{*2: 16}SEPC150MD、10SEPC270M: 0.45±0.05

Characteristics list Case size Specifications Part number (mm) Rated Rated capacitance Size Ripple voltage ESR*2 LC*4 (±20 %) Click here for part number code tan δ^{*3} (V) øD L current *1 list of lead terminal cutting (µF) (mΩ max.) (µA) and lead terminal taping (mA rms) 100 5.0 4180 7 0.10 500 2SEPC100MZ 9.0 В9 500 330 5.0 9.0 4180 7 0.10 2SEPC330MZ 390 6.3 6.0 C6 3900 10 0.12 500 2SEPC390M 500 4180 7 2SEPC470MZ 470 5.0 9.0 0.10 **B9** 5.0 9.0 4180 7 0.10 500 2SEPC560MZ 3900 10 500 2SEPC560M 6.3 6.0 C6 0.12 560 500 2SEPC560MW 6.3 9.0 C9 5600 7 0.10 280 2SEPC560MX E9 4700 2.5 8.0 9.0 8 0.10 6.3 9.0 C9 5600 7 0.10 500 2SEPC820MW 500 8.0 7.0 E7 5300 8 0.10 2SEPC820MD 500 2SEPC820MX 6100 820 8.0 9.0 7 0.10 E9 7200 500 2SEPC820MY 8.0 9.0 5 0.10 13.0 E13 6100 7 500 2R5SEPC820M 8.0 0.10 7 500 2SEPC1000MX 1000 9.0 E9 6100 0.10 8.0 2700 13.0 F13 1350 2SFPC2700M 10.0 5560 10 0.10 500 4SEPC560MW 6.3 9.0 C9 5600 7 0.10 4SEPC560MX 560 8.0 9.0 E9 6100 7 0.10 500 500 4SEPC560M 4.0 8.0 13.0 6100 7 0.10 E13 7 544 4SEPC680M 680 8.0 13.0 6100 0.10 4SEPC820M 820 10.0 13.0 F13 6640 7 0.10 656 280 6SEPC220M 2980 220 6.3 5.5 C55 18 0.12 6.3 9.0 C9 5600 7 0.10 592 6SEPC470MW 9.0 E9 5700 8 592 6SEPC470MX 470 8.0 0.10 8.0 13.0 E13 5700 8 0.10 592 6SEPC470M 7 705 6SEPC560MW 9.0 C9 5600 6.3 6.3 0.10 560 8.0 9.0 E9 6100 0.10 705 6SEPC560MX 7 680 10.0 13.0 F13 6640 7 0.10 857 6SEPC680M 6SEPC1000MD 1000 8.0 7.0 E7 3530 18 0.10 1260 1890 6SEPC1500M 1500 10.0 13.0 F13 5560 10 0.10 8.0 7.0 E7 3220 22 500 10SEPC270MD 10 270 0.12 320 16SEPC100M 6.3 6.0 C6 2490 24 0.10 100 6.3 9.0 C9 4680 10 0.10 500 16SEPC100MW 150 3220 22 500 16SEPC150MD 8.0 7.0 E7 0.12 576 16SEPC180MX 8.0 9.0 E9 5000 10 0.10 180 576 16SEPC180M 12.0 16 8.0 E12 4360 16 0.10 16SEPC220MD 220 8.0 7.0 E7 4150 13 0.10 500 8.0 9.0 E9 5000 10 0.10 864 16SEPC270MX 270 12.0 864 16SEPC270M 8.0 E12 5000 11 0.10 470 1504 16SEPC470M 10.0 13.0 F13 6100 10 0.10

[◆] Please refer to each page in this catarog for "Flow conditions" and "Taping specifications".

Frequency	Frequency correction factor for ripple current									
Frequency(f)	120 Hz ≦ f < 1 kHz	1 kHz ≦ f < 10 kHz	10 kHz ≦ f < 100 kHz	100 kHz ≦ f < 500 kHz						
Coefficient	0.05	0.3	0.7	1						

^{*1:} Ripple current (100 kHz / +105 ℃)

^{*2:} ESR (100 kHz to 300 kHz / +20 ℃)

^{*3:} tan δ (120 Hz / +20 °C)

^{*4:} After 2 minutes

Packing specifications

♦ Radial lead type

Lead terminal process

1-1. Correspondence list

** The following table is a standard specification. Please contact us separately concerming specifications except for that mentioned below.

Series	Size code	Bag-packed products	(lead terminal cutting)	Taning products
Series	Size code	Not processed	Straight cut	Taping products
	B9, C55, C6, C9, E7, E9, E12	No code	+C3	+TSS (+S)
SEPC	E13	No code	+C3	+TS
	F13	No code	+C3	+T

1-2. Lead terminal cutting specifications

Process names	Size code	Lead terminal cutting code	Lead terminal dimensions
Straight cut	B9 C55, C6, C9 E7, E9, E12, E13 F13	+C3	L Unit : mm

1-3. Taping specifications for automatic insertion

Size code	Case size	F	Taping code	Taping dimensions		
В9	ø5	F=2.0 mm		P2		
C55, C6, C9	ø6.3	F=2.5 mm	+TSS (+S)	+TSS (+S)	* · · · · · · · · · · · · · · · · · ·	
E7, E9, E12	ø8	F=3.5 mm		ΔDo ± t Hold-down tape		
E13	ø8	F=3.5 mm	+TS	P ₂ P ₃ P ₄ P ₄ P ₅ P ₆ P ₇ P ₇ P ₈ P ₈ P ₈ P ₉ P ₉ P ₉ P ₉ P ₁		
F13	ø10	F=5.0 mm	+T	P) P) P) Carrier tape		

Cod	ام		D	D.	D	P_2	۸ ۵	W	۱۸/	W ₁	W_2	ш	~D
Cod	е	Г	Р	Ρ ₀	F ₁	Γ2	Δh	VV	W_0	vv ₁	VV ₂	Н	ϕD_0
Tolera	nce	+0.8 -0.2	±1.0	±0.2	±0.5	±1.0	±1.0	±0.5	min.	±0.5	max.	±0.75	±0.2
	ø5	2.0	12.7	12.7	5.35	6.35	0	18.0	9.5	9.0	2.5	17.5	4.0
+TSS (+S)	ø6.3	2.5	12.7	12.7	5.10	6.35	0	18.0	9.5	9.0	2.5	17.5	4.0
	ø8	3.5	12.7	12.7	4.60	6.35	0	18.0	9.5	9.0	2.5	17.5	4.0
+TS	ø8	3.5	12.7	12.7	4.60	6.35	0	18.0	9.5	9.0	2.5	17.5	4.0
+T	ø10	5.0	12.7	12.7	3.85	6.35	0	18.0	9.5	9.0	2.5	18.5	4.0

Cod	е	t	l	L
Tolera	nce	±0.3	max.	max.
	ø5	0.6	0	11.0
+TSS (+S)	ø6.3	0.6	0	11.0
	ø8	0.6	0	11.0
+TS	ø8	0.6	0	11.0
+T	ø10	0.6	0	11.0

Unit: mm

Minimum packing quantity and weight

ı	Size	Case	Bag-packe	d products	Taping	oroducts
	code	size	Quantity(pcs./Bag)	Typical weight(g)	Quantity(pcs./Bag)	Typical weight(g)
-	В9	ø5	500	180	2000	1000
-	C55	ø6.3	500	150	1500	650
Ī	C6	ø6.3	500	160	1500	700
-	C9	ø6.3	500	240	1500	1000

Size	Case	Bag-packe	d products	Taping p	oroducts
code	size	Quantity(pcs./Bag)	Typical weight(g)	Quantity(pcs./Bag)	Typical weight(g)
E7	ø8	200	110	1000	820
E9	ø8	200	130	1000	900
E12	ø8	200	200	1000	980
E13	ø8	200	160	1000	1060
F13	ø10	200	280	500	940

dial lead (Le	ead terminal cutting / Lea	ad terminal taping)	
Series	No processing	Lead terminal cutting	Lead terminal tapin
	10SEPC270MD	10SEPC270MD+C3	10SEPC270MD+S
	16SEPC100M	16SEPC100M+C3	16SEPC100M+TSS
	16SEPC100MW	16SEPC100MW+C3	16SEPC100MW+S
	16SEPC150MD	16SEPC150MD+C3	16SEPC150MD+S
	16SEPC180M	16SEPC180M+C3	16SEPC180M+TSS
	16SEPC180MX	16SEPC180MX+C3	16SEPC180MX+S
	16SEPC220MD	16SEPC220MD+C3	16SEPC220MD+S
	16SEPC270M	16SEPC270M+C3	16SEPC270M+TSS
	16SEPC270MX	16SEPC270MX+C3	16SEPC270MX+S
	16SEPC470M	16SEPC470M+C3	16SEPC470M+T
	2R5SEPC820M	2R5SEPC820M+C3	2R5SEPC820M+TS
	2SEPC1000MX	2SEPC1000MX+C3	2SEPC1000MX+S
	2SEPC100MZ	2SEPC100MZ+C3	2SEPC100MZ+TSS
	2SEPC2700M	2SEPC2700M+C3	2SEPC2700M+T
	2SEPC330MZ	2SEPC330MZ+C3	2SEPC330MZ+TSS
	2SEPC390M	2SEPC390M+C3	2SEPC390M+TSS
	2SEPC470MZ	2SEPC470MZ+C3	2SEPC470MZ+TSS
	2SEPC560M	2SEPC560M+C3	2SEPC560M+TSS
	2SEPC560MW	2SEPC560MW+C3	2SEPC560MW+TS
SEPC	2SEPC560MX	2SEPC560MX+C3	2SEPC560MX+TSS
	2SEPC560MZ	2SEPC560MZ+C3	2SEPC560MZ+TSS
	2SEPC820MD	2SEPC820MD+C3	2SEPC820MD+TSS
	2SEPC820MW	2SEPC820MW+C3	2SEPC820MW+TS
	2SEPC820MX	2SEPC820MX+C3	2SEPC820MX+TSS
	2SEPC820MY	2SEPC820MY+C3	2SEPC820MY+TSS
	4SEPC560M	4SEPC560M+C3	4SEPC560M+TS
	4SEPC560MW	4SEPC560MW+C3	4SEPC560MW+TS
	4SEPC560MX	4SEPC560MX+C3	4SEPC560MX+TSS
	4SEPC680M	4SEPC680M+C3	4SEPC680M+TS
	4SEPC820M	4SEPC820M+C3	4SEPC820M+T
	6SEPC1000MD	6SEPC1000MD+C3	6SEPC1000MD+S
	6SEPC1500M	6SEPC1500M+C3	6SEPC1500M+T
	6SEPC220M	6SEPC220M+C3	6SEPC220M+TSS
	6SEPC470M	6SEPC470M+C3	6SEPC470M+TS
	6SEPC470MW	6SEPC470MW+C3	6SEPC470MW+TS
	6SEPC470MX	6SEPC470MX+C3	6SEPC470MX+TSS
	6SEPC560MW	6SEPC560MW+C3	6SEPC560MW+TS
	6SEPC560MX	6SEPC560MX+C3	6SEPC560MX+TSS
	6SEPC680M	6SEPC680M+C3	6SEPC680M+T



Guidelines and precautions regarding the technical information and use of our products described in this online catalog.

- If you want to use our products described in this online catalog for applications requiring special qualities or reliability, or for applications where the failure or malfunction of the products may directly jeopardize human life or potentially cause personal injury (e.g. aircraft and aerospace equipment, traffic and transportation equipment, combustion equipment, medical equipment, accident prevention, anti-crime equipment, and/or safety equipment), it is necessary to verify whether the specifications of our products fit to such applications. Please ensure that you will ask and check with our inquiry desk as to whether the specifications of our products fit to such applications use before you use our products.
- The quality and performance of our products as described in this online catalog only apply to our products when used in isolation. Therefore, please ensure you evaluate and verify our products under the specific circumstances in which our products are assembled in your own products and in which our products will actually be used.
- If you use our products in equipment that requires a high degree of reliability, regardless of the application, it is recommended that you set up protection circuits and redundancy circuits in order to ensure safety of your equipment.
- The products and product specifications described in this online catalog are subject to change for improvement without prior notice. Therefore, please be sure to request and confirm the latest product specifications which explain the specifications of our products in detail, before you finalize the design of your applications, purchase, or use our products.
- The technical information in this online catalog provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.
- If any of our products, product specifications and/or technical information in this online catalog is to be exported or provided to non-residents, the laws and regulations of the exporting country, especially with regard to security and export control, shall be observed.

<Regarding the Certificate of Compliance with the EU RoHS Directive/REACH Regulations>

- The switchover date for compliance with the RoHS Directive/REACH Regulations varies depending on the part number or series of our products.
- When you use the inventory of our products for which it is unclear whether those products are compliant with the RoHS Directive/REACH Regulation, please select "Sales Inquiry" in the website inquiry form and contact us.

We do not take any responsibility for the use of our products outside the scope of the specifications, descriptions, guidelines and precautions described in this online catalog.



Notices

■ Applicable laws and regulations

- •This product complies with the RoHS Directive (Restriction of the use of certain hazardous substances in electrical and electronic equipment (DIRECTIVE 2011/65/EU and (EU)2015/863)).
- No Ozone Depleting Chemicals(ODC's), controlled under the Montreal Protocol Agreement, are used in producing this product. We do not use PBBs or PBDEs as brominated flame retardants.
- Export procedure which followed export related regulations, such as foreign exchange and a foreign trade method, on the occasion of export of this product.
- These products are not dangerous goods on the transportation as identified by UN(United Nations) numbers or UN classification.

Limited applications

- This capacitor is designed to be used for electronics circuits such as audio/visual equipment, home appliances, computers and other office equipment, optical equipment, measuring equipment.
- Prior to usage of this capacitor for applications requiring high reliability and safety and malfunction of capacitor might threaten human life or property, it is highly recommended to confirm the usage of this capacitors with Panasonic.

■ Intellectual property rights and licenses

• The technical information in this specification provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.

Items to be observed

■ For specification

• This specification guarantees the quality and performance of the product as individual components. The durability differs depending on the environment and the conditions of usage.

Before use, check and evaluate their compatibility with actual conditions when installed in the products.

When safety requirements cannot be satisfied in your technical examination, inform us immediately.

· Do not use the products beyond the specifications described in this document.

■ Upon application to products where safety is regarded as important

Install the following systems for a fail-safe design to ensure safety if these products are to be used in equipment where a defect in these products may cause the loss of human life or other signification damage, such as damage to vehicles (automobile, train, vessel), traffic lights, medical equipment, aerospace equipment, electric heating appliances, combustion/ gas equipment, rotating rotating equipment, and disaster/crime prevention equipment.

- (1) The system is equipped with a protection circuit and protection device.
- (2) The system is equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault.

Conditions of use

- Before using the products, carefully check the effects on their quality and performance, and determined whether or not they can be used. These products are designed and manufactured for general-purpose and standard use in general electronic equipment. These products are not intended for use in the following special conditions.
 - (1) In liquid, such as Water, Oil, Chemicals, or Organic solvent.
 - (2) In direct sunlight, outdoors, or in dust.
 - (3) In vapor, such as dew condensation water of resistive element, or water leakage, salty air, or air with a high concentration corrosive gas, such as Cl₂, H₂S, NH₃, SO₂, or NOx.
 - (4) In an environment where strong static electricity or electromagnetic waves exist.
 - (5) Mounting or placing heat-generating components or inflammables, such as vinyl-coated wires, near these products.
 - (6) Sealing or coating of these products or a printed circuit board on which these products are mounted, with resin and other material.
 - (7) Using resolvent, water or water-soluble cleaner for flux cleaning agent after soldering. (In particular, when using water or a water-soluble cleaning agent, be careful not to leave water residues)
 - (8) Using in the atmosphere where strays acid or alkaline.
 - (9) Using in the atmosphere where there are excessive vibration and shock.
 - (10) Using in the atmosphere where there are low pressure or decompression.
- · Please arrange circuit design for preventing impulse or transitional voltage.
- Do not apply voltage, which exceeds the full rated voltage when the capacitors receive impulse voltage, instantaneous high voltage, high pulse voltage etc.
- Our products there is a product are using an electrolyte solution. Therefore, misuse can result in rapid deterioration of characteristics and functions of each product. Electrolyte leakage damages printed circuit and affects performance, characteristics, and functions of customer system.



Ţ

Application Guidelines (OS-CON)

1. Circuit design

1.1 Prohibited circuits

- (1) Leakage current of the OS-CON may increase in the following conditions.
 - (a) Soldering
 - (b) When voltage is not applied: high temperature no-load test, high temperature and high humiditynoload test, rapidly changing temperature test, etc.
- (2) Avoid the use of the OS-CON in the following type of circuits because leakage current may increase.
 - (a) High-impedance circuits
 - (b) Coupling circuits
 - (c) Time constant circuits
 - (d) Other circuits that are significantly affected by leakage current.
 - * If you plan to use 2 or more OS-CONs in a series connection, please contact us before use.

1.2 Failure and life-span

The failure rate is 0.5 % /1000 h (Confidence level: 60 %) based on JIS C 5003.

The prospective failure is not zero. The mainly failure modes are as follows.

1.2-1 Contingency failure

The most common failure mode is a short circuit. Mainly caused by the soldering or operating temperature environment, along with heat stresses, electrical stresses or mechanical stressesas follows.

- · Applying voltage over the rated voltage.
- · Applying reverse voltage
- · Excessive mechanical stress
- · Applying rush current by sudden charge or discharge out of the specification.
- (1) The following phenomenon is seen when short-current is applied to the OS-CON.
 - (a) When current is relatively low. (ø10 : approx 1 A or less, ø8 : approx 0.5 A or less, ø6.3 : approx 0.2 A or less) The OS-CON becomes heated, but no effects are visible even when the current is continuously carried.
 - (b) When the short circuit currents exceed the mentioned value above.
 - After internal temperature increase, sealing rubber may be turned over.
 - In some cases, odorous gas may be produced.
- (2) In case a short circuit occurs, ensure safety by fully considering the followings.
 - (a) If odorous gas is released, turn off the main power of the equipment.
 - In this case, keep your face and hands away from the area.
 - (b) Though it depends on the conditions, it takes seconds to minutes before odorant gas generates. Protective circuit should operate in this period.
 - (c) If the gas comes into eyes, rinse immediately. If the gas is inhaled, gargle immediately.
 - (d) Do not lick the electrolyte. If the electrolyte touches skin, wash it off with soap immediately.
 - (e) The OS-CON contains combustible substances. In case a large current continues to flow after a short circuit, in the worst case, the shorted-out section may ignite. For safety, install a redundant circuit or a protective circuit, etc.

1.2-2 Wear-out failure (life time)

When lifetime span exceeded the specified guarantee time of endurance and damp heat, electrolyte might insulate and cause electric characteristic changed. This is called an open circuit.

The electric characteristics of capacitance and ESR may possibly change within the specified range in specifications even if it is used under the condition of the rated voltage, electric and mechanical performance.

Please note it when designing.

1.3 Leakage current

Mechanical stress may cause OS-CON's leakage current increased.

In such a case, leakage current will gradually decrease by applying voltage (withinthe category voltage and the upper limit of category temperature).

1.4 Rapid charge and discharge limitation

Allowance of a large rush current to flow due to rapid charge and discharge may result in short circuit or large leakage current. The protection circuit, to maintain high reliability, is recommended when rush current to flow to the OS-CON is in the following cases.

- (1) Products which 10 times of allowable ripple current is less than 10 A: It is when 10 A or over of rush current is applied.
- (2) Products which 10 times of allowable ripple current is 10 A or over : It is when rush current, which the figure is over 10 times of allowable ripple current, is applied.



2. Mounting

2.1 Soldering with a soldering iron

- (1) When lead terminals for radial lead type must be processed because the lead pitch and the PCB holes do not match, process them without any stresses to the OS-CON before soldering.
- (2) Solder without any excessive stresses to the OS-CON itself.
- (3) When the OS-CON has been soldered once and needs to be removed, remove it after the solder has been completely melted
- (4) Do not let the tip of the soldering iron touch the OS-CON itself.

2.2 Flow soldering

- (1) Do not apply flow soldering to OS-CON SMD type.
- (2) Do not solder the OS-CON itself by submerging it in melted solder.
- (3) Solder the opposite side that the OS-CON is mounted on.
- (4) Note that flux does not adhere to anywhere expect the lead terminal.
- (5) Note that other components do not fall over and touch the OS-CON when soldering.

2.3 Reflow soldering

- (1) Do not apply reflow soldering to OS-CON Radial Lead type.
- (2) Please contact us for setting VPS conditions.

2.4 Capacitor handling after soldering

Do not subject the OS-CON to excessive stress as follows.

- (1) Do not tilt, bend or twist the OS-CON.
- (2) Do not move the PCB with holding the OS-CON itself.
- (3) Do not hit the OS-CON with objects.
- (4) When stacking PCBs, make sure that the OS-CON does not touch other PCBs or components.

2.5 Circuit board cleaning

Check the following items before washing PC board with these detergents: high quality alcohol-based cleaning fluid such as Pine-a ST-100S, clean thru 750H, 750L, 710M, 750K or Techno Care FRW 14 through 17 or detergents including substitute freon as AK-225AES or IPA.

- (1) Use immersion or ultrasonic waves to clean within 2 minutes.
- (2) The temperature of the cleaning fluid should be less than 60 °C.
- (3) Watch the contamination of the detergent such as conductivity, pH, specific gravity, water content, etc.
- (4) Do not store the OS-CON in a location subject to gases from the cleaning fluid or in an airtight container after cleaning.
- (5) Dry the PCB or OS-CON with hot air that should be less than the upper category temperature.
- (6) Please note that indication may disappear when rubbing print side after washing depending on a cleaner.
- (7) Please contact us for details about detergents, cleaning methods and detergents other than those listed above.

2.6 Fixatives and coating materials

- (1) Select the appropriate covering and sealant materials for the OS-CON. In particular, don't use acetone in the fixative, coating agent and diluent.
- (2) Before applying the fixative or coating, completely remove any flux residue and foreign matter from the area where the board and the OS-CON will be jointed together.
- (3) Allow any detergent to dry before applying the fixative or coating.
- (4) Please contact us for the fixative and coating heat curing conditions.

2.7 Capacitor insulation

Be sure to completely separate the case, negative lead terminal, positive lead terminal and PC board patterns with each other due to the following reasons.

- (1) Insulation is not guaranteed at a part of resin on the surface of a case.
- (2) It offers inconstant resistance between a case and a negative lead terminal and it isn't insulated.



3. Storage

Open the bags just before mounting and use up all products once opened, For keeping a good solderability, store the OS-CON as follows.

		Before unsealing	After unsealing	
SMD type ^{*1}		Within 24 months after shipment	Within 30 days from opening (packaged with carrier tape)	
Radial	Bag packing product	Within 30 months after shipment	Within 7 days from opening	
lead type	Taping product	Within 24 months after shipment	within r days from opening	

*1 : The JEDEC J-STD-020 standard is not applicable

* Intellectual property right

We, Panasonic Group are providing the product and service that customers can use without anxiety, and are working positively on the protection of our products underintellectual property rights.

Representative patents relating to OS-CON are as follows:

US Patent No.7158367

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

6SEPC220M 2R5SEPC820M+TS 2SEPC330MZ+TSS 2SEPC820MD 2SEPC560MX+TSS 2SEPC820MY+TSS 4SEPC560MW 16SEPC180MX+S 10SEPC270MD+S 6SEPC560MW 2SEPC470MZ 2SEPC560M+TSS 2SEPC820MW+TSS 16SEPC270M 6SEPC560MX+TSS 4SEPC560MX+TSS 2SEPC2700M+T 2SEPC100MZ 16SEPC100MW 16SEPC270MX+S 6SEPC680M 6SEPC560MW+TSS 4SEPC680M+TS 2SEPC820MW 6SEPC1500M 6SEPC220M+TSS 16SEPC180M 2SEPC330MZ 6SEPC470ME 6SEPC470ME+TSS 6SEPC470MX 2SEPC560MZ+TSS 2SEPC390M+TSS 2SEPC560MW+TSS 2SEPC820MX+TSS 2SEPC560M 2SEPC560MX 4SEPC560MX 4SEPC560M+TS 16SEPC150MD+S 2SEPC820MD+TSS 2SEPC470MZ+TSS 2SEPC470MZ+TSS 2SEPC820M 2SEPC1000MX+S 4SEPC820M+T 2SEPC820MX 16SEPC270MX 16SEPC470M+T 2SEPC390M 10SEPC270MD 16SEPC100MX+TSS 6SEPC470M+T 2SEPC390M 16SEPC180M+TSS 2SEPC1000MX 6SEPC470MW 16SEPC100MW+S 16SEPC100M 16SEPC470M 6SEPC470M 6SEPC470M 16SEPC270MD 16SEPC270M+TSS 4SEPC820M 4SEPC560MX 4SEPC560MW+TSS 4SEPC820M 16SEPC270M+TSS 4SEPC820M 6SEPC470MX+TSS 6SEPC560MW 4SEPC560MW+TSS 4SEPC820M 6SEPC470MW+TSS 2SEPC560MW+TSS 4SEPC820M 6SEPC470MX+TSS 6SEPC560MW 4SEPC560MW+TSS 4SEPC820M 6SEPC470MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 4SEPC820M 6SEPC470MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 4SEPC820M 6SEPC470MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MW+TSS 2SEPC560MM+TSS 4SEPC820M 6SEPC470MW+TSS 2SEPC560MM+TSS 2SEPC560MM+TSS 2SEPC560MW+TSS 2SEPC560MM+TSS 2S