


## Surface Mount Type

Series: **FC** Type: **V**

Low impedance



### ■ Features

- Endurance : 105 °C 1000 h
- Low impedance (1/2 for HA series)
- Vibration-proof product is available upon request. (ø8 mm and larger)
- AEC-Q200 qualified\*
- RoHS directive compliant

### ■ Specifications

Category Temp. Range	-40 °C to +105 °C							
Rated W.V. Range	6.3 V.DC to 50 V.DC							
Nominal Cap. Range	1 µF to 1500 µF							
Capacitance Tolerance	±20 % (120 Hz/+20 °C)							
DC Leakage Current	I ≤ 0.01 CV or 3 (µA) After 2 minutes (Whichever is greater)							
tan δ	Please see the attached standard products list							
Characteristics at Low Temperature	W.V. (V)	6.3	10	16	25	35	50	(Impedance ratio at 120 Hz)
	Z(-25 °C) / Z(+20 °C)	2	2	2	2	2	2	
	Z(-40 °C) / Z(+20 °C)	3	3	3	3	3	3	
Endurance	After applying rated working voltage for 1000 hours at +105 °C±2 °C and then being stabilized at +20 °C, Capacitors shall meet the following limits.							
	Capacitance change	±20 % of initial measured value						
	tan δ	≤ 200 % of initial specified value						
	DC leakage current	≤ initial specified value						
Shelf Life	After storage for 1000 hours at +105 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance.(With voltage treatment)							
	After reflow soldering and then being stabilized at +20 °C, capacitor shall meet the following limits.							
Resistance to Soldering Heat	Capacitance change	±10 % of initial measured value						
	tan δ	≤ initial specified value						
	DC leakage current	≤ initial specified value						

### ■ Frequency correction factor for ripple current

	Frequency (Hz)				
	50, 60	120	1 k	10 k	100 k to
Correction factor	0.70	0.75	0.90	0.95	1.00

### ■ Marking

Example: 6.3 V 22 µF  
Marking color : BLACK

Rated Voltage Mark

j	6.3 V	E	25 V
A	10 V	V	35 V
C	16 V	H	50 V

### ■ Dimensions in mm (not to scale)

(Unit : mm)

Size code	D	L	A, B	H	I	W	P	K
B	4.0	5.4 <sup>+0.1</sup> <sub>-0.2</sub>	4.3	5.5 max.	1.8	0.65±0.1	1.0	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
C	5.0	5.4 <sup>+0.1</sup> <sub>-0.2</sub>	5.3	6.5 max.	2.2	0.65±0.1	1.5	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
D	6.3	5.4 <sup>+0.1</sup> <sub>-0.2</sub>	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
E	8.0	6.2±0.3	8.3	9.5 max.	3.4	0.65±0.1	2.2	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
F	8.0	10.2±0.3	8.3	10.0 max.	3.4	0.90±0.2	3.1	0.70±0.2
G	10.0	10.2±0.3	10.3	12.0 max.	3.5	0.90±0.2	4.6	0.70±0.2

\* This product qualify for AEC-Q200, but it has some deviations.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

01 Mar. 2014

## ■ Standard Products

Endurance : 105 °C 1000 h

W.V.	Cap. (±20 %)	Case size			Specification			Part No. (RoHS:compliant)	Reflow	Min. Packaging Q'ty
		Dia.	Length	Size Code	Ripple Current (100 kHz) (+105°C) (mA r.m.s.)	$\tan \delta$ (120 Hz) (+20 °C)	Impedance (100 kHz) (+20 °C) ( $\Omega$ )			Taping
(V)	( $\mu$ F)	(mm)	(mm)							(pcs)
6.3	22	4	5.4	B	60	0.26	3.00	EEEF0J220R	(1)	2000
	47	5	5.4	C	95	0.26	1.80	EEEF0J470R	(1)	1000
	68	6.3	5.4	D	140	0.26	1.00	EEEF0J680P	(1)	1000
	100	6.3	5.4	D	140	0.26	1.00	EEEF0J101P	(1)	1000
	220	8	6.2	E	230	0.26	0.40	EEEF0J221P	(2)	1000
	330	8	10.2	F	450	0.26	0.30	EEEF0J331P	(2)	500
	1000	10	10.2	G	670	0.26	0.15	EEEF0J102P	(2)	500
	1500	10	10.2	G	670	0.26	0.15	EEEF0J152P	(2)	500
10	33	5	5.4	C	95	0.19	1.80	EEEF1A330R	(1)	1000
	100	8	6.2	E	230	0.19	0.40	EEEF1A101P	(2)	1000
	150	8	6.2	E	230	0.19	0.40	EEEF1A151P	(2)	1000
	220	8	10.2	F	450	0.19	0.30	EEEF1A221P	(2)	500
	470	10	10.2	G	670	0.19	0.15	EEEF1A471P	(2)	500
	1000	10	10.2	G	670	0.19	0.15	EEEF1A102P	(2)	500
16	10	4	5.4	B	60	0.16	3.00	EEEF1C100R	(1)	2000
	22	5	5.4	C	95	0.16	1.80	EEEF1C220R	(1)	1000
	47	6.3	5.4	D	140	0.16	1.00	EEEF1C470P	(1)	1000
	68	8	6.2	E	230	0.16	0.40	EEEF1C680P	(2)	1000
	100	8	6.2	E	230	0.16	0.40	EEEF1C101P	(2)	1000
	220	10	10.2	G	670	0.16	0.15	EEEF1C221P	(2)	500
	330	10	10.2	G	670	0.16	0.15	EEEF1C331P	(2)	500
	470	10	10.2	G	670	0.16	0.15	EEEF1C471P	(2)	500
	680	10	10.2	G	670	0.16	0.15	EEEF1C681P	(2)	500
25	6.8	4	5.4	B	60	0.14	3.00	EEEF1E6R8R	(1)	2000
	22	6.3	5.4	D	140	0.14	1.00	EEEF1E220P	(1)	1000
	33	6.3	5.4	D	140	0.14	1.00	EEEF1E330P	(1)	1000
	47	8	6.2	E	230	0.14	0.40	EEEF1E470P	(2)	1000
	68	8	10.2	F	450	0.14	0.30	EEEF1E680P	(2)	500
	100	8	10.2	F	450	0.14	0.30	EEEF1E101P	(2)	500
	220	10	10.2	G	670	0.14	0.15	EEEF1E221P	(2)	500
	330	10	10.2	G	670	0.14	0.15	EEEF1E331P	(2)	500
	470	10	10.2	G	670	0.14	0.15	EEEF1E471P	(2)	500
35	1	4	5.4	B	60	0.12	3.00	EEEF1V1R0R	(1)	2000
	2.2	4	5.4	B	60	0.12	3.00	EEEF1V2R2R	(1)	2000
	3.3	4	5.4	B	60	0.12	3.00	EEEF1V3R3R	(1)	2000
	4.7	4	5.4	B	60	0.12	3.00	EEEF1V4R7R	(1)	2000
	6.8	5	5.4	C	95	0.12	1.80	EEEF1V6R8R	(1)	1000
	10	5	5.4	C	95	0.12	1.80	EEEF1V100R	(1)	1000
	22	6.3	5.4	D	140	0.12	1.00	EEEF1V220P	(1)	1000
	33	8	6.2	E	230	0.12	0.40	EEEF1V330P	(2)	1000
	47	8	6.2	E	230	0.12	0.40	EEEF1V470P	(2)	1000
	100	10	10.2	G	670	0.12	0.15	EEEF1V101P	(2)	500
	220	10	10.2	G	670	0.12	0.15	EEEF1V221P	(2)	500
	330	10	10.2	G	670	0.12	0.15	EEEF1V331P	(2)	500
50	1	4	5.4	B	30	0.12	5.00	EEEF1H1R0R	(1)	2000
	2.2	4	5.4	B	30	0.12	5.00	EEEF1H2R2R	(1)	2000
	3.3	4	5.4	B	30	0.12	5.00	EEEF1H3R3R	(1)	2000
	4.7	5	5.4	C	50	0.12	3.00	EEEF1H4R7R	(1)	1000
	10	6.3	5.4	D	70	0.12	2.00	EEEF1H100P	(1)	1000
	22	8	6.2	E	120	0.12	0.70	EEEF1H220P	(2)	1000
	33	8	10.2	F	300	0.12	0.60	EEEF1H330P	(2)	500
	47	10	10.2	G	500	0.12	0.30	EEEF1H470P	(2)	500
	100	10	10.2	G	500	0.12	0.30	EEEF1H101P	(2)	500
	220	10	10.2	G	500	0.12	0.30	EEEF1H221P	(2)	500

- Please refer to the page of "Reflow Profile" and "The Taping Dimensions".
- When requesting vibration-proof product, please put the last "V" instead to "P"

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panasonic:

[EEE-FC0J101P](#) [EEE-FC0J102P](#) [EEE-FC0J152P](#) [EEE-FC0J220R](#) [EEE-FC0J221P](#) [EEE-FC0J331P](#) [EEE-FC0J470R](#) [EEE-FC0J680P](#) [EEE-FC1A101P](#) [EEE-FC1A102P](#) [EEE-FC1A151P](#) [EEE-FC1A221P](#) [EEE-FC1A330R](#) [EEE-FC1A471P](#) [EEE-FC1C100R](#) [EEE-FC1C101P](#) [EEE-FC1C220R](#) [EEE-FC1C221P](#) [EEE-FC1C331P](#) [EEE-FC1C470P](#) [EEE-FC1C471P](#) [EEE-FC1C680P](#) [EEE-FC1E101P](#) [EEE-FC1E220P](#) [EEE-FC1E221P](#) [EEE-FC1E330P](#) [EEE-FC1E331P](#) [EEE-FC1E470P](#) [EEE-FC1E471P](#) [EEE-FC1E680P](#) [EEE-FC1E6R8R](#) [EEE-FC1H100P](#) [EEE-FC1H101P](#) [EEE-FC1H1R0R](#) [EEE-FC1H220P](#) [EEE-FC1H221P](#) [EEE-FC1H2R2R](#) [EEE-FC1H330P](#) [EEE-FC1H3R3R](#) [EEE-FC1H470P](#) [EEE-FC1H4R7R](#) [EEE-FC1V100R](#) [EEE-FC1V101P](#) [EEE-FC1V1R0R](#) [EEE-FC1V220P](#) [EEE-FC1V221P](#) [EEE-FC1V2R2R](#) [EEE-FC1V330P](#) [EEE-FC1V331P](#) [EEE-FC1V3R3R](#) [EEE-FC1V470P](#) [EEE-FC1V4R7R](#) [EEE-FC1V6R8R](#) [EEV-FC1E6R8R](#) [EEE-FC1C681P](#) [EEE-FC1H101V](#)