



FEATURES

- 1. High inrush current capability**
 - 1) Operating load capability: inrush 118 A, steady 8 A
 - 2) UL/C-UL TV-8 approved
- 2. High insulation resistance**
 - 1) Creepage distance and clearances between contact and coil: Min. 6 mm .236 inch (In compliance with IEC60065)
 - 2) Surge withstand voltage between contact and coil: 10,000 V or more
- 3. Conforms to the various safety standards**
UL/C-UL, TÜV, and SEMKO approved

TYPICAL APPLICATIONS

- Audio visual equipment
- Flat TVs and audio equipment, etc.
- Office equipment
- Home appliances

ORDERING INFORMATION

	LKT	1a	F	-	
LK-T relay					
Contact arrangement 1a: 1 Form A					
Protective construction F: Flux-resistant type					
Nominal coil voltage (DC) 5V, 9V, 12V, 24V					

Notes: Certified by UL/C-UL, TÜV and SEMKO
VDE approved type is available. Please consult us for details.

TYPES

Contact arrangement	Nominal coil voltage	Part No.
1 Form A	5V DC	LKT1aF-5V
	9V DC	LKT1aF-9V
	12V DC	LKT1aF-12V
	24V DC	LKT1aF-24V

Standard packing Carton: 100 pcs. Case: 500 pcs.
Note: 3V, 6V and 18V DC types are also available. Please consult us for details.

RATING

1. Coil data

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 20°C 68°F)
5V DC	70%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	50mA	100Ω	250mW	6.5V DC
9V DC			27.8mA	324Ω		11.7V DC
12V DC			20.8mA	576Ω		15.6V DC
24V DC			10.4mA	2,304Ω		31.2V DC


2. Specifications

Characteristics	Item		Specifications
Contact	Arrangement		1 Form A
	Contact resistance (Initial)		Max. 100 mΩ (By voltage drop 6 V DC 1A)
	Contact material		AgSnO ₂ type
Rating	Nominal switching capacity (resistive load)		5A 277V AC
	Max. switching power (resistive load)		1,385VA
	Max. switching voltage		277V AC
	Max. switching current		8A (AC)
	Min. switching capacity (reference value)*1		100mA, 5V DC
Electrical characteristics	Insulation resistance (Initial)		Min. 1,000MΩ (at 500V DC) Measurement at same location as “Breakdown voltage” section.
	Breakdown voltage (Initial)	Between open contacts	1,000 Vrms for 1 min. (Detection current: 10 mA)
		Between contact and coil	4,000 Vrms for 1 min. (Detection current: 10 mA)
	Temperature rise (coil)		Max. 35°C 95°F (By resistive method, nominal coil voltage applied to the coil; contact carrying current: 5A, at 70°C 158°F)
	Surge breakdown voltage*2 (Between contact and coil) (Initial)		10,000 V
	Operate time (at nominal voltage) (at 20°C 68°F) (Initial)		Max. 15 ms (excluding contact bounce time.)
	Release time (at nominal voltage) (at 20°C 68°F) (Initial)		Max. 5 ms (excluding contact bounce time) (Without diode)
Mechanical characteristics	Shock resistance	Functional	200 m/s ² (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.)
		Destructive	1,000 m/s ² (Half-wave pulse of sine wave: 6 ms.)
	Vibration resistance	Functional	10 to 55 Hz at double amplitude of 1.5 mm (Detection time: 10μs.)
		Destructive	10 to 55 Hz at double amplitude of 1.5 mm
Expected life	Mechanical (at 180 times/min.)		Min. 10 ⁶
	Electrical (at 20 times/min.)		Min. 10 ⁵ (ON: 1.5s, OFF: 1.5s, at nominal switching capacity)
Conditions	Conditions for operation, transport and storage*3		Ambient temperature: −40°C to +70°C −40°F to +158°F, Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature), Air pressure: 86 to 106kPa
	Max. operating speed		20 times/min. (at nominal switching capacity)
Unit weight			Approx. 12 g .42 oz


Notes:
*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.
*2. Wave is standard shock voltage of ±1.2×50μs according to JEC-212-1981
*3. The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. Refer to "6. Usage, Storage and Transport Conditions" in [AMBIENT ENVIRONMENT](#) section in [Relay Technical Information](#).

REFERENCE DATA


1. Max. switching power (AC resistive load)



2. Coil temperature rise
Sample: LKT1aF-12V, 6 pcs.
Point measured: coil inside
Contact current: 0 A, 8A




3. Ambient temperature characteristics and coil applied voltage




4-(1). Electrical life test
 (5 A 277 V AC, resistive load)
 Sample: LKT1aF-12V, 6 pcs.
 Operation frequency: 20 times/min.
 (ON/OFF = 1.5s: 1.5s)
 Ambient temperature: 20°C 68°F


Circuit:



Change of pick-up and drop-out voltage




Change of contact resistance




4-(2). Electrical life test
 (UL508 TV-8 rating test)
 Sample: LKT1aF-12V, 6 pcs.

- Overload test
 Load: 12 A 120 V AC (60 Hz),
 Inductive load ($\cos\phi = 0.75$)
 Operation frequency: 6 times/min
 (ON : OFF = 1 s : 9 s)
 No. of operations: 50 ope.
- Endurance test
 Load: 8A 120 V AC (960 W lamp load),
 (Inrush: 118 A)
 Operation frequency: 1 times/min
 (ON : OFF = 1 s : 59 s)
 No. of operations: 25,000 ope.

Change of pick-up and drop-out voltage



Change of contact resistance




DIMENSIONS (mm inch)

Download [CAD Data](#) from our Web site.


CAD Data



External dimensions



PC board pattern (Bottom view)



Schematic (Bottom view)



Dimension:

Less than 1mm .039inch:
 Min. 1mm .039inch less than 3mm .118 inch: ±0.2 ±.008
 Min. 3mm .118 inch: ±0.3 ±.012

General tolerance

±0.1 ±.004
 ±0.2 ±.008
 ±0.3 ±.012

SAFETY STANDARDS

UL/C-UL (Recognized)		VDE (Certified)		TV rating (UL/C-UL)		TÜV (Certified)		SEMKO (Certified)	
File No.	Contact rating	File No.	Contact rating	File No.	Rating	File No.	Rating	File No.	Contact rating
E43149 (C-UL)	5A 277V AC 5A 30V DC 8A 277V AC 10A 277V AC	40014390	8A 250V AC ($\cos\phi=1.0$)	UL E43149	TV-8	B 11 03 13461 284	8A 250V AC ($\cos\phi=1.0$)	807779	3/100A 250V AC 5/40A 250V AC

* CSA standard: Certified by C-UL

For Cautions for Use, see [Relay Technical Information](#).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[LKT1AF-18V](#) [LKT1AF-3V](#) [LKT1AF-6V](#)