



**ALL DIMENSIONS ARE
FOR REFERENCE ONLY**
DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTHERWISE NOTED

SPECIFICATIONS

OVERALL HEIGHT..... 5.60 [142.29]
ROTATION..... 360 DEGREES
TURN..... 360 DEGREES
TILT..... 90 DEGREES
SHIPPING WEIGHT..... 5.25 LBS
VISE OPENING..... 2 1/4 [57.15] MAXIMUM
JAW WIDTH..... 2 1/2 [63.50]
JAW HEIGHT..... 1/2 [12.70]

MATERIAL:

- 1. VISE HEAD ASSY*..... 380 ALUMINUM DIE CASTING
SILVER PAINT
- 2. BASE ASSY**..... #3 ZINC DIE CAST SILVER PAINT
- 3. KNOB..... BLACK GLASS REINFORCED
THERMAL COMPOSITE ALLOY
- 4. BASE TRAY..... #3 ZINC DIE CAST SILVER PAINT
- 5. BUMPON..... BLACK RUBBER
- 6. SCREW..... 1/4-20 X 1/2 PHILLIPS HEAD, STEEL

*VISE HEAD ASSEMBLY INCLUDES ADJUSTING SCREW, GUIDE PINS, LEVER,
LEVER ROD CAPS AND STEM.
**BASE ASSEMBLY INCLUDES HALF BALL HOUSINGS, RETAINER RING,
SCREWS, STUD AND NUT.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
PANAVISE PRODUCTS INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
PANAVISE PRODUCTS INC IS
PROHIBITED.

		UNLESS OTHERWISE SPECIFIED:				NAME		DATE	
		DIMENSIONS ARE IN INCHES		DRAWN					
		TOLERANCES:		CHECKED					
		FRACTIONAL ± 1/64		ENG APPR.					
		ANGULAR:		MFG APPR.					
		MACH ± 1/2° BEND ±		Q.A.					
		TWO PLACE DECIMAL: ±.01		COMMENTS:					
		THREE PLACE DECIMAL: ±.005							
		INTERPRET GEOMETRIC							
		TOLERANCING PER: ASME 14.5M -2009							
		MATERIAL							
NEXT ASSY		USED ON		FINISH					
APPLICATION				DO NOT SCALE DRAWING					

7540 Colbert Drive, Reno, Nevada 89511-1225
Phone (775) 850-2900 Fax (775) 850-2929

TITLE:
LOW PROFILE PANAVISE
WORK CENTER SPEC SHEET

SIZE	DWG. NO.	REV
B	302-SP	A
SCALE: 1:2		WEIGHT:
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panavise:](#)

[302](#)