




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	RELEASE	JRM 2/16/21	

ALL DIMENSIONS ARE
FOR REFERENCE ONLY
DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTEHRWISE NOTED

SPECIFICATIONS

- OVERALL HEIGHT..... 7.12 [180.95]
ROTATION..... 360 DEGREES
TURN..... 360 DEGREES
TILT..... 90 DEGREES
SHIPPING WEIGHT..... 5.40 LBS
VISE OPENING W/JAW PADS..... 6 [152.40] MAXIMUM
JAW OPENING W/O JAW PADS..... 6 1/4 [158.75] MAXIMUM
JAW PAD WIDTH..... 1.5 [38.10]
JAW PAD HEIGHT..... 1.875 [47.63]

MATERIAL:

1. VISE HEAD ASSY*..... LOW CARBON STEEL,
ZINC DIE CASTING
2. BASE ASSY** #3 ZINC DIE CAST SILVER PAINT
3. KNOB..... BLACK GLASS REINFORCED THERMAL
COMPOSITE ALLOY
4. BASE TRAY..... #3 ZINC DIE CAST SILVER PAINT
5. JAW PADS..... BLACK NEOPRENE
6. BUMPON..... BLACK RUBBER
7. SCREW..... 1/4-20 X 1/2 PHILLIPS HEAD, STEEL

*VISE HEAD ASSEMBLY INCLUDES HEAD PLATE, HAIRPIN, ADJUSTING SCREW,
STEM AND VISE HEAD.
**BASE ASSEMBLY INCLUDES HALF BALL HOUSINGS, RETAINER RING,
SCREWS, STUD AND NUT.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
PANAVISE PRODUCTS INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
PANAVISE PRODUCTS INC IS
PROHIBITED.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1/2° BEND ± TWO PLACE DECIMAL: ± .01 THREE PLACE DECIMAL: ± .005		DRAWN	NAME	DATE	 7540 Colbert Drive, Reno, Nevada 89511-1225 Phone (775) 850-2900 Fax (775) 850-2929 TITLE: GENERAL PURPOSE WORKCENTER SPEC SHEET	
		CHECKED				
		ENG APPR.				
		MFG APPR.				
		Q.A.				
INTERPRET GEOMETRIC TOLERANCING PER: ASME 14.5M -2009 MATERIAL		COMMENTS:			SIZE B	DWG. NO. 367-SP
NEXT ASSY	USED ON	FINISH			REV A	
APPLICATION		DO NOT SCALE DRAWING			SCALE: 1:2	WEIGHT:
					SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panavise:](#)

[367](#)