

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





TABLE 1						
WIRE DIA.	PART NO.	DIM. "A" +/- .062	DIM 1/2 "A" +/- .062	DIM. "B" +/- .062	DIM. "C" +/- .062	LABELS/ ROLL
.12"-.20"	F100X150AJT	0.75 [19.1]	0.375 [9.7]	0.75 [19.1]	1.875 [47.8]	2500
.09"-.28"	F100X300AJT	2.00 [50.8]	1.00 [25.4]	1.00 [25.4]	3.375 [85.9]	2500
.32"-.38"	F100X213AJT	0.75 [19.1]	0.375 [9.7]	1.375 [35.1]	2.50 [63.5]	2500
.20"-.46"	F100X363AJT	2.00 [50.8]	1.00 [25.4]	1.625 [41.4]	4.00 [101.6]	2500

NOTE:
1. MILLIMETERS ARE IN [].

							TITLE "FLAG LABEL" THERMAL TRANSFER PRINTABLE CUSTOMER DRAWING					
							ITEM REVISION NAME I00412BH/08					
							DATASET FILE NAME I00412BH_DC_C10631/08H					
7	6/29/15	RVU	SEWH	JHAC	GMY4-F WAS GMY4-HT.	GAECN02945	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
6	1/26/11	RVU			CHANGE WIRE DIA. NUMBERS.	6290	.x ± .12 [3.05] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±				GMY4-F WHITE POLYESTER	
5	9/29/10	RVU			Change the Wire Dia. numbers to: F100X150AJT- .12"- .20", F100X300AJT- .09"- .28", F100X213AJT- .32"- .40", & F100X363AJT- .20"- .48".	6158	 THIRD ANGLE PROJECTION					
							DRAWING NUMBER:					
							C10631					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							RVU	1/18/06	JHAC	NTS		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[F100X150AJT](#) [F100X213AJT](#) [F100X300AJT](#) [F100X363AJT](#)