


2

1



PLT.6SM
PLT.7M
HEAD VIEW




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT.6SM	.06 (1.6)	.6 (15)	.030 (.76)	.070 (1.8)	.124 (3.1)	.095 (2.4)	.125 (3.2)	2.8 (71)	8 (36)	SUB-MINIATURE	CURVED	.02 (9.0)
PLT.7M	.06 (1.6)	.68 (17)	.032 (.8)	.090 (2.3)	.148 (3.8)	.115 (2.9)	.180 (4.6)	3.1 (79)	18 (80)	MINIATURE	CURVED	.04 (16)
PLT1M	.06 (1.6)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	CURVED	.07 (32)
PLT1.5M	.06 (1.6)	1.25 (32)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	5.6 (142)	18 (80)	MINIATURE	CURVED	.10 (45)
PLT2M	.06 (1.6)	2.00 (51)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	8.0 (203)	18 (80)	MINIATURE	CURVED	.13 (59)
PLT1.5I	.06 (1.6)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	40 (178)	INTERMEDIATE	CURVED	.14 (64)
PLT2I	.06 (1.6)	2.00 (51)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	8.0 (203)	40 (178)	INTERMEDIATE	CURVED	.20 (91)
PLT2.5I	.06 (1.6)	2.50 (64)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	9.7 (246)	40 (178)	INTERMEDIATE	CURVED	.27 (122)

NOTES:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE					
							PAN-TY CABLE TIE - PLT SERIES					
							CUSTOMER DRAWING					
							ITEM REVISION NAME					
							W10001CA/35					
							DATASET FILE NAME					
							W10001CA/35-SS-5540 SH1.REV35					
35	4/05/21	BWG	MPH	JADE	CORRECTED MM MINIMUM BUNDLE DIAMETER ALL LISTED PARTS.	098922/00	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
34	10/01/15	BWG	MPH	JADE	REVISED NOTES.	SS-5540/34	.X ± - - - .XXX ± .020 [.51] .XX ± .02 [.5] ANGLES ± - - -			NYLON 6.6		
33	8/13/13	BWG	KJM	RTF1	UPDATED TITLE BORDER.	SS-5540/33	 - THIRD ANGLE PROJECTION			DRAWING NUMBER:		
										SS-5540 SHEET 1		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							CEW	12-27-84	HVP	NONE		A

2

1

D101000A/16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT1M-C](#) [PLT2I-C](#) [PLT2I-C0](#) [PLT2I-M0](#) [PLT.7M-C](#) [PLT.7M-M0](#) [PLT.6SM-C0](#) [PLT.6SM-M](#) [PLT2M-M](#) [PLT.7M-M](#)
[PLT.7M-M30](#) [PLT1M-C1](#) [PLT1M-C10](#) [PLT1M-C2](#) [PLT1M-C3](#) [PLT1M-C5](#) [PLT1M-C6](#) [PLT1M-C702Y](#) [PLT1M-DTP](#)
[PLT1M-MP](#) [PLT1M-MT30](#) [PLT1M-M00](#) [PLT1M-M3](#) [PLT1M-M30](#) [PLT1M-M60](#) [PLT1M-M7](#) [PLT2.5I-C0](#) [PLT2.5I-M20](#)
[PLT2M-C](#) [PLT2M-C0](#) [PLT2M-M10](#) [PLT2M-M4Y](#) [PLT2I-M5](#) [PLT2M-M8](#) [PLT2M-M3](#) [PLT2M-M1](#) [PLT2I-M14](#)
[PLT2I-M3](#) [PLT1M-M702Y](#) [PLT2M-M2](#) [PLT2M-M7](#) [PLT2I-M4Y](#) [PLT2I-M1](#) [PLT1M-M39](#)